

HA1SV12004

50W DC/DC Power Modules



FEATURES

- High efficiency: 86% @110Vin full load
- Size:61.0mm*57.9mm*12.7mm(2.4" *2.28" *0.5")
- Industry standard pin out and footprint
- Fixed frequency operation
- Input UVP/ OVP
- Hiccup output over current protection (OCP)
- Hiccup output over voltage protection (OVP)
- Output current limited protection(OCL)
- Auto recovery OTP
- Monotonic startup into normal
- 3000V isolation and reinforce insulation
- No minimum load required
- ISO 9001, TL 9000, ISO 14001, QS9000, OHSAS18001 certified manufacturing facility
- EN61373, EN50155
- EN60950-1

Delphi Series HA1SV12, half Brick Family DC/DC Power Modules: 53~154V in, 12V/4.2A out, 50W

The Delphi Module HA1SV12004PRFA, half brick, 53~154V input, single output, isolated DC/DC converter is the latest offering from a world leader in power system and technology and manufacturing — Delta Electronics, Inc. This product provides up to 100 watts power in an industry standard footprint and pin out. With creative design technology and optimization of component placement, these converters possess outstanding electrical and thermal performances, as well as extremely high reliability under highly stressful operating conditions. The HA1SV12004PRFA offers more than 79% high efficiency at 2A load in all input voltage range.

APPLICATIONS

Railway /Transportation system



TECHNICAL SPECIFICATIONS

PARAMETER	NOTES and CONDITIONS		A		
		Min.	Тур.	Max.	Units
1.ABSOLUTE MAXIMUM RATINGS	ENGOAGE	50	440	454)//I
1.1 Input Voltage	EN50155	53	110	154	Vdc
1.2 Input surge withstand 1.3 Operating Ambient Temperature	<100ms	-40		250 100	Vdc °C
1.4 Storage Temperature		-55		125	°C
1.5 Input/Output Isolation Voltage	reinforce	-55		3000	Vdc
2. INPUT CHARACTERISTICS	Tomoroo			3000	Vuc
2.1 Operating Input Voltage		53	110	154	Vdc
2.2 Input Under-Voltage Lockout					• 40
2.2.1 Turn-On Voltage Threshold		49	51	53	Vdc
2.2.2 Turn-Off Voltage Threshold		46	48	50	Vdc
2.3 Input Over-Voltage Lockout					
2.3.1 Turn-On Voltage Threshold		154	158	162	Vdc
2.3.2 Turn-Off Voltage Threshold		158	162	166	Vdc
2.4 Operating input current					
2.5 Maximum Input Current	Full Load, 53Vin		1.1	1.2	Α
2.6 No-Load Input Current	Vin=110V, Io=0A		18.3	30	mA
2.7 Off Converter Input Current	Vin=110V		17.1	30	mA
2.8 Input Reflected-Ripple Current (pk-pk)	Vin=110V, Io=full load, Cin=150uF/400V		35		mA
3. OUTPUT CHARACTERISTICS					
3.1 Output Voltage Set Point	Vin=110V, Io=0, Tc=25°C	11.8	12	12.2	Vdc
3.1.1 Load regulation	Vin=110V, Io=Io min to Io max		±0.05	±0.2	%
3.1.2 Line regulation	Vin=53V to160V, lo=full load		±0.01	±0.2	%
3.1.3 Temperature regulation	Vin=110V, Tc= min to max case temperatrue		±0.004	± 0.007	%/℃
3.2 Output Voltage Ripple and Noise	5Hz to 20MHz bandwidth				
3.2.1 Peak-to-Peak	Full Load,		40	60	mV
3.2.2 rms	Full Load,		6	15	mV
3.3 Operating Output Current Range		0 4.4	4.0	4.2	A
3.4 Output DC Current-Limit Inception 4. DYNAMIC CHARACTERISTICS		4.4	4.9	5.4	Α
4.1 Output Voltage Current Transient	110V, 0.1A/μs				
4.1.1 Positive Step Change in Output Current	50% lo.max to 75%		200	400	mV
4.1.2 Negative Step Change in Output Current	75% lo.max to 50%		200	400	mV
4.2 Turn-On Transient	75% IO.IIIAX to 30%		200	400	IIIV
4.2.1 Start-Up Time, From On/Off Control			50	100	ms
4.2.2 Start-Up Time, from Vin=53V to 90%Vo.set	Vin=110V		55	80	ms
4.2.3 Rise time(Vout from 10% to 90%)	VIII-110V		25	50	ms
	Capacitor:680uF/25V(RUBYCON)			00	
4.3 Maximum output capacitor	(P/N: 140146810408)*1		680		μF
5. EFFICIENCY	(1,1,1,1,1,1,1,1,1,1,1,1,1,1,1,1,1,1,1,				
5.1 100% Load	Vin=110V		86		%
5.2 60% Load	Vin=110V		83.5		%
6. ISOLATION CHARACTERISTICS					
6.1 Input to Output				3000	Vrms
6.2 Input to base				1500	Vrms
6.3 Output to base				500	Vrms
6.4 Isolation Resistance			10		ΜΩ
7. FEATURE CHARACTERISTICS					
7.1 Switching Frequency			300		kHz
7.2 ON/OFF Control, Negative Remote On/Off logic					V
7.2.1 Logic High (Module On)		3		5	V
7.2.2 Logic Low (Module Off)		-10		1 10	V
7.3 Output Voltage Trim Range 7.4 Output Over-Voltage Protection	Over full temp range; % of nominal Vout	-10 110	120	130	% %
8. GENERAL SPECIFICATIONS	Over ruii temp range; % or nominar vout	110	120	130	70
8.1 Weight	With heat spreader		80		grams
8.2 Over-Temperature Shutdown (NTC resistor)	Refer to Figure 18 for NTC resistor location		118		°C
8.3 MTBF	Traini to Figure To for NTO resistor foodilori		1,302,169		hours
(T _A =25°C, Natural convection, Vin=110Vdc, nomi	nal Vout unless otherwise noted:		.,002,100		TIOUTO

(T_A=25°C, Natural convection, Vin=110Vdc, nominal Vout unless otherwise noted;



ELECTRICAL CHARACTERISTICS CURVES




Figure 1: Efficiency vs. load current for 53, 110and 154V input voltage at 25°C.




Figure 3: Turn-on transient at zero load current) (10ms/div). Top Trace: Vout; 5V/div; Bottom Trace: ON/OFF input: 2V/div.




Figure 5: Turn-on transient at zero load current (10ms/div). Top Trace: Vout; 5V/div; Bottom Trace: input voltage: 50V/div.




Figure 2: Power dissipation vs. load current fr 53,110and 154V input voltage at 25°C.




Figure 4: Turn-on transient at full load current (10ms/div).
Top Trace: Vout: 5V/div; Bottom Trace: ON/OFF input: 2V/div.




Figure 6: Turn-on transient at full load current (10ms/div). Top Trace: Vout; 1V/div; Bottom Trace: input voltage: 50V/div.



ELECTRICAL CHARACTERISTICS CURVES




Figure 7: Output voltage response to step-change in load current (50%-75%-50% of full load; $di/dt = 0.1A/\mu s$). Bottom Trace: Vout;50mV/div; Time: 1ms/div




Figure 8: Output voltage response to step-change in load current (50%-75%-50% of full load; di/dt = 2.5A/µs). Bottom Trace: Vout;50mV/div; Time: 1ms/div




Figure 9: Output voltage noise and ripple measurement test setu




Figure 10: Output voltage ripple at nominal input voltage and max load current (10 mV/div, 2us/div) Bandwidth: 20 MHz.




Figure 11: Output voltage vs. load current showing typical current limit curves and converter shutdown points.



DESIGN CONSIDERATIONS

Input Source Impedance

The impedance of the input source connecting to the DC/DC power modules will interact with the modules and affect the stability. A low ac-impedance input source is recommended. If the source inductance is more than a few μ H, we advise 150 μ F electrolytic capacitor (ESR < 0.7 Ω at 100 kHz) mounted close to the input of the module to improve the stability.

Layout and EMC Considerations

Delta's DC/DC power modules are designed to operate in a wide variety of systems and applications. For design assistance with EMC compliance and related PWB layout issues, please contact Delta's technical support team. Below is the reference design for an input filter tested with HA1SV12004PRFA to meet class A in CISSPR 22.

Schematic and Components List




Figure 12 EMC test schematic

C121=120Uf/400V

C123,C124,C127,C132 =220pF/275VAC

C128,C129,C130,C131=2200pF/300VAC

C122,C125,C126=0.47uF/250V

T1=3.4mH, common choke R110,R111,R112,R113,R114=300kohm/1206

Test Result:

At T = +25°C, Vin = 110V and full load black line is QP model:




Figure 13 EMI test positive line

Safety Considerations

The power module must be installed in compliance with the spacing and separation requirements of the end-user's safety agency standard, i.e., UL60950-1, CSA C22.2 NO. 60950-1 2nd and IEC 60950-1 2nd: 2005 and EN 60950-1 2nd: 2006+A11+A1: 2010, if the system in which the power module is to be used must meet safety agency requirements.

Basic insulation based on 110 Vdc input is provided between the input and output of the module for the purpose of applying insulation requirements when the input to this DC-to-DC converter is identified as TNV-2 or SELV. An additional evaluation is needed if the source is other than TNV-2 or SELV.

When the input source is SELV circuit, the power module meets SELV (safety extra-low voltage) requirements. If the input source is a hazardous voltage which is greater than 60 Vdc and less than or equal to 110 Vdc, for the module's output to meet SELV requirements, all of the following must be met:

- The input source must be insulated from the ac mains by reinforced or double insulation.
- The input terminals of the module are not operator accessible.
- A SELV reliability test is conducted on the system where the module is used, in combination with the module, to ensure that under a single fault, hazardous voltage does not appear at the module's output.



When installed into a Class II equipment (without grounding), spacing consideration should be given to the end-use installation, as the spacing between the module and mounting surface have not been evaluated.

The power module has extra-low voltage (ELV) outputs when all inputs are ELV.

This power module is not internally fused. To achieve optimum safety and system protection, an input line fuse is highly recommended. The safety agencies require a normal-blow fuse with 5A maximum rating to be installed in the ungrounded lead. A lower rated fuse can be used based on the maximum inrush transient energy and maximum input current.

Soldering and Cleaning Considerations

Post solder cleaning is usually the final board assembly process before the board or system undergoes electrical testing. Inadequate cleaning and/or drying may lower the reliability of a power module and severely affect the finished circuit board assembly test. Adequate cleaning and/or drying is especially important for un-encapsulated and/or open frame type power modules. For assistance on appropriate soldering and cleaning procedures, please contact Delta's technical support team.

FEATURES DESCRIPTIONS

Over-Current Protection

The modules include an internal output over-current protection circuit, which will endure current limiting for an unlimited duration during output overload. If the output current exceeds the OCP set point, the modules will shut down, and will try to restart after shutdown(hiccup mode). If the overload condition still exists, the module will shut down again. This restart trial will continue until the overload condition is corrected.

Over-Voltage Protection

The modules include an internal output over-voltage protection circuit, which monitors the voltage on the output terminals. If this voltage exceeds the over-voltage set point, the protection circuit will constrain the max duty cycle to limit the output voltage, if the output voltage continuously increases the modules will shut down, and then restart after a hiccup-time (hiccup mode).

Over-Temperature Protection

The over-temperature protection consists of circuitry that provides protection from thermal damage. If the module will shut down. The module will restart after the temperature is within specification

Remote On/Off

The remote on/off feature on the module can be either negative or positive logic. Negative logic turns the module on during a logic low and off during a logic high. Positive logic turns the modules on during a logic high and off during a logic low.

Remote on/off can be controlled by an external switch between the on/off terminal and the Vi (-) terminal. The switch can be an open collector or open drain. For negative logic if the remote on/off feature is not used, please short the on/off pin to Vi (-). For positive logic if the remote on/off feature is not used, please leave the on/off pin to floating.




Figure 14: Remote on/off implementation

Output Voltage Adjustment (TRIM)

To increase or decrease the output voltage set point, connect an external resistor between the TRIM pin and SENSE(+) pin or SENSE(-) pin. The TRIM pin should be left open if this feature is not used.

For trim down, the external resistor value required to obtain a percentage of output voltage change \triangle % is defined as:

$$Rtrim - down = \left[\frac{10*Vnom*(1-\Delta)}{Vnom-Vnom*(1-\Delta)}\right](K\Omega)$$

Ex. When Trim-down -10% (12V×0.9=10.8V)
$$Rtrim-down = \left[\frac{10*12*0.9}{12-12*0.9}\right](K\Omega) = 90(K\Omega)$$

For trim up, the external resistor value required to obtain a percentage output voltage change \triangle % is defined as:

$$Rtrim - up = \frac{Vnom*7.92(1+\Delta)}{Vnom*(1+\Delta)*0.208-2.5}K\Omega$$

Ex. When Trim-up +10% (12Vx1.1=13.2V)

$$Rtrim - up = \frac{12 \times 7.92 \times (1 + 0.1)}{12 \times (1 + 0.1) \times 0.208 - 2.5} = 419(K\Omega)$$

The output voltage can be increased by both the remote sense and the trim, however the maximum increase is the larger of either the remote sense or the trim, not the sum of both.



The output voltage can be increased by both the remote sense and the trim, however the maximum increase is the larger of either the remote sense or the trim, not the sum of both.

When using remote sense and trim, the output voltage of the module is usually increased, which increases the power output of the module with the same output current.

Care should be taken to ensure that the maximum output power of the module remains at or below the maximum rated power.

Pin function

The pin was difine as follow in figure 20 ,we will explain the pin function:

+IN, -IN .DC voltage inputs.

Gate IN. The Gate IN pin on a driver module may be used as a logic enable/disable input.When Gate IN is pull low (<1V,referenced to -Vin),the module is turned off . when Gate IN is floating (open collector) ,the module is turned on .The open circuit voltage of Gate in PIN is less than 5V.

Gate OUT . the pulsed signal at the Gate OUT pin of a regulating driver module is used to synchronously drive the surge circuit in order to meet the RIA12 surge needed. If you don't used this function, please floating it. **+OUT**, **-OUT** .DC voltage outputs.

T(TRIM). Provides fixed or variable adjustment of the module output.

Trimming down. Allows output voltage of the module to be trimmed down, with a decrease in efficiency .ripple as a percent of output voltage goes up and input range widens since input voltage dropout(loss of regulation) moves down

Trimming up. Reverses the above effects.

-Sense,+Sense.Provides for locating the point of optimal voltage regulation external to the converter.

THERMAL CONSIDERATIONS


Thermal management is an important part of the system design. To ensure proper, reliable operation, sufficient cooling of the power module is needed over the entire temperature range of the module. Convection cooling is usually the dominant mode of heat transfer.

Hence, the choice of equipment to characterize the thermal performance of the power module is a wind tunnel.

Thermal Testing Setup

Delta's DC/DC power modules are characterized in heated vertical wind tunnels that simulate the thermal environments encountered in most electronics equipment. This type of equipment commonly uses vertically mounted circuit cards in cabinet racks in which the power modules are mounted.

The following figure shows the wind tunnel characterization setup. The power module is mounted on a test PWB and is vertically positioned within the wind tunnel. The space between the neighboring PWB and the top of the power module is constantly kept at 6.35mm (0.25").



Note: Wind Tunnel Test Setup Figure Dimensions are in millimeters and (Inches)

Figure 15: Wind tunnel test setup

Thermal Derating

Heat can be removed by increasing airflow over the module. To enhance system reliability, the power module should always be operated below the maximum operating temperature. If the temperature exceeds the maximum module temperature, reliability of the unit may be affected.



THERMAL CURVES




Figure 16: * temperature measured point

THERMAL CURVES




Figure 18: NTC resistor location

THERMAL CURVES




Figure 17: Output current vs. ambient temperature and air velocity @Vin=110V(Either Orientation, airflow from input to ouput, with heat spreader)



LEAD FREE (SAC) PROCESS RECOMMEND TEMP. PROFILE






Figure 19 recommended temperature profile for lead-free wave soldering

MECHANICAL DRAWING(BASEPLATE)



PIN#	Function		
1	+ln		
2	Gate In		
3	Gate out		
4	-ln		
5	+Out		
6	+Sense		
7	Trim		
8	-Sense		
9	-Out		



43.6 [1.72]

P9


Figure 20 the pin function and mechanical drawing

DIMENSIONAL TOLERANCE


X ±0.3mm x.x ±0.2mm x.xx ±0.1mm



MECHANICAL DRAWING(WITHOUT MOUNTING HOLE)



PIN#	Function
1	+ln
2	Gate In
3	Gate out
4	-In
5	+Out
6	+Sense
7	Trim
8	-Sense
9	-Out






Figure 21 the pin function and mechanical drawing

DIMENSIONAL TOLERANCE

X ±0.3mm x.x ±0.2mm x.xx ±0.1mm



PART NUMBERING SYSTEM									
н	A1	s	V	12	004	Р	R	F	А
Form	Input	Number of	Product	Output	Output	ON/OFF	Pin		Option Code
Factor	Voltage	Outputs	Series	Voltage	Current	Logic	Length		
H -	110-	S –	V-	12-	004-	N –	N - 0.145"	F-	A – Baseplate
Half Brick	53V~154V	Single	Series	12V	4.2A	Negative	R - 0.170" M - SMD pin	RoHS 6/6 (Lead Free)	H-without mounting hole
			Number			P -		Space - RoHS5/6	
						Positive			

MODEL LIST						
MODEL NAME	INPUT		OUTPUT		EFF @ 100% LOAD	
HA1SV12004PRFA	53V~154V	1.1A	12V	4.2A	86%	
HA1SV12004PRFH	53V~154V	1.1A	12V	4.2A	86%	

Default remote on/off logic is negative and pin length is 0.170"

For different remote on/off logic and pin length, please refer to part numbering system above or contact your local sales office. For modules with through-hole pins and the optional heatspreader, they are intended for wave soldering assembly onto system boards; please do not subject such modules through reflow temperature profile.

CONTACT: www.deltaww.com/dcdc

USA:

Telephone: East Coast: 978-656-3993

West Coast: 510-668-5100 Fax: (978) 656 3964

Email: dcdc@deltaww.com

Europe:

Phone: +31-20-655-0967 Fax: +31-20-655-0999

Asia & the rest of world:

Telephone: +886 3 4526107

P11

ext 6220~6224 Fax: +886 3 4513485

WARRANTY

Delta offers a five (5) year limited warranty. Complete warranty information is listed on our web site or is available upon request from Delta.

Information furnished by Delta is believed to be accurate and reliable. However, no responsibility is assumed by Delta for its use, nor for any infringements of patents or other rights of third parties, which may result from its use. No license is granted by implication or otherwise under any patent or patent rights of Delta. Delta reserves the right to revise these specifications at any time, without notice.