


WJ300-5.0  
PCB SCREW TERMINAL BLOCK



PCB terminal block  
 Rated current: 16 A  
 Rated voltage: 250 V  
 Wire range: 22-14 AWG  
 Pitch: 5.0 mm  
 Mounting: Wave soldering



UL/CUL

Use Group	B	C	D
Rate Voltage [V]	250	-	250
Rated Current [A]	16	-	10
Wire Range [AWG]	22~14		
Dielectric Voltage-Withstand	1.5KV		

IEC

Overvoltage Category	III	III	II
Contamination Class	3	2	2
Rated Voltage [V]	250	400	630
Rated Current [A]	24	24	24
Impulse withstand voltage [KV]	4	4	4
Conductor cross section[solid/flexible] [mm <sup>2</sup> ]	0.5~2.5		

Material

# WJ300-5.0

## PCB SCREW TERMINAL BLOCK

Insulation Material	PA66
Flame retardant rating	UL94V-0
Conductor Material	Copper alloy
Plating of conductor surface	Sn plated

### Other Data

Pitch/Poles [mm]/[P]	5.0/2~24
Stripping Length [mm]	5~6
Screw/Torque(Max)[N.m]	M3/0.5
Operating temperature [°C]	-40~+105
Soldering temperature	260°C/5S
Pin dimensions [mm]	Ø1.0
PCB Hole Diameter [mm]	Ø1.2

### Dimensions

### PCB opening diagram

