ALUMINUM ELECTROLYTIC CAPACITORS SPECIFICATION SHEET

RoHS Compliance

CUSTOMER PART No.		
Rubycon PART No.	50 ZLJ 560 M 12.5X20	
DRAWING No.	RER-215026	ISSUE No.1
ISSUE DATE	08 May 2023	



1938-1, NISHIMINOWA, INA-SHI, NAGANO-KEN, JAPAN https://www.rubycon.co.jp/

	Hiroki Komatsu		
DESIGN	H. Kromerton		
	Hideyuki Sumida		
CHECK	14. Sumida		
	Toshihiro Koike		
APPROVAL	Haike		

Aluminum electrolytic capacitor Specification Sheet

50 ZLJ 560 M 12.5X20

Drawing No.: RER-215026

Issue No. : 1


1.Scope

This specification covers polarized aluminum electrolytic capacitors with non-solid electrolyte for use in electronic equipments. Style: CE 04 (Radial Leaded)

2.Numbering System

Rated Voltage	Series	Capacitance	Capacitance Tolerance	Option	Lead Forming	Size
<u>50</u>	<u>ZLJ</u>	<u>560</u>	<u>М</u>	_		12.5X20

3.Diagram of dimensions Unit: mm



		Dimension	s	
φD	L	F	φd	α
12.5	20	5	0.6	2

1	Sleeve	P.E.T.	
2	Case	Aluminum	
3	Lead Wire	Copper clad steel wire	Tin plated

A safety vent shall be provided.

4.Marking

Unless otherwise specified, capacitor shall be clearly marked the following items on its body.

Sleeve color: Black, Lettering color: White

(1)Trade mark **Rubycon**

(2)Rated Voltage 50V (3)Nominal Capacitance 560µF

(4)Polarity (Negative Polarity)

(5)Series ZLJ

(6)Lot Number

(7)Maximum Operating
Temperature
(8)PET sleeve mark

105°C

PET

5.Electrical Performance

Table-1

Operating Temperature Range		-40 ~105	(°C)
Nominal Capacitance	20°C, 120Hz	560	(µF)
Capacitance Tolerance		-20 ~ 20	(%)
Rated Voltage		50	(V.DC)
Surge Voltage		63	(V.DC)
Leakage Current	20°C, 2min.	280	(µA max.)
Dissipation Factor (tanδ)	20°C, 120Hz	0.10	(max.)
Rated Ripple Current	105°C, 100kHz	2300	(mAr.m.s.)
Impedance Ratio 120Hz	Z-25°C/Z20°C	2	(max.)
	Z-40°C/Z20°C	3	(max.)
Impedance	20°C, 100kHz	0.032	(Ωmax.)
	-10°C, 100kHz	0.1	(Ωmax.)

Drawing No. : RER-215026

Rubycon ZLJ series

Aluminum electrolytic capacitor Specification Sheet

LJ series Issue No. : 1

6. PERFORMANCE

	T 0 1111					
1 Load Life Test	<condition> Capacitor under the test shall be applied the rated voltage continuously through 1000Ω series protective resistor (with rated ripple current) at following temperature and time. After the test and returned in standard condition for 1 to 2 hours, and the capacitor shall meet following requirements.</condition>					
	Temperature:	Temperature: 105 ±2°C Time: 10000 ⁺⁷² h				
	Time: 100					
	<criteria></criteria>					
	Leakage Current	Not more that	an the specit	fied value		
	Capacitance Change					
	Dissipation Factor			he specified	value	
	Appearance	Notable cha	nges shall n	ot be found. (except sleeve condition)	
2 Shelf Life Test	<condition> Capacitor shall be stored at follor in standard condition for 1 to 2 h (If any doubt arises on the judgm in JIS C 5141,5.2.)</condition>	nours and the cap	acitor shall ı	meet following		
	· ·	105 ±2°C				
	• • • • • • • • • • • • • • • • • • •	000 ⁺⁴⁸ h				
		0				
	<criteria></criteria>					
	Leakage Current		Not more than the specified value			
	Capacitance Change		Within ±25% of the initial value			
	Dissipation Factor		Not more than 200% of the specified value			
	Appearance	Appearance Notable changes shall not be found				
3 Rated ripple current	(1) The rated ripple current is the at maximum operating tempe (2) The combined value of D.C. voltage and shall not be rever	erature. voltage and the p				
	<frequency coefficient=""></frequency>					
	Frequency (Hz) Capacitance (uF)	1k	10k	100k≤		
	(Hz)		10k 0.94	100k≤ 1		
	(Hz) Capacitance (µF)					
	(Hz) Capacitance (µF)					
	(Hz) Capacitance (µF) 560 0.55					

Drawing No.: RER-215026



Aluminum electrolytic capacitor Specification Sheet

ZLJ series Issue No. : 1

Notes on use of aluminum electrolytic capacitors

(1) Charge and discharge

Do not use for the circuit that repeats quick charge or discharge.

(2) External stress

Do not apply excessive force of pushing, pulling bending, and/or twisting to the main body, lead wire and terminals.

(3) Heat resistance at soldering process

In the soldering process of PC board with Capacitors mounted, secondary shrinkage or crack of sleeve may be observed when soldering temperature is too high and /or soldering time is too long.

If lead wire of other components or pattern of double sided PC board touches the capacitor, the similar failure may be also originated at preheating, heating at hardening process of adhesive and soldering process.

(4) Insulation and PC board mounting

Sleeve is for marking purpose only.

It is not recognized as insulation materials.

When double sided PC board is employed, note that it could cause a short circuit if lead wire of other components or pattern of double sided PC board touches capacitor. Please avoid circuit pattern runs underneath capacitor.

In addition, case and cathode terminal are not insulated.

(5) Adhesives and coating materials

Do not use the adhesives and coating materials that contain halogenated organic solvents or chloroprene as polymer.

(6) Storage

Keep at a normal temperature and humidity. During a long storage time, leakage current will be increased. To prevent heat rise or any trouble that high leakage current possibly causes, voltage treatment is recommended for the capacitors that have been stored for a long time.

(Storage Condition)

- Do not keep Aluminum Electrolytic Capacitors in hot and/or humid atmosphere. Recommended storage condition is 5°C-35°C in temperature and not higher than 75% in relative humidity.
- · Do not keep Aluminum Electrolytic Capacitors in a condition where spray of water, saltwater or oil is expected.
- Do not store Aluminum Electrolytic Capacitors in an environment full of hazardous gas (e.g. hydrogen sulfide, sulfurous acid gas, nitrous acid, chlorine gas, ammonia, bromine gas, methyl bromide).
- · Do not keep Aluminum Electrolytic Capacitors under exposure to ozone, ultraviolet rays or radiation.
- Do not keep Aluminum Electrolytic Capacitors under exposure to acid or alkaline environment.

(7) Fumigation and halogenated flame retardant

It may cause corrosion of internal electrodes, aluminum cases and terminal surface when the following conditions exist.

- Fumigation of wooden pallets before shipment to disinfect vermin.
- Existence of components or parts that contain halogenated flame retardant agent (bromine etc.) together with capacitors.
- · When halogenated detergents of antiseptics for preventing infection of epidemic diseases contact directly to capacitors.

(8) PC board cleaning after soldering

Please consult us when cleaning is subjected.

*Guide to application except the above are described in our catalog and JEITA RCR-2367D (including any amendments).

JEITA RCR-2367D: "Safety application guide for fixed aluminum electrolytic capacitors for use in electronic equipment."

Published by Japan Electronics and Information Technology Industries Association.