
Data Sheet

Chip Monolithic Ceramic Capacitors Medium Voltage High Capacitance for General Use

GRM31CR72A104KW03L (1206, X7R, 0.10µF, DC100V)

• For your new designs, alternative parts should be used. These parts should be used only for existing design. Please consult with us for details.

RoHS regulation conformity parts



(in mm)

■ Dimensions

Length L	3.2mm±0.2mm
Width W	1.6mm±0.2mm
Thickness T	1.6mm±0.2mm
Electrode e	0.3mm min.
Electrode g (min.)	1.2mm

■ Rated Value

	Murata PN Code	Spec
Temperature Char.	R7	X7R (EIA), ±15%
Capacitance	104	0.10μF
Capacitance Tol.	К	±10%
Rated Voltage	2A	DC100V

Packaging

Code	Packaging	Minimum Quantity
L	180mm Embossed Tape	2000

■ Specifications

Please refer to

'Specification and Test Methods' PDF file.

• This data sheet is applied for CHIP MONOLITHIC CERAMIC CAPACITOR used for General Electronics equipment for your design.

<Notice>

Solderability of Tin plating termination chip might be deteriorated when low temperature soldering profile where peak solder temperature is below the Tin
melting point is used. Please confirm the solderability of Tin plating termination chip before use.

Plese refer to 'Caution' and 'Notice' for the other details.

- The RoHS compliance means that we judge from EU Directive 2002/95/EC the products do not contain lead, cadmium, mercury, hexavalent chromium, PBB and PBDE, except exemptions stated in EU Directive 2002/95/EC annex and impurities existing in natural world.
- This statement does not insure the compliance of any of the listed parts with any laws or legal imperatives developed by any EU members individually with regards to the RoHS Directive.

⚠ Note

- 1. This datasheet is downloaded from the website of Murata Manufacturing co., ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2. This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.