

SPK-8032BVT-LF


This speaker is designed to operate over a broad frequency range. It's light weight and solvent cleanable. The small size and PCB mountable design can be advantagous for many board level applications.




Electrical Specifications					
Speaker Type:	Loudspeaker	Sound Output (SPL):	73dB (@3V, 1W/10cm)		
Max Input Power:	0.15 W	Rated Current:	142 mA (max.)		
Rated Impedance:	8Ω (± 20%)	Resonant Frequency:	1.5KHz (± 200 Hz)		
Frequency Range:	500 Hz - 4 KHz				

Environmental Specifications					
Min. Operating Temp:	-20°C / -4°F	Max. Humidity:	95% (RH)		
Max. Operating Temp:	60°C / 140°F	Storage Temp:	-30°C - +70°C		

Material Specifications					
Housing Material:	ABS	Weight:	3 g		
Termination Style:	PCB Leads				







© 2020 ISL Products International Ltd. Specifications subject to change without notice.

ISL Products International Ltd. • 235 Robbins Ln., Ste 270 • Syosset, NY 11791 • info@islproducts.com • www.islproducts.com