


Antenna YP0009BA Datasheet

OC: YP0009BA



Build a Smarter World



Our aim is to provide customers with timely and comprehensive service. For any assistance, please contact our company headquarters:

Quectel Wireless Solutions Co., Ltd.

Building 5, Shanghai Business Park Phase III (Area B), No.1016 Tianlin Road, Minhang District, Shanghai 200233. China

Tel: +86 21 5108 6236 Email: <u>info@quectel.com</u>

Or our local office. For more information, please visit:

http://www.quectel.com/support/sales.htm.

For technical support, or to report documentation errors, please visit:

http://www.quectel.com/support/technical.htm

Or email to support@quectel.com.

General Notes

Quectel offers the information as a service to its customers. The information provided is based upon customers' requirements. Quectel makes every effort to ensure the quality of the information it makes available. Quectel does not make any warranty as to the information contained herein, and does not accept any liability for any injury, loss or damage of any kind incurred by use of or reliance upon the information. All information supplied herein is subject to change without prior notice.

Disclaimer

While Quectel has made efforts to ensure that the functions and features under development are free from errors, it is possible that these functions and features could contain errors, inaccuracies and omissions. Unless otherwise provided by valid agreement, Quectel makes no warranties of any kind, implied or express, with respect to the use of features and functions under development. To the maximum extent permitted by law, Quectel excludes all liability for any loss or damage suffered in connection with the use of the functions and features under development, regardless of whether such loss or damage may have been foreseeable.

Duty of Confidentiality

The Receiving Party shall keep confidential all documentation and information provided by Quectel, except when the specific permission has been granted by Quectel. The Receiving Party shall not access or use Quectel's documentation and information for any purpose except as expressly provided herein. Furthermore, the Receiving Party shall not disclose any of the Quectel's documentation and information to any third party without the prior written consent by Quectel. For any noncompliance to the above requirements, unauthorized use, or other illegal or malicious use of the documentation and information, Quectel will reserve the right to take legal action.

Antenna_Datasheet 1 / 18



Copyright

The information contained here is proprietary technical information of Quectel. Transmitting, reproducing, disseminating and editing this document as well as using the content without permission are forbidden. Offenders will be held liable for payment of damages. All rights are reserved in the event of a patent grant or registration of a utility model or design.

Copyright © Quectel Wireless Solutions Co., Ltd. 2021. All rights reserved.

Antenna_Datasheet 2 / 18



About the Document

Revision History

Version	Date	Author	Note
1.0	2020-11-26	Toby Wang	Initial

Antenna_Datasheet 3 / 18



Contents

Ab	out the	Document	3
Co	ntents		4
1	Prod	uct Description	5
2	Prod	uct Features	5
3	Prod	uct Specifications	6
4	Over	all Performance	7
	4.1.	Test Environment	7
	4.2.	VSWR	8
	4.3.	Efficiency	9
		Gain	
	4.5.	Radiation Patterns	13
5	Prod	uct Size	18



1 Product Description

The antenna is designed for superior performance, and can be widely used for wireless applications.

We provide comprehensive antenna design support such as simulation, testing and manufacturing for custom antenna solutions to meet your specific application needs.

2 Product Features

- 1.1_6G_Antenna
- High efficiency
- Excellent performance



Antenna_Datasheet 5 / 18



3 Product Specifications

Passive Electrical Specifications	
Frequency Range	1100–6000 MHz
Input Impendence	50 Ω
VSWR	≤ 3.0
Gain	≤ 4.67 dBi
Polarization Type	Linear
Mechanical Specifications	
Antenna Size	49 mm × 13 mm × 0.85 mm
Casing	FR4
Radiator	Cu
Connector Type	MHF 4
Working Temperature	-20 °C to +85 °C
Radome Color	Green

Antenna_Datasheet 6 / 18



4 Overall Performance

4.1. Test Environment


- KEYSIGHT VNA Network Analyzer E5063A 100 kHz 6.5 GHz
- RayZone[®] 2800 Chamber 5G (FR1) SISO/MIMO, 400 MHz 6.0 GHz.



Antenna_Datasheet 7 / 18



4.2. **VSWR**





Frequency (MHz)	1100	1500	1805	2170	2300	2690	3300	5000	6000
VSWR	2.77	1.35	2.42	1.50	1.45	1.38	1.47	1.35	1.08

Antenna_Datasheet 8 / 18




4.3. Efficiency






Antenna_Datasheet 9 / 18








Frequency (MHz)	1100	1500	1800	2160	2300	2680	3300	5000	6000
Efficiency (%)	33.28	47.7	42.19	56.5	41.52	59.76	59.5	52.36	33.9

Antenna_Datasheet 10 / 18




4.4. Gain






Antenna_Datasheet 11 / 18








Frequency (MHz)	1100	1500	1800	2160	2300	2680	3300	5000	6000
Gain (dBi)	-0.83	2.8	2.88	2.1	2.3	3.22	1.36	1.49	1.13

Antenna_Datasheet 12 / 18




4.5. Radiation Patterns




Antenna_Datasheet 13 / 18






Antenna_Datasheet 14 / 18






Antenna_Datasheet 15 / 18





Antenna_Datasheet 16 / 18






Antenna_Datasheet 17 / 18



5 Product Size



Antenna_Datasheet 18 / 18