Specification

Drawing No.	TKY1T-H1-22296-00[45]
Issued Date.	September 17, 2022

TO: Digi-Key

Note: In case of specification change, KYOCERA Part Number also will be changed.

Product Name	Crystal Oscillator
Product Model	
Frequency	32.768 kHz
Customer Part Number	
Customer Specification Number	
KYOCERA Part Number	MC2016K32K7680C13ASH
Remarks RoHS Compliant / MS	1 / AEC-Q200 Certified

Customer Acceptance

Accept Signature	Accept Date	
	Department	
	Person in charge	

Seller

KYOCERA Corporation Corporate Electronic Components Group Electronic Components Sales Division

6 Takeda Tobadono-cho, Fushimi-ku, Kyoto 612-8501 Japan

TEL. No. 075-604-3500 FAX. No. 075-604-3501 KYOCERA Corporation Corporate Electronic Components Group RF Devices Division Yamagata higashine Plant 5850, Higashine-koh, Higashine-shi, Yamagata 999-3701 Japan TEL. No. 0237-43-5611 FAX. No. 0237-43-5615

Design Department	Quality Assurance	Approved by	Examined by	Written by
Crystal Components Application Engineering Section2 RF Devices Engineering Department 1 RF Devices Division	Y.Katuta	T.Koyanagi 柳	K.Jikthara 原	Y.Nato 藤

KYOCERA Corporation

Drawing No.

TKY1T-H1-22296-00[45]

Revision History

Rev.No.	Description of revise	Date	Approved by	Examined by	Written by
00	First Edition	Sep. 17, 22	T.Koyanagi	K.Jikuhara	Y.Kato

1. Scope

This specification shall be defined of the Clock Oscillator for the integrated circuits (ICs).

2. Customer Part Number

3. KYOCERA Part Number

MC2016K32K7680C13ASH

4. Electrical Characteristics

4-1. Absolute Maximum Rating

Item	Symbol	Rated Value	Units
Power Supply Voltage	V _{cc}	-0.3 to +4.5	V
Input Voltage	V _{IN}	-0.3 to V _{CC} +0.3	V
Storage Temperature	T _{STG}	-55 to +125	°C

Note:

If the part is used beyond absolute maximum ratings, it may cause internal destruction. The part should be used under the recommended operating conditions the reliability of this part may be damaged if those conditions are exceeded.

4-2. Recommended Operating Conditions

Item	Symbol	Min	Тур	Max	Units	Remarks
Power Supply Voltage	V _{cc}	1.6	3.3	3.63	V	
Input Voltage	V _{IN}	0		V _{cc}	V	
Operating Temperature	T _{OPR}	-40	+25	+125	°C	

4-3. Electrical Characteristics

Item	Symbol	Min	Тур	Max	Units	Remarks
Output Frequency	Fo		32.768		kHz	
Frequency Tolerance	F_tol	-90		+90	nom	Include initial tolerance(@+25°C) and operating temperature range and Rated Power supply voltage change (Vcc±10%)
Aging	F_Aging	-3		+3	ppm	1year@+25°C
Other	F_Oth	-4		+4		Load change, shock and vibration
Current Consumption (No Load/ 1.6≤V _{CC} ≤2.0V)			-	28		
Current Consumption (No Load/ 2.0 <v<sub>CC≤2.8V)</v<sub>	Icc			29	μΑ	
Current Consumption (NoLoad/2.8 <v<sub>cc≤3.63V)</v<sub>				30		
Standby Current	Ist			5	μA	
Symmetry (Duty Ratio)	SYM	45	50	55	%	@ 50% V _{CC}
Rise Time/ Fall Time (10% V _{cc} to 90% V _{cc})	Tr/ Tf)		50	ns	
Output Voltage-"L"	Vol			10% Vcc	V	I _{OL} = 1mA
Output Voltage-"H"	Vон	90% Vcc			v	I _{OH} = -1mA
Output Load	CL			15	pF	CMOS
Input Voltage-"L"	VIL			30% Vcc	V	
Input Voltage-"H"	VIH	70% Vcc			v	
Output Disable Time	t_dis			100	ns	
Output Enable Time	t_ena			2	ms	
Start-up Time	t_ _{sta}			5	ms	@Minimum operating voltage to be 0sec

Note: All electrical characteristics have defined on the maximum loaded and recommended operating conditions.

Table 1


Drawing No.	TKY1T-H1- 22296-00[45]
-------------	------------------------

4-4. Measurement Condition

The reference temperature shall be +25±2°C. The measurement shall be performed at the temperature range of +5 °C to +35 °C unless otherwise the result is doubtful.

4-5. Clock Timing Chart

The clock timing chart is "Fig. 2".



Note: CL includes probe and test fixture capacitance



"L" Level





Fig.2 Clock Timing Chart (C-MOS Output)



High Z (No-Oscillation)

e.g. :"P4A" means "Apr-10-2034"

Table 2

M

30

4 Vcc

6. Parts Numbering Guide

$\frac{\text{MC2016K32K7680}}{A} \frac{\text{C}}{B} \frac{1}{C} \frac{3}{E} \frac{\text{A}}{\text{F}} \frac{\text{SH}}{\text{G}}$

- A. Series (SMD Oscillator)
- B. Output Frequency 32.768KHz
- C. Output C: C-MOS
- D. Supply Voltage
 1: 1.8V/ 2.5V/ 3.3V Compatible
- E. Frequency Tolerance4-3. Electrical Characteristics reference
- F. Symmetry (Duty Ratio) and Stand-by Function A: Symmetry: 45% to 55% with Stand-by Function
- G. For Automotive

Packing (Tape & Reel 2,000pcs/Reel)

7. Environmental Characteristics (Based on AEC-Q200 Rev. D)

AEC- Q200 No	Items	Conditions	Reference	Criteria of Acceptance	Sample Size [PCS]
3	High Temperature Exposure (Storage)	+125°C 1000 hrs. Unpowered.	MIL-STD-202 Method 108	Satisfy Electrical Characteristics.	77
4	Temperature Cycling	1000cycles (-55 to +125°C)	JESD22 Method JA-104	Satisfy Electrical Characteristics.	77
6	Moisture Resistance	+25°C, +65°C 90%RH 10cycles 24 hrs/1cycle. Unpowered. Steps 7a & 7b not required.	MIL-STD-202 Method 106	Satisfy Electrical Characteristics. Clause 13 shall be also satisfied.	77
7	Biased Humidity	+85°C, 85%RH, 1000 hrs. Vcc=3.63V, CL=15pF	MIL-STD-202 Method 103	Satisfy Electrical Characteristics.	77
8	Operational Life	+125°C, 1000 hrs. Vcc=3.63V, CL=15pF	MIL-STD-202 Method 108	Satisfy Electrical Characteristics.	77
9	External Visual	Magnification 10x	MIL-STD-883 Method 2009	Thing that abnormality is not found in externals. (Inspect device construction, marking and workmanship. Electrical Test not required.)	30
10	Physical Dimension	-	JESD22 Method JB-100	Satisfy Approval Sheet	30
12	Resistance to Solvents	Magnification 10x	MIL-STD-202 Method 215	Thing that abnormality is not found in externals.	5
13	Mechanical Shock	100G/6ms/Half-sine Velocity change 12.3 (Vi)ft/sec	MIL-STD-202 Method 213	Satisfy Electrical Characteristics.	30
14	Vibration	10 to 2000Hz. 5g's for 20 minutes 12 cycles each of 3 orientations.	MIL-STD-202 Method 204	Satisfy Electrical Characteristics.	30
15	Resistance to Soldering Heat	Soaking:+260±5°C, 10±1sec	MIL-STD-202 Method 210	Satisfy Electrical Characteristics.	30
16	Thermal Shock	-55°C/+125°C. 300Cycles, Max. transfer time 20 sec. Dwell time 5 min. Air-Air.	MIL-STD-202 Method 107	Satisfy Electrical Characteristics.	30
17	ESD	Human Body Model: 100pF/1500ohm/500~2000V 5 pulses	AEC-Q200-002	Satisfy Electrical Characteristics.	15
18	Solderability	8 hrs. steam age +215°C solder temperature 5 second dwell	J-STD-002	Dipped potion: Minimum 95% coverage	15
19	Electrical Characterization	-	Approval Sheet	Satisfy Approval Sheet	30 x 3Lot

Drawing No.


TKY1T-H1- 22296-00[45]

AEC- Q200 No	Items	Conditions	Reference	Criteria of Acceptance	Sample Size [PCS]
21	Board Flex	It pressurizes in the direction of the arrow, it pressurizes at the speed of 2mm in bend width about 0.5mm/sec, and it maintains it for 60 seconds.	AEC-Q200-005	Satisfy Electrical Characteristics. Without looseness or crack etc.	30
22	Terminal Strength (SMD)	The static load of 1.8Kg is added in the direction of the arrow and it maintains it in the prime fields of parts for 60 sec with a scratch treatment device of R0.5.	AEC-Q200-006	Satisfy Electrical Characteristics. Without looseness or crack etc.	30

After above test, measurement shall be done after leaving sample in room temperature for 2 hours.

Table 3


8. Recommended Land pattern and Soldering Guide



Note:

Since the part doesn't have Bypass Capacitor between $V_{\rm cc}$ and GND, Please mount high frequency type capacitor $0.01\mu F$ to the nearest position of oscillator.


Fig.3 Land pattern




• Available Reflow times: Maximum twice

Fig.4 Reflow profile (Lead Free Available)

9. Taping Specifications



	A ₀		P ₁	D_1		
				U	nit: (mm)	
symbol	A ₀	B ₀	W	F	Ε	S
imensions	1.8±0.05	2.25±0.05	8.0±0.2	3.5±0.05	1.75±0.1	E
symbol	P 1	P ₂	P ₀	D ₀	Τ	S
imensions	4.0±0.1	2.0±0.05	4.0±0.1	1.5+0.1/-0	0.2±0.05	D
symbol	K	D ₁				S
imensions	0.9±0.1	1.1±0.1				E



-			Unit: (mm)
Symbol	A	N	W 1
Dimensions	180 +0/-1.5	60+1/0	9.0+0.3/-0
Symbol	W2	C	D
Dimensions	11.4±1.0	13.0±0.2	21.0±0.8
Symbol	E		
Dimensions	2.0±0.5		

Fig.6 Reel

9-1. Taping Quantities


Di Si Di

D

• The taping of per reel shall be packed 2,000 pcs.

Fig.5 Emboss Carrier Tape

- The parts shall be contained continuously in the pocket.
- 9-2. Leader and Blank Pockets
 - The package shall be consisted of leader, blank pockets and loaded pocket as follows "Fig. 7".
 - The power of peeling strength between top tape and carrier tape shall be 0.1N(10gf) to 1.0N(100gf) as follows "Fig. 8".



D) Lot No.

Drawing No.	TKY1T-H1- 22296-00[45]
-------------	------------------------

10. The agreement of this specifications

In case there is any obscure point or doubt concerning the contents of the specification, it shall be settled through consultation of both parties.

11. Remarks on Usages

A) Storage Conditions

The parts shall be stored in temperature range of -5 to +40°C, humidity 40 to 60% RH, and avoid direct sunlight. Then the parts shall be used within 6 months.

B) Handling Conditions

Although the part has protection circuit against static electricity, when excess static electricity is applied, the inside IC may get damaged.

Before mounting on the PCB, please make sure the direction of the part is correct. Otherwise the part of temperature will increase. And also the part will have some damages.

Please do not use the parts under the unfavorable condition such as beyond specified range in this specification.

Please do not use the parts under the condition, in the water or in the salt water also environment of dew or harmful gas.

Please make sure the condition of pick and place following pick up nozzle guideline.

Picking Method: Case of Head Unit 1.6 x 1.2mm (Inside Diameter)

The proper condition of pick and place will be different each equipment. Therefore, please check before testing.

This product can be used for general electronic equipment (information equipment, communication equipment, audiovisual equipment, measuring equipment, home appliances, etc.)Intended to be used. Equipment and systems (traffic equipment, safety equipment, aviation / space control, nuclear power control, life support equipment) that require special quality and reliability and whose failure or malfunction may endanger human life or harm the human body. (Including medical devices, etc.), basic driving functions (running, turning, stopping) and collision safety in traffic equipment, applications related directly or indirectly to collision safety, and applications that are expected to have a significant impact on property, etc. It is not intended to be used.In the unlikely event that this product is used for any of these purposes, we will not be liable for any damages resulting from such use.

C) Rework Condition

Please do not pick up Head Unit. We can't guaranty electrical performance and reliability.

D) Soldering Conditions

This product can respond to the general Pb-free reflow profile. The wave soldering cannot be supported.

E) Soldering in Mounting

In case of Solder paste and conductive glue contact product lid or product side face exception for product terminal it's possible to influence product characteristics. Please be careful above contents.

F) Washing Conditions

Ultra sonic cleaning is available. However there is a possibility that Crystal in the part may cause damaged under certain condition. Therefore please test before using.

After washing, please dry the parts completely. Otherwise water drops between the parts and PCB may cause migration.

In case of using this part without above precaution, Kyocera is unable to guarantee the specific characteristics.

12. Quality guarantee

In case when Kyocera Corporation rooted failure occurred within 1year after its delivery, substitute product will be arranged based on discussion. Quality guarantee of product after 1year of its delivery is waivered.