

Harvatek Surface Mount CHIP LEDs Data Sheet BTL11IRS-A1C00011TU1930

Preliminary

Official Product	HT Part No. BTL11IRS-A1C00011TU1930				
Tentative Product	*******				
Specifications are subject to changes for improvement without advance notice. Proprietary data, drawings, company confidential all rights reserved.		06/26/2023	Preliminary	Page 1/14	



DISCLAIMER	3
LIFE SUPPORT POLICY	3
PRODUCT SPECIFICATIONS	4
ATTENTION: ELECTROSTATIC DISCHARGE (ESD) PROTECTION	4
LABEL SPECIFICATIONS	5
ELECTRO-OPTICAL CHARACTERISTICS	6
PACKAGE OUTLINE DIMENSION AND RECOMMENDED SOLDERING PATTERN FOR REFLOW	
Soldering	7
CHARACTERISTICS OF BTL11IRS	8
PACKAGING	10
TAPE DIMENSION	10
REEL DIMENSION	11
Packing	11
DRY PACK	12
Baking	12
Precautions	12
REFLOW SOLDERING	13
Reworking	13
CLEANING	13
CAUTIONS OF PICK AND PLACE	14
REVISE HISTORY	14

Official Product	HT Part No. BTL11IRS-A1C00011TU1930			
Tentative Product	********			
Specifications are subject to changes for improvement without advance notice. Proprietary data, drawings, company confidential all rights reserved.		06/26/2023	Preliminary	Page 2/14



DISCLAIMER

HARVATEK reserves the right to make changes without further notice to any products herein to improve reliability, function or design. HARVATEK does not assume any liability arising out of the application or use of any product or circuit described herein; neither does it convey any license under its patent rights, nor the rights of others.

Life Support Policy

HARVATEK's products are not authorized for use as critical components in life support devices or systems without the express written approval of the President of HARVATEK or HARVATEK INTERNATIONAL. As used herein:

- 1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, and (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury of the user.
- 2. A critical component in any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

Official Product	HT Part No. BTL11IRS-A1C00011TU1930				
Tentative Product	********				
Specifications are subject to changes for improvement without advance notice. Proprietary data, drawings, company confidential all rights reserved.		06/26/2023	Preliminary	Page 3/14	



Product Specifications

Item	Specification	Material	Quantity
Peak Wavelength	Typ:810nm		
λ_{p}	@100 mA/ $T_S = 25^{\circ}C$; Tolerance: ± 1 nm		
Radiant Intensity	Typ:290 mW/sr		
l _e	@100 mA/ $T_S = 25^{\circ}C$; Tolerance: $\pm 10\%$		
Forward Voltage	1.2-2.0V		
V _F	@100 mA/ $T_S = 25^{\circ}C$; Tolerance: $\pm 0.1V$		
Reverse Current	< 10 µA		
I_R	@ V _R = 5V		
Resin	Clear	Ероху	
Carrier tape	EIA 481-1A specs	Conductive black tape	
Reel	EIA 481-1A specs	Conductive blue	
Label	HT standard	Paper	
Packing bag	430x500mm	Aluminum laminated bag / zipper	One reel per bag
Carton	HT standard	Paper	Non-specified

Others:

Each immediate box consists of 10 reels. The 10 reels may not necessarily have the same lot number or the same bin combinations of Iv, λP and Vf. Each reel has a label identifying its specification; the immediate box consists of a product label as well.

Note: This is shipped test conditions

*Remarks: This product should be operated in forward bias. If a reverse voltage is continuously applied to the product, such operation can cause migration resulting in LED damage.

ATTENTION: Electrostatic Discharge (ESD) protection



The symbol to the left denotes that ESD precaution is needed. ESD protection for GaP and AlGaAs based chips is necessary even though they are relatively safe in the presence of low static-electric discharge. Parts built with AlInGaP, GaN, or/and InGaN based chips are **STATIC SENSITIVE devices**. ESD precaution must


be taken during design and assembly.

If manual work or processing is needed, please ensure the device is adequately protected from ESD during the process.

Official Product	HT Part No. BTL11IRS-A1C00011TU1930				
Tentative Product	*******				
Specifications are subject to changes for improvement without advance notice. Proprietary data, drawings, company confidential all rights reserved.		06/26/2023	Preliminary	Page 4/14	



Label Specifications



■Harvatek P/N:

B TL1 1 IRS- A1C 0001 1T

Product	Package	Dice Q'ty	Color	Current	Series Number	Taping
РСВ	3.6(L)x3.2(W)x3.4(H) mm	1:Single	IRS:810nm	100mA	X001~XZZZ	1.Taping style
						2. Q'ty

■ Lot No.:

1	2	3	4	5	6	7	8	9	10
E	1	Α	1	A	2	2	L	1	2
Coc	de 1 2	Code 3	Code 4	Code 5	Code 6	Code 7	Code 8	Code 9	Code 10
		Mfg. Year	Mfg. Month	Mfg. Date	Consecuti	ve number		Special code	e
Internal Tr	racing Code	2020-L 2021-M 2022-P 2023-Q 2026-T 2027-V 2030-Y 2031-Z	1:Jan. 2:Feb. A:Oct. B:Nov. C:Dec.	1:A 2:B 3:C 26:Z 27:7 28:8 29:9 30:3 31:4	01-	-ZZ		000~ZZZ	

Official Product	HT Part No. BTL11IRS-A1C00011TU1930			
Tentative Product	*******			
Specifications are subject to changes for improvement without advance notice. Proprietary data, drawings, company confidential all rights reserved.		06/26/2023	Preliminary	Page 5/14



Absolute Maximum Rating At 25℃

Symbol	Parameters	Ratings	Units	Notes
I _F	Forward Current	100	mA	
I _{FP}	Peak Forward Current	1	А	1
V _R	Reverse Voltage	5	V	
T_{opr}	Operating Temperature	-40 ~ +85	$^{\circ}\!\mathbb{C}$	
T _{stg}	Storage Temperature	-40 ~ +100	$^{\circ}\!\mathbb{C}$	
T _{sol}	Soldering Temperature	260	$^{\circ}\!\mathbb{C}$	2

Notes:

- 1. I_{FP} Conditions--Pulse Width \leq 100 μ s and Duty \leq 1%.
- 2. Soldering time \leq 5 seconds.

Electro-Optical Characteristics

Symbol	Parameters	Test conditions	Min	Тур	Max	Units	Notes
l _e	Radiant Intensity	I _F =100mA	225	290	340	mW/sr	3
λ_{P}	Peak Wavelength	I _F =100mA	-	810	-	nm	4
Δλ	Spectral bandwidth at 50% of I _{max}	I _F =100mA	-	30	-	nm	
V _F	Forward Voltage	I _F =100mA	1.2	1.7	2.0	V	5
I _R	Reverse Current	V _R =5V	-	-	10	μA	
20	Angle of Half Intensity (X)	I 100m A	-	12	-	doa	
$2\theta_{1/2}$	Angle of Half Intensity (Y)	I _F =100mA	-	12	-	deg	

Notes:

3. Radiant Intensity (I_e) Bin:

Color	Bin Code	Spec. Range
	QF	225-240 mW/sr
	QG	240-255 mW/sr
	QH	255-270 mW/sr
IRS	QJ	270-285 mW/sr
	QK	285-300 mW/sr
	QL	300-320 mW/sr
	QM	320-340 mW/sr

(It maintains a tolerance of ±10% on Radiant Intensity)

Official Product	HT Part No. BTL11IRS-A1C00011TU1930			
Tentative Product	*******			
Specifications are subject to changes for improvement without advance notice. Proprietary data, drawings, company confidential all rights reserved.		06/26/2023	Preliminary	Page 6/14



Notes:

4. Peak Wavelength (λ_P) :

Color	Bin Code	Spec. Range
IRS	D5	790-830 nm

(It maintains a tolerance of ±1nm on Wavelength Bin)


5. Forward Voltage (V_F) Bin:

Color	Bin Code	Spec. Range		
	D5	1.2-1.4 V		
IRS	D6	1.4-1.6 V		
	E5	1.6-1.8 V		
	E6	1.8-2.0 V		

(It maintains a tolerance of ±0.1V on forward voltage measurements)

Package Outline Dimension and Recommended Soldering Pattern for Reflow Soldering


(Unit: mm Tolerance: +/-0.1)





Official Product	HT Part No. BTL11IRS-A1C00011TU1930			
Tentative Product	*******			
Specifications are subject to changes for improvement without advance notice. Proprietary data, drawings, company confidential all rights reserved.		06/26/2023	Preliminary	Page 7/14





Characteristics of BTL11IRS











Official Product	HT Part No. BTL11IRS-A1C00011TU1930			
Tentative Product	*******			
Specifications are subject to changes for improvement without advance notice. Proprietary data, drawings, company confidential all rights reserved.		06/26/2023	Preliminary	Page 8/14



Precaution for Use


- 1. The chips should not be used directly in any type of fluid such as water, oil, organic solvent, etc.
- 2. When the LEDs are illuminating, the maximum ambient temperature should be first considered before operation.
- 3. LEDs must be stored in a clean environment. A sealed container with a nitrogen atmosphere is necessary if the storage period is over 3 months after shipping.
- 4. The LEDs must be used within 168 hrs after unpacked. Unused products must be repacked in an anti-electrostatic package, folded to close any opening and then stored in a dry and cool space.
- 5. The appearance and specifications of the products may be modified for improvement without further notice.
- 6. The LEDs are sensitive to the static electricity and surge. It is strongly recommended to use a grounded wrist band and anti-electrostatic glove when handling the LEDs.If a voltage over the absolute maximum rating is applied to LEDs, it will damage LEDs.Damaged LEDs will show some abnormal characteristics such as remarkable increase of leak current, lower turn-on voltage and getting unlit at low current.


Official Product	HT Part No. BTL11IRS-A1C00011TU1930			
Tentative Product	*******			
Specifications are subject to changes for improvement without advance notice. Proprietary data, drawings, company confidential all rights reserved.		06/26/2023	Preliminary	Page 9/14

Dim. C




Packaging Tape Dimension






Unit: mm




Official Product	HT Part No. BTL11IRS-A1C00011TU1930			
Tentative Product	*******			
Specifications are subject to changes for improvement without advance notice. Proprietary data, drawings, company confidential all rights reserved.		06/26/2023	Preliminary	Page 10/14



Reel Dimension



Packing



10 reels per box is available depending on shipment quantity.

Official Product	HT Part No. BTL11IRS-A1C00011TU1930			
Tentative Product	********			
Specifications are subject to changes for improvement without advance notice. Proprietary data, drawings, company confidential all rights reserved.		06/26/2023	Preliminary	Page 11/14




Dry Pack

All SMD optical devices are **MOISTURE SENSITIVE**. Avoid exposure to moisture at all times during transportation or storage. Every reel is packaged in a moisture protected anti-static bag. Each bag is properly sealed prior to shipment.

A humidity indicator will be included in the moisture protected anti-static bag prior to shipment.

The packaging sequence is as follows:



Baking

Baking before soldering is recommended when the package has been unsealed for 168 hrs. The conditions are as followings:

- 1. $60\pm3^{\circ}$ C ×(12~24hrs)and<5%RH, taped reel type.
- 2. $100\pm3^{\circ}$ C ×(45min~1hr), bulk type.
- 3. $130\pm3^{\circ}$ ×(15min~30min), bulk type.

Precautions

- 1. Avoid exposure to moisture at all times during transportation or storage.
- 2. Anti-Static precaution must be taken when handling GaN, InGaN, and AlGaInP products.
- 3. It is suggested to connect the unit with a current limiting resistor of the proper size. Avoid applying a reverse voltage beyond the specified limit.
- 4. Avoid operation beyond the limits as specified by the absolute maximum ratings.
- 5. Avoid direct contact with the surface through which the LED emits light.
- 6. If possible, assemble the unit in a clean room or dust-free environment.

Official Product	HT Part No. BTL11IRS-A1C00011TU1930			
Tentative Product	******			
Specifications are subject to changes for improvement without advance notice. Proprietary data, drawings, company confidential all rights reserved.		06/26/2023	Preliminary	Page 12/14




Reflow Soldering

Recommend soldering paste specifications:

- 1. Operating temp.: Above 217°C ,60~150sec
- 2. Peak temp.:260°C Max.,10sec Max.
- 3. Reflow soldering should not be done more than two times.
- 4. Never take next process until the component is cooled down to room temperature after reflow.
- 5. The recommended reflow soldering profile (measuring on the surface of the LED terminal) is following:

Lead-free Solder Profile



Reworking

- Rework should be completed within 5 seconds under 260°C.
- The iron tip must not come in contact with the copper foil.
- Twin-head type is preferred.

Cleaning

Following are cleaning procedures after soldering:

- An alcohol-based solvent such as isopropyl alcohol (IPA) is recommended.
- Temperature x Time should be 50°C x 30sec. or <30°C x 3min
- Ultra sonic cleaning: < 15W/ bath; bath volume ≤ 1liter
- Curing: 100°C max, <3min

Official Product	HT Part No. BTL11IRS-A1C00011TU1930			
Tentative Product	********			
Specifications are subject to changes for improvement without advance notice. Proprietary data, drawings, company confidential all rights reserved.		06/26/2023	Preliminary	Page 13/14



Cautions of Pick and Place

- Avoid stress on the resin at elevated temperature.
- Avoid rubbing or scraping the resin by any object.
- Electric-static may cause damage to the component. Please ensure that the equipment is properly grounded. Use of an ionizer fan is recommended.

Revise History

Rev.	Descriptions	Date	Page
Preliminary	-	06/23/2023	-

Official Product	HT Part No. BTL11IRS-A1C00011TU1930			
Tentative Product	*******			
Specifications are subject to changes for improvement without advance notice. Proprietary data, drawings, company confidential all rights reserved.		06/26/2023	Preliminary	Page 14/14