







Product Outline:

This is PLCC-4 series with high output reflector type 3528 LEDs are available in Infrared Emitter. With special binning technology, Quelighting is able to provide special binning for customer's needs

Features:

- High brightness output @ 100mA
- Package Dimension = 3.5mmX2.8mmX1.9mm
- PLCC-4 850nm LED
- RoHS compliant
- Custom Bin available upon special request

Application:

- Mechanically and spectrally matched to the phototransistor
- Infrared Illumination for cameras
- Sensor technology
- Gesture Recognition
- Surveillance


Compliance and Certification:









Mechanical Property: (Dimension)








Units: mm

Recommended Solder footprint:



Units: mm





(T=25 °C)

Electrical / Optical Characteristic (T=25 °C)									
Product	Color	1 (0)	V _F (V)		λp (nm)		lv(mW)		
Product	Color	l _F (mA)	Тур.	max	Min.	Тур.	Max.	min	typ.
QLIR05BYAM	Infrared	100	1.5	2.0		850		10	18

(1) The Forward Voltage tolerance is $\pm 0.1V$

(2) The λD tolerance is ±1nm

(3) The Iv tolerance is $\pm 7\%$

Absolute Maximum Rating

Part #	P _d (mW)	I _F (mA)	I _{FP} (mA)*	V _R (V)	Т _{оР} (°С)	Т _{sт} (°С)	T _{SOL} (°C)**
Infrared	200	100	100	5	-40 – 85	-40 - 100	260

*Duty 1/10 @ 10Khz

** Junction Temperature

*** IR Reflow for no more than 10 sec @ 260 °C

**** Thermal resistance is calculated from junction to solder

Forward Voltage (V_F) Bin:

VF rank @ 100mA					
Code name	Min.	Max.	Unit		
L6	1.4	2.0	V		

The forward voltage tolerance is $\pm 0.1V$

Radiant Intensity Bin:

Po (mW/sr) rank @ 100mA					
Code name Min. Max. Unit					
P0010	10	20	···· \\/		
P0020	20	30	mW		


luminous intensity tolerance is ± 7%





QLIR05BYAM V1.0


Characteristic Curves







QLIR05BYAM V1.0







Solder Profile:

-The recommended reflow soldering profile is as follows (temperatures indicated are as measured on the surface of the LED resin):


- When soldering LEDs,
- Do not solder/reflow the same LED over two times.
- Recommend soldering conditions:

Hand soldering: 300 °C max , 3 sec. max.

Reflow soldering: Pre-heat 150 max , 180 sec. max. °C

Peak 260 ma °C x , 5 sec. max.

- Reflow temperature profile as below: (lead-free solder)











Taping & Packing:



Unit : mm











Labeling

Quantity: XX			QueLighting
Quelighting F			
lv Bin: XX	Color Bin: XX	Vf Bin: XX	Date Code: XXXX

Ordering Information:

Part #	Multiple Quantities	Quantity per Reel
QLIR05BYAM		1000pcs, 2000 pcs





Revision History:

Revision Date:	Changes:	Version #:
08-05-2020	Initial release	1.0

