BUSSMANN SERIES

PTSAHT0805

Automotive high temperature SMD PTC fuses



Product features

- AEC-Q200 qualified
- Positive temperature coefficient (PTC)
- Surface mount resettable fuse
- Compact 0805 (2012 metric) footprint
- High temperature
- Voltage rating 16 V
- Current rating from 0.10 A
- Fast time-to-trip

Applications

- Infotainment
- In-vehicle navigation
- Telematics
- Car lighting
- Power window and seat control
- Instrument clusters
- PCB trace protection

Environmental compliance







Part number system/ordering: PTSAHT080516V010

- PT= PTC resettable fuse
- S= Surface mount
- AHT= Automotive with high operating temperature
- 0805= Dimension code
- 16V= Maximum voltage
- 010= Ihold current rating (010= 0.10 A)




Product specifications


	Vmax ¹	lmax²	lhold ³	ltrip ⁴	Pd⁵	Time-t (maxin		Resistance ⁶		
Part number	(V _{dc})	(A)	(A)	(A)	typical (W)	(A)	(seconds)	Initial (R _i) minimum (Ω)	Post trip (R ₁) maximum (Ω)	Part marking
PTSAHT080516V010	16	40	0.10	0.60	1.00	2.50	1.50	1.00	10.00	1

- 1. Vmax: Maximum continuous voltage the device can withstand without damage at rated current
- 2. Imax: Maximum fault current the device can withstand without damage at rated voltage
- 3. Ihold: Maximum current the device will pass without interruption at +23 °C still air
- 4. Itrip: Minimum current that will transition the device from low resistance to high resistance at +23 °C still air
- 5. Pd: Power dissipated from the device when in tripped state at +23 °C still air
- 6. R; Minimum resistance of the device at +23 °C R; Maximum resistance of the device one hour after tripping at +23 °C

Dimensions-mm



Recommended pad layout



Part number	A typ	A max	B typ	B max	C typ	C max	D min	E min	F	G	Н
PTSAHT080516V010	2.25	2.50	1.50	1.60	0.60	0.80	0.25	0.076	1.2	1.0	1.5

Thermal derating chart - Ihold (A)

Part number	Maximum ambient temperature (°C)									
	-40	-20	0	25	40	50	60	70	85	125
PTSAHT080516V010	0.150	0.130	0.115	0.100	0.090	0.084	0.078	0.072	0.063	0.040


PTSAHT0805 Automotive high temperature SMD PTC fuses

General specifications

Operating temperature: -40 $^{\circ}$ C to + 125 $^{\circ}$ C (with derating)
Storage temperature: -10 °C to + 40 °C
Storage relative humidity: ≤70%
Storage conditon: Keep away form corrosive atmosphere and sunlight
Passive aging: IEC60738-1 , +60 °C, 1000 hours, ≤20% IEC60738-1 , +85 °C, 1000 hours, ≤20%
Humidity aging: +85 °C, 85% RH, 100 hours, ≤20%
Thermal shock: IEC60738-1, +85 °C/ -40 °C, 20 cycles, ≤50%
Trip cycle life: UL1434, Vmax, Imax, 100 cycles, no arcing or burning
Trip endurance: UL1434, Vmax, Itrip ≤ I ≤ Imax, 2 hours, no arcing or burning
MSL test: J-STD-020, MSL=1, pass and no visible damage

Packaging information

Supplied in tape and reel packaging, 4000 parts per 7.0" (178 mm) diameter reel (EIA-481 compliant)



	w	F	E1	E2	P0	P1	P2	D0	D1	A0	BO	KO	Т
-	8.00 ± 0.30	3.50 ± 0.10	1.75 ± 0.10	-	4.00 ± 0.10	4.00 ± 0.10	2.00 ± 0.05	1.50 + 0.10/-0	-	1.68 ± 0.10	2.44 ± 0.10	1.04 + 0.10	0.22 ± 0.05

Solder reflow profile




Table 1 - Standard SnPb solder (T_C)

Package thickness	Volume mm3 <350	Volume mm3 ≥350
<2.5 mm)	235 °C	220 °C
≥2.5 mm	220 °C	220 °C

Table 2 - Lead (Pb) Free Solder (T_C)

Package thickness	Volume mm³ <350	Volume mm³ 350 - 2000	Volume mm³ >2000
<1.6 mm	260 °C	260 °C	260 °C
1.6 – 2.5 mm	260 °C	250 °C	245 °C
>2.5 mm	250 °C	245 °C	245 °C

Reference J-STD-020

Profile feature	Standard SnPb solder	Lead (Pb) free solder	
Preheat and soak • Temperature min. (T _{smin})	100 °C	150 °C	
• Temperature max. (T _{smax})	150 °C	200 °C	
• Time (T _{smin} to T _{smax}) (t _s)	60-120 seconds	60-120 seconds	
Ramp up rate T_L to T_p	3 °C/ second max.	3 °C/ second max.	
Liquidous temperature (TL) Time (t_L) maintained above T_L	183 °C 60-150 seconds	217 °C 60-150 seconds	
Peak package body temperature (Tp)*	Table 1	Table 2	
Time $(t_p)^*$ within 5 °C of the specified classification temperature (T_c)	20 seconds*	30 seconds*	
Ramp-down rate (T _p to T _L)	6 °C/ second max.	6 °C/ second max.	
Time 25 °C to peak temperature	6 minutes max.	8 minutes max.	

^{*} Tolerance for peak profile temperature (T_D) is defined as a supplier minimum and a user maximum.

Life Support Policy: Eaton does not authorize the use of any of its products for use in life support devices or systems without the express written approval of an officer of the Company. Life support systems are devices which support or sustain life, and whose failure to perform, when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in significant injury to the user.

Eaton reserves the right, without notice, to change design or construction of any products and to discontinue or limit distribution of any products. Eaton also reserves the right to change or update, without notice, any technical information contained in this bulletin.

Eaton Electronics Division 1000 Eaton Boulevard Cleveland, OH 44122

Cleveland, OH 44122 United States Eaton.com/electronics

© 2021 Eaton All Rights Reserved Printed in USA Publication No. ELX1044 BU-ELX21044 June 2021

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

