

SML4728 - SML4764

SURFACE MOUNT SILICON ZENER DIODES


V_Z : 3.3 - 100 Volts
P_D : 1 Watt

FEATURES :

- * Complete Voltage Range 3.3 to 100 Volts
- * High peak reverse power dissipation
- * High reliability
- * Low leakage current
- * Pb / RoHS Free

MECHANICAL DATA :

- * Case : SMA Molded plastic
- * Epoxy : UL94V-O rate flame retardant
- * Polarity : Color band denotes cathode end
- * Mounting position : Any
- * Weight : 0.060 gram (Approximately)




MAXIMUM RATINGS

Rating at 25 °C ambient temperature unless otherwise specified

| Rating | Symbol | Value | Unit |
|--|------------------|---------------|------|
| DC Power Dissipation at T _L = 75 °C (Note1) | P _D | 1.0 | W |
| Maximum Forward Voltage at I _F = 200 mA | V _F | 1.2 | V |
| Junction Temperature Range | T _J | - 55 to + 150 | °C |
| Storage Temperature Range | T _{STG} | - 55 to + 150 | °C |

Note :

(1) P.C.B. Mounted on 0.31x0.31x0.08" (8x8x2mm) copper areas pads.





ELECTRICAL CHARACTERISTICS

Rating at 25 °C ambient temperature unless otherwise specified

| Type | Nominal Zener Voltage | | Maximum Zener Impedance | | | Maximum Reverse Leakage Current | | Maximum DC Zener Current | Maximum Surge Current |
|---------|-------------------------|------|-------------------------|-----------|------|---------------------------------|------|--------------------------|-----------------------|
| | Vz ⁽¹⁾ @ IZT | IZT | ZzT @ IZT | Zzk @ Izk | Izk | IR @ VR | | IZM | IRM ⁽²⁾ |
| | (V) | (mA) | (Ω) | (Ω) | (mA) | (μA) | (V) | (mA) | (mApk) |
| SML4728 | 3.3 | 76.0 | 10 | 400 | 1.0 | 100 | 1.0 | 276 | 1380 |
| SML4729 | 3.6 | 69.0 | 10 | 400 | 1.0 | 100 | 1.0 | 252 | 1260 |
| SML4730 | 3.9 | 64.0 | 9.0 | 400 | 1.0 | 50 | 1.0 | 234 | 1190 |
| SML4731 | 4.3 | 58.0 | 9.0 | 400 | 1.0 | 10 | 1.0 | 217 | 1070 |
| SML4732 | 4.7 | 53.0 | 8.0 | 500 | 1.0 | 10 | 1.0 | 193 | 970 |
| SML4733 | 5.1 | 49.0 | 7.0 | 550 | 1.0 | 10 | 1.0 | 178 | 890 |
| SML4734 | 5.6 | 45.0 | 5.0 | 600 | 1.0 | 10 | 2.0 | 162 | 810 |
| SML4735 | 6.2 | 41.0 | 2.0 | 700 | 1.0 | 10 | 3.0 | 146 | 730 |
| SML4736 | 6.8 | 37.0 | 3.5 | 700 | 1.0 | 10 | 4.0 | 133 | 660 |
| SML4737 | 7.5 | 34.0 | 4.0 | 700 | 0.5 | 10 | 5.0 | 121 | 605 |
| SML4738 | 8.2 | 31.0 | 4.5 | 700 | 0.5 | 10 | 6.0 | 110 | 550 |
| SML4739 | 9.1 | 28.0 | 5.0 | 700 | 0.5 | 10 | 7.0 | 100 | 500 |
| SML4740 | 10 | 25.0 | 7.0 | 700 | 0.25 | 10 | 7.6 | 91 | 454 |
| SML4741 | 11 | 23.0 | 8.0 | 700 | 0.25 | 5.0 | 8.4 | 83 | 414 |
| SML4742 | 12 | 21.0 | 9.0 | 700 | 0.25 | 5.0 | 9.1 | 76 | 380 |
| SML4743 | 13 | 19.0 | 10 | 700 | 0.25 | 5.0 | 9.9 | 69 | 344 |
| SML4744 | 15 | 17.0 | 14 | 700 | 0.25 | 5.0 | 11.4 | 61 | 305 |
| SML4745 | 16 | 15.5 | 16 | 700 | 0.25 | 5.0 | 12.2 | 57 | 285 |
| SML4746 | 18 | 14.0 | 20 | 750 | 0.25 | 5.0 | 13.7 | 50 | 250 |
| SML4747 | 20 | 12.5 | 22 | 750 | 0.25 | 5.0 | 15.2 | 45 | 225 |
| SML4748 | 22 | 11.5 | 23 | 750 | 0.25 | 5.0 | 16.7 | 41 | 205 |
| SML4749 | 24 | 10.5 | 25 | 750 | 0.25 | 5.0 | 18.2 | 38 | 190 |
| SML4750 | 27 | 9.5 | 35 | 750 | 0.25 | 5.0 | 20.6 | 34 | 170 |
| SML4751 | 30 | 8.5 | 40 | 1000 | 0.25 | 5.0 | 22.8 | 30 | 150 |
| SML4752 | 33 | 7.5 | 45 | 1000 | 0.25 | 5.0 | 25.1 | 27 | 135 |
| SML4753 | 36 | 7.0 | 50 | 1000 | 0.25 | 5.0 | 27.4 | 25 | 125 |
| SML4754 | 39 | 6.5 | 60 | 1000 | 0.25 | 5.0 | 29.7 | 23 | 115 |
| SML4755 | 43 | 6.0 | 70 | 1500 | 0.25 | 5.0 | 32.7 | 22 | 110 |
| SML4756 | 47 | 5.5 | 80 | 1500 | 0.25 | 5.0 | 35.8 | 19 | 95 |
| SML4757 | 51 | 5.0 | 95 | 1500 | 0.25 | 5.0 | 38.8 | 18 | 90 |
| SML4758 | 56 | 4.5 | 110 | 2000 | 0.25 | 5.0 | 42.6 | 16 | 80 |
| SML4759 | 62 | 4.0 | 125 | 2000 | 0.25 | 5.0 | 47.1 | 14 | 70 |
| SML4760 | 68 | 3.7 | 150 | 2000 | 0.25 | 5.0 | 51.7 | 13 | 65 |
| SML4761 | 75 | 3.3 | 175 | 2000 | 0.25 | 5.0 | 56.0 | 12 | 60 |
| SML4762 | 82 | 3.0 | 200 | 3000 | 0.25 | 5.0 | 62.2 | 11 | 55 |
| SML4763 | 91 | 2.8 | 250 | 3000 | 0.25 | 5.0 | 69.2 | 10 | 50 |
| SML4764 | 100 | 2.5 | 350 | 3000 | 0.25 | 5.0 | 76.0 | 9.0 | 45 |

Notes :

- (1) Standard voltage tolerance is ±10%, Suffix A ± 5%
- (2) Surge current is a non-repetitive, 8.3ms pulse width square wave or equivalent sine-wave superimposed on IZT per JEDEC Method
- (3) " SML " will be omitted in marking on the diode.