







Product Outline:

This is PLCC-4 series with high output reflector type 3528 LEDs are available in Infrared Emitter. With special binning technology, Quelighting is able to provide special binning for customer's needs

Features:

- High brightness output @ 100mA
- Package Dimension = 3.5mmX2.8mmX1.9mm
- PLCC-4 1300nm LED
- RoHS compliant
- Custom Bin available upon special request

Application:

- Mechanically and spectrally matched to the phototransistor
- Infrared Illumination for cameras
- Sensor technology
- Gesture Recognition
- Surveillance

Compliance and Certification:







Mechanical Property: (Dimension)







Units: mm

Recommended Solder footprint:



Units: mm





(T=25 °C)

| Electrical / Optical Characteristic (T=25 °C) | | | | | | | | | |
|---|----------|---------------------|--------------------|-----|---------|------|--------|-----|------|
| Product | Color | l _F (mA) | V _F (V) | | λp (nm) | | lv(mW) | | |
| Product | | | Тур. | max | Min. | Тур. | Max. | min | typ. |
| QLIR05FYAM | Infrared | 100 | 1.5 | 2.0 | | 1300 | | 2 | 3 |

(1) The Forward Voltage tolerance is ±0.1V

(2) The λD tolerance is ±1nm

(3) The Iv tolerance is $\pm 7\%$

Absolute Maximum Rating

| Part # | P _d (mW) | I _F (mA) | I _{FP} (mA)* | V _R (V) | Т _{оР} (°С) | Т _{sт} (°С) | Т _{SOL} (°С)** |
|----------|---------------------|---------------------|-----------------------|--------------------|----------------------|----------------------|-------------------------|
| Infrared | 200 | 100 | 100 | 5 | -40 – 85 | -40 - 100 | 260 |

*Duty 1/10 @ 10Khz

** Junction Temperature

*** IR Reflow for no more than 10 sec @ 260 °C

**** Thermal resistance is calculated from junction to solder

Forward Voltage (V_F) Bin:

| VF rank @ 100mA | | | | | |
|-----------------|------|------|------|--|--|
| Code name | Min. | Max. | Unit | | |
| L6 | 1.4 | 2.0 | V | | |

The forward voltage tolerance is $\pm 0.1V$

Radiant Intensity Bin:

| Po (mW/sr) rank @ 100mA | | | | | |
|-------------------------|------|------|------|--|--|
| Code name | Min. | Max. | Unit | | |
| P00022 | 2 | 4 | mW | | |

luminous intensity tolerance is ± 7%





QLIR05FYAM V1.0

Characteristic Curves





QLIR05FYAM V1.0











Solder Profile:

-The recommended reflow soldering profile is as follows (temperatures indicated are as measured on the surface of the LED resin):

- When soldering LEDs,
- Do not solder/reflow the same LED over two times.
- Recommend soldering conditions:

Hand soldering: 300 °C max , 3 sec. max.

Reflow soldering: Pre-heat 150 max , 180 sec. max. °C

Peak 260 ma °C x , 5 sec. max.

- Reflow temperature profile as below: (lead-free solder)









Taping & Packing:



Unit : mm











Labeling

| Quantity: XX | | | QueLighting |
|---------------|-----------------|------------|-----------------|
| Quelighting F | 9/N: XXXXXX | | |
| lv Bin: XX | Color Bin: XX | Vf Bin: XX | Date Code: XXXX |

Ordering Information:

| Part # | Multiple Quantities | Quantity per Reel |
|------------|---------------------|-------------------|
| QLIR05FYAM | | 1000pcs, 2000 pcs |
| | | |
| | | |
| | | |





Revision History:

| Revision Date: | Changes: | Version #: |
|----------------|-----------------|------------|
| 08-05-2020 | Initial release | 1.0 |
| | | |
| | | |
| | | |
| | | |

