IEC Appliance Inlet C20 or C24, Split panel or screw-on mounting, PCB Terminal



Split panel mounting, Snap-in PCB 1.6 mm, Additional earth terminal 90° to connector axis



Split panel mounting, Screw-on PCB, Additional earth terminal 90° to connector axis



Screw-on panel mounting, Snap-in PCB 1.6 mm, Additional earth terminal in connector axis





70° C

See below:

Approvals and Compliances

Description

- Panel mount :
- Splitpanel (sandwich) or screw-on from backside
- Appliance Inlet , Pin temperature 70 °C , protection class I or II
- V-Lock notch standard
- Additional ground terminal
- Safety of electrical appliances for household and similar purposes.
 Meets the requirements for appliances in unattended use. This includes the enhanced requirements of glow wire tests acc. to IEC 60695-2-11 or -12 & -13.
- Variants with protection cover on rear side
- For PCB mounting: screw-on or snap-in 1.6 mm

Other versions on request

- Further colours on request

Weblinks

pdf data sheet, html datasheet, General Product Information, Approvals, Distributor-Stock-Check, Accessories, Detailed request for product

Technical Data

Ratings IEC	16A / 250VAC; 50Hz
Ratings UL/CSA	20A / 250VAC; 60Hz
Dielectric Strength	> 1.5 kVAC between L-N
	> 1.5 kVAC between L/N-PE
	(1 min/50 Hz)
Allowable Operation Tempe-	-25 °C to 70 °C
rature	
IP-Protection	front side IP20 acc. to IEC 60529
Protection against electric	Suitable for appliances with protection
shock	class I or II acc. to IEC 61140
Terminal	PCB terminals, additional ground ter-
	minal
Panel Thickness S	for sandwich mounting
	1/1.2/1.5/2/2.5/3/4 mm
Material: Housing	Thermoplastic, black, UL 94V-0

(for cold cor	I, CSA C22.2 no. 60320-1 nditions) pin-temperature 70 rotection Class I or II
O, 10A, 11	OLECTION CIASS FOR II

Approvals and Compliances

Detailed information on product approvals, code requirements, usage instructions and detailed test conditions can be looked up in Details about Approvals

SCHURTER products are designed for use in industrial environments. They have approvals from independent testing bodies according to national and international standards. Products with specific characteristics and requirements such as required in the automotive sector according to IATF 16949, medical technology according to ISO 13485 or in the aerospace industry can be offered exclusively with customer-specific, individual agreements by SCHURTER.

Approvals

The approval mark is used by the testing authorities to certify compliance with the safety requirements placed on electronic products. Approval Reference Type: GSP4

Approval Logo	Certificates	Certification Body	Description
10	VDE Approvals	VDE	Certificate Number: 40035923
c AL °us	UL Approvals	UL	UL File Number: E96454
(W)	CCC Approvals	CCC	CCC Certificate Number: 2020180204014249, 2020180204014250

Product standards

Product standards that are referenced

Organization	Design	Standard	Description
<u>IEC</u>	Designed according to	IEC 60320-1	Appliance couplers for household and similar general purposes
(N)	Designed according to	UL 60320-1	Standard for Attachment Plugs and Receptacles
CSA Group	Designed according to	CSA C22.2 no. 60320-1	General Use Receptacles, Attachment Plugs, and Similar Wiring Devices

Application standards

Application standards where the product can be used

Organization	Design	Standard	Description
<u>IEC</u>	Designed for applications acc.	IEC/UL 62368-1	Audio/video, information and communication technology equipment - Part 1: Safety requirements
IEC	Designed for applications acc.	IEC 60335-1	Safety of electrical appliances for household and similar purposes. Meets the requirements for appliances in unattended use. This includes the enhanced requirements of glow wire tests acc. to IEC 60695-2-11 or -12 & -13.


Compliances


The product complies with following Guide Lines


Identification	Details	Initiator	Description
C€	CE declaration of conformity	SCHURTER AG	The CE marking declares that the product complies with the applicable requirements laid down in the harmonisation of Community legislation on its affixing in accordance with EU Regulation 765/2008.
UK CA	UKCA declaration of conformity	SCHURTER AG	The UKCA marking declares that the product complies with the applicable requirements laid down in the British Amendment of Regulation (EC) 765/2008.
RoHS	RoHS	SCHURTER AG	Directive RoHS 2011/65/EU, Amendment (EU) 2015/863
©	China RoHS	SCHURTER AG	The law SJ / T 11363-2006 (China RoHS) has been in force since 1 March 2007. It is similar to the EU directive RoHS.
REACH	REACH	SCHURTER AG	On 1 June 2007, Regulation (EC) No 1907/2006 on the Registration, Evaluation, Authorization and Restriction of Chemicals 1 (abbreviated as "REACH") entered into force.
V -Lock		SCHURTER AG	V-Lock system are based on a matching plug-dose combination. The connector is equipped with a notch intended for use with the latching cordset. The cord latching system prevents against accidental removal of the cordset.
00	White Paper Glow wire test	SCHURTER AG	Meets the requirements of IEC 60335-1 for appliances in unattended use. This includes the enhanced requirements of glow wire tests acc. to IEC 60695-2-11 or -12 &-13.


Dimensions [mm]


Split panel mounting / Snap-in on PCB















Dimension
Quick connect 6.3x0.8 mm
Solder


Υ В 40.3 15.0 30.0 37.3 30.0 15.0


Ζ 25.9 22.9


2) with protection cover


Split panel mounting / Screw-on mounting on PCB















Dimension	
Quick connect 6.3x0.8 mm	
Solder	

Α	В	Υ
40.3	15.0	30.0
37.3	15.0	30.0

Ζ 25.9 22.9


- 1) Mounting screw torque max. 0.3 Nm
- 2) with protection cover

Screw-on rear side / Snap-in on PCB



2) with protection cover

Screw-on rear side / Screw-on mounting on PCB



1) Mounting screw torque max. 0.3 Nm

2) with protection cover

All Variants

Protection Class	Panel mounting	Panel Thick- ness s [mm]	PCB mounting	Additional ground ter	minal	Cover	Order Number
				Terminal	Terminal direction		
1	Sandwich	1.0	Screw	solder terminal	90° to connector axis	none	GSP4.010C.11
1	Sandwich	1.5	Screw	solder terminal	90° to connector axis	none	GSP4.010C.13
1	Sandwich	1.5	Screw	Quick connect terminal 6.3 x 0.8 mm	straight	none	GSP4.0107.13
I	Sandwich	1.5	Snap-in	Quick connect terminal 6.3 x 0.8 mm	90° to connector axis	none	GSP4.0205.13
1	Sandwich	1.5	Snap-in	Quick connect terminal 6.3 x 0.8 mm	straight	none	GSP4.0207.13
I	Sandwich	3.0	Snap-in	Quick connect terminal 6.3 x 0.8 mm	straight	none	GSP4.0207.16
1	Sandwich	3.0	Snap-in	Quick connect terminal 6.3 x 0.8 mm	straight	mounted	GSP4.0217.16
I	Screw	-	Screw	Quick connect terminal 6.3 x 0.8 mm	straight	none	GSP4.0107.10
I	Screw	-	Snap-in	Quick connect terminal 6.3 x 0.8 mm	90° to connector axis	none	GSP4.0205.10
I	Screw	-	Snap-in	Quick connect terminal 6.3 x 0.8 mm	straight	none	GSP4.0207.10
I	Screw	-	Snap-in	Quick connect terminal 6.3 x 0.8 mm	straight	mounted	GSP4.0217.10
II	Sandwich	1.5	Snap-in	-	-	mounted	GSP4.0210.13

Most Popular.

Availability for all products can be searched real-time:https://www.schurter.com/en/Stock-Check/Stock-Check-SCHURTER

With screw mounting on PCB, 2 screws are included

Packaging unit

50 Pcs

Mating Outlets/Connectors

Category / Description



Appliance Outlet Overview complete

5017 Mounting: Screw-on mounting, 250 VAC, 16 A Appliance Outlet: IEC	5017



Connector Overview complete

4795, Mounting: Power Cord, Cable Connector: IEC C19	4795
4790, Mounting: Power Cord, Screw Connector: IEC C19	4790



Power Supply Cord Overview complete

Cord Sets 16 A, Europlug, 2.5 m, Connector IEC C19, H05VV-F3G1.5, black	6004.0395
Cord Sets 16 A, Interconnection, 1.0 m, Connector IEC C19, H05VV-F3G1.5, black	6020.0392
Cord Sets 16 A, Interconnection, 2.0 m, Connector IEC C19, H05W-F3G1.5, black	6020.0394

Mating Outlets/Connectors shuttered



Power Cord Overview complete

VAC19KS, Overview, V-Lock cord retaining, diverse Connector IEC C19, diverse, black

VAC19KS

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Schurter:

<u>GSP4.0107.10</u> <u>GSP4.010C.13</u> <u>GSP4.0207.13</u> <u>GSP4.0207.16</u> <u>GSP4.0210.13</u> <u>GSP4.0107.13</u> <u>GSP4.0207.10</u> <u>GSP4.0217.10</u> <u>GSP4.0205.10</u> <u>GSP4.0217.16</u> <u>GSP4.010C.11</u> <u>GSP4.0117.13</u> <u>GSP4.0205.13</u> <u>GSP4.020C.10</u> <u>GSP4.020E.13</u> <u>GSP4.0217.13</u> 3-104-933