

QT-FIT 5/8 2X18...39

QUICKTRONIC FIT 5/8 | ECG for FL and CFL, not dimmable



Product family features

- Supply voltage: 220...240 V
- Line voltage: 198...264 V
- Line frequency: 50 Hz | 60 Hz
- Lamp start with optimum filament preheating
- Energy Efficiency Index EEI: A2
- Automatic shutdown of defective lamps and at end of life (EoL T.2)
- Lamp operation: to EN 60929
- Safety: to EN 61347-2-3

Product family benefits

- Long lamp life
- No adverse effect from frequent on/off switching
- Automatic restart after lamp replacement
- Perfect lamp start for applications with motion sensors
- VDE/VDE EMC certified system
- Very high energy efficiency due to cut-off technology

Areas of application

- Open-plan offices, corridors and storage rooms
- Public buildings
- Strip lighting
- Suitable for luminaires of protection class I
- Modernization of existing systems

Product datasheet

Technical data

Electrical data

Input voltage AC	198...264 V
Nominal voltage	220...240 V
Mains frequency	50...60 Hz
Input voltage DC	185...264 V ¹⁾
Maximum output power	2 x 39 W
Efficiency in full-load	91 % ²⁾
Operating frequency	40...50 kHz
Max. ECG no. on circuit breaker 10 A (B)	12 ³⁾
Max. ECG no. on circuit breaker 16 A (B)	19 ³⁾
Inrush current	40 A

¹⁾ Minimum voltage for lamp ignition: 198 V, 185...198 V for maximum 1 h


²⁾ at 230 V, 50 Hz

³⁾ Type B

Light technical data

Starting time	2.0 s
---------------	-------

Dimensions & weight



Length	280.0 mm
Width	30.0 mm
Height	21.0 mm
Mounting hole spacing, length	270.0 mm
Product weight	183.00 g
Cable cross-section, output side	0.5...1.5 mm ² ¹⁾
Cable cross-section, input side	0.5...1.5 mm ² ¹⁾

¹⁾ Solid leads

Temperatures & operating conditions

Ambient temperature range	-15...+50 °C
Permitted rel. humidity during operation	5...85 % ¹⁾

¹⁾ Maximum 56 days/year at 85 %

Lifespan

ECG lifetime	50000 h
--------------	---------

Expected Lifetime

Product name	Lamp group				
QT-FIT 5/8 2X18...39	HO 24 W	ECG ambient temperature [ta]	40	50	60
		Temperature at tc-point [°C]	55	60	70
		Lifetime [h]	100000	70000	40000
	HO 39 W	ECG ambient temperature [ta]	40	50	58
		Temperature at tc-point [°C]	60	70	75
		Lifetime [h]	70000	40000	30000
	L 18 W	ECG ambient temperature [ta]	40	50	60
		Temperature at tc-point [°C]	50	60	70
		Lifetime [h]	100000	90000	50000
	L 30 W	ECG ambient temperature [ta]	40	50	60
		Temperature at tc-point [°C]	55	65	75
		Lifetime [h]	100000	60000	40000
	L 36 W	ECG ambient temperature [ta]	40	50	60
		Temperature at tc-point [°C]	55	65	75
		Lifetime [h]	100000	60000	30000

Additional product data

Suitable for lamp power (2 lamps)	18...39 W
-----------------------------------	-----------

Capabilities

Suitable for fixtures with prot. class	I
End of lamp life safety shutdown	EOL T.2
Max. cable length to lamp/LED module	2.0 m / 1.0 m
Dimmable	No
Intended for no-load operation	No

Certificates & standards

Approval marks – approval	CE / VDE / ENEC 10 / VDE-EMC
EEI – Energy Label	A2
Standards	Acc. to EN 61347-2-3/IEC 61347-2-3/Acc. to EN 55015:2006 + A1:2007 + A2:2009/Acc. to EN 61000-3-2/IEC 61000-3-2/Acc. to EN 61547/IEC 61547
Protection class	I
Type of protection	IP20


Logistical data

Commodity code	850410809000
----------------	--------------

Environmental information


Information according Art. 33 of EU Regulation (EC) 1907/2006 (REACH)	
Date of Declaration	14-04-2022
Primary Article Identifier	4008321873903
Candidate List Substance 1	Lead
CAS No. of substance 1	7439-92-1
Safe Use Instruction	The identification of the Candidate List substance is sufficient to allow safe use of the article.
Declaration No. in SCIP database	65704919-0d83-404e-95f9-569fba9de57a

Wiring Diagram



QUICKTRONIC® FIT T5/T8

Series	QT-FIT 58	QT-FIT 58	QT-FIT 58	QT-FIT 58
Series	17 x	17 x	16 x	8 x
Series	8 770 x 28 mm	8 770 x 28 mm	8 770 x 28 mm	8 770 x 28 mm
Series	20 47 x	20 47 x	10 32 x	10 32 x
Series	8 770 x 28 mm	8 770 x 28 mm	8 770 x 28 mm	8 770 x 28 mm
T _h	4.20 A	4.20 A	4.40 A	4.55 A
T _h	200 µs	200 µs	200 µs	200 µs



319639_QTP5 2x...

592455_EAC QT-FIT 58

Additional product information

- In order to achieve good radio interference suppression: 1. Keep the cable between ECG and lamp as short as possible. 2. The single lamp wires must be routed as close as possible to each other, whereas the lines of the different lamp ends must be routed separately.

Download Data

File
User instruction QUICKTRONIC QT FIT 5 8
Product Datasheet 502688_ECG lifetime - QUICKTRONIC non DIM
Certificates 592319_EAC certificate for Quicktronics QT
Certificates 346513_ENEC QT-FIT 5_8
Certificates 346514_EMC QT-FIT 5_8
Certificates 346515_CE Declaration QT-FIT 5_8

Product datasheet



Declarations of conformity
QUICKTRONIC CE 3364256 190821

Ecodesign regulation information:

Separate control gear and light sources must be disposed of at certified disposal companies in accordance with Directive 2012/19/EU (WEEE) in the EU and with Waste Electrical and Electronic Equipment (WEEE) Regulations 2013 in the UK. For this purpose, collection points for recycling centres and take-back systems (CRSO) are available from retailers or private disposal companies, which accept separate control gear and light sources free of charge. In this way, raw materials are conserved and materials are recycled.

Logistical Data

Product code	Product description	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Volume	Gross weight
4008321873903	QT-FIT 5/8 2X18...39	Shipping carton box 20	312 mm x 165 mm x 98 mm	5.05 dm ³	3801.00 g

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.

QT-FIT 5/8 2X18...39

QUICKTRONIC FIT 5/8 | ECG for FL and CFL, not dimmable

Product name	Lamp group	Nominal current	Nominal wattage + Power loss	Power factor λ [PIM]	Luminous flux at 35 °C	Number of lighting outlets	Luminous flux at 25 °C
QT-FIT 5/8 2X18...39	HO 24 W	0.24 A	53.00 W	0.98	1750 lm	2	
	HO 39 W	0.36 A	80.00 W	0.98	3100 lm	2	
	L 18 W	0.17 A	39.00 W	0.95	1350 lm	2	
	L 23 W	0.26 A	59.30 W			1	1900 lm
	L 30 W	0.27 A	63.00 W	0.98		2	2350 lm
	L 36 W	0.31 A	70.00 W	0.98	3200 lm	2	