


QuPanel 5G/LTE Global MIMO 2x2

Directional ultra wideband 5G/LTE MIMO 2x2 antenna

QuPanel **5G**/LTE omnidirectional MIMO 2x2 is ultra wideband 5G outdoor antenna. It's primary designed for LTE/5G/3G/2G devices which require high efficiency connections. The antenna covers many LTE bands including the new Extended LTE **Band 71** and frequencies: **600 - 6000MHz**. The mounting bracket allows the antenna to be installed on the pole or on the wall, as the client antenna to receive Internet by LTE/5G/3G/2G. It's ideal solution to use with all industrial and domestic 2x2 5G modems and routers like: Teltonika, Digi, Mikrotik, Robustel, Cisco, etc.



WIDE BAND 600-6000MHZ, 5G TECHNOLOGY



GALVANIZED STEEL, WALL OR POLE MOUNTING BRACKET



TWO SMA CONNECTORS



80° BEAMWIDTH



POE 7DBI GAIN



MADE IN EUROPE



5G AND LTE ANTENNA SPECIFICATION

FREQUENCY	617 - 960 MHz 1.7 - 2.7 GHz 3.3 - 4.6 GHz 4.7 - 6.0 GHz
GAIN	617 - 960 MHz : 6 dBi 1.7 - 2.7 GHz : 7 dBi 3.3 - 4.6 GHz : 7 dBi 4.7 - 6.0 GHz : 5.5dBi
SUPPORTED LTE/5G BANDS	1, 2, 3, 4, 5, 7, 8, 9, 10, 12, 13, 14, 17, 18, 19, 20, 22, 25, 26, 27, 28, 29, 30, 33, 34, 35, 36, 37, 38, 39, 40, 41, 42, 43, 44, 48, 49, 52, 53, 65, 66, 67, 68, 69, 71, 85, 103, n77, n78, n79, n80, n81, n82, n83, n84, n85, n89, n90, n95, n97, n98, n100, n101
VSWR	<2.00, max <3.00
BEAMWIDTH	80°/80° ±15°
POLARIZATION	X (±45degrees)
IMPEDANCE	50 Ω

MECHANICAL SPECIFICATION

MATERIALS	ABS, aluminum, PTFE, fiberglass
CONNECTOR TYPE	SMA
INGRESS PROTECTION	IP67
DIMENSIONS	486.0 x 292.2 x 105.6 mm 19.13 x 11.50 x 4.16 inch
WEIGHT	2.8 kg 6.17 lbs
OPERATING TEMPERATURE	From -40°C to 80°C From -40°F to 176°F

FREQUENCY BANDS

LTE / 4G GSM	<table border="1"> <tr> <td>5</td><td>6</td><td>8</td><td>12</td><td>13</td><td>14</td><td>17</td> </tr> <tr> <td>18</td><td>19</td><td>20</td><td>26</td><td>27</td><td>28</td><td>29</td> </tr> <tr> <td>44</td><td>67</td><td>68</td><td>71</td><td>85</td><td>n81</td><td>n82</td> </tr> <tr> <td>n83</td><td>n89</td><td></td><td></td><td></td><td></td><td></td> </tr> </table> <p>617 MHz 960 MHz</p>	5	6	8	12	13	14	17	18	19	20	26	27	28	29	44	67	68	71	85	n81	n82	n83	n89					
5	6	8	12	13	14	17																							
18	19	20	26	27	28	29																							
44	67	68	71	85	n81	n82																							
n83	n89																												
LTE / 4G UMTS	<table border="1"> <tr> <td>1</td><td>2</td><td>3</td><td>4</td><td>9</td><td>10</td><td>25</td> </tr> <tr> <td>33</td><td>34</td><td>35</td><td>36</td><td>37</td><td>39</td><td>59</td> </tr> <tr> <td>62</td><td>n80</td><td>n84</td><td>n86</td><td>n95</td><td></td><td></td> </tr> </table> <p>1710 MHz 2170 MHz</p>	1	2	3	4	9	10	25	33	34	35	36	37	39	59	62	n80	n84	n86	n95									
1	2	3	4	9	10	25																							
33	34	35	36	37	39	59																							
62	n80	n84	n86	n95																									
LTE / 4G WCS DARS	<table border="1"> <tr> <td>2300 MHz</td> <td>30</td> <td>40</td> <td>2400 MHz</td> </tr> </table>	2300 MHz	30	40	2400 MHz																								
2300 MHz	30	40	2400 MHz																										

LTE / 4G

 2400 MHz 7 38 41 53 69 n90 2700 MHz

LTE / 5G

 3300 MHz 22 42 43 48 49 52 n78 3800 MHz

COMPATIBLE ROUTERS

VARIANTS: AP5G2-G, AP5G2-G1

TELTONIKA

RUT200, RUT230, RUT240, RUT241, RUT900, RUT901, RUT950, RUT951, RUT955, RUT956, RUTX09, RUTX11

DIGI

6310-DX, 6330-MX, EX12, EX15, IX10, IX20, WR31

ROBUSTEL

EG5100, LG5100, R1500, R1510, R1511, R1520 Global, R2010, R2011, R2110, R3000 Industrial, R3000 LG, R3000 Lite, R3000 Quad, R3010

SIEMENS

6GK5876-4AA00-2BA2, 6GK5876-4AA00-2DA2, 6GK5876-4AA10-2BA2

ANYBUS

Wireless Router WLAN

COMSET

CM210A-W, CM210Q-W, CM510Q-W, CM685T-W, CM685V-1, CM685V-4, CM685V-6, CM685V-6-G, CM820T-W, CM820V-4, CM820V-W

CRADLEPOINT

CBA550, E100, E102, IBR200, IBR600C, IBR900, L950

D-LINK

G415 AX1500, G416 AX1500, N300 4G

FORTINET

FEX-101F, FEX-201F, FEX-211E, FEX-212F

FOUR-FAITH

4G Cellular Router F-R100, Cellular Wireless Router F-R200, Dual-sim WiFi Router F3946, Industrial WiFi Router F3X36Q, LAN Port Router F3X26 V2, LTE Industrial Router F3X27 V2, LTE Wireless Router F3x36

PEPLINK

MAX BR1 Classic, MAX BR1 ENT, MAX BR1 M2M, MAX BR1 Mini, MAX BR1 MK2, MAX BR1 Pro, MAX BR1 Slim

PROROUTE

H685 4G Router

SIERRA WIRELESS

AirLink LX40, AirLink LX60, AirLink MP70, AirLink RV50X, AirLink RV55, AirLink RX55

WAVETEL


W2400 LTE , W3600 4G/LTE Dual WAN, W3604 Multi-WAN, W3608 Multi-WAN, W421, W4600, W4600-S2

WLINK


G200, G510, G520, R210, R220, R520

PLOTS



VSWR




Gain




PORT 1 - 5G/LTE from 650MHz to 950MHz




PORT 1 - 5G/LTE from 1.71GHz to 2.17GHz




PORT 1 - 5G/LTE from 2.3GHz to 2.7GHz




PORT 1 - 5G/LTE from 3.3GHz to 3.8GHz




PORT 1 - 5G/LTE from 4.2GHz to 4.6GHz




PORT 1 - 5G/LTE from 5.0GHz to 5.9GHz




PORT 2 - 5G/LTE from 650MHz to 950MHz




PORT 2 - 5G/LTE from 1.71GHz to 2.17GHz




PORT 2 - 5G/LTE from 2.3GHz to 2.7GHz



PORT 2 - 5G/LTE from 3.3GHz to 3.8GHz



PORT 2 - 5G/LTE from 4.2GHz to 4.6GHz



PORT 2 - 5G/LTE from 5.0GHz to 5.9GHz

