ADD: 4th Building, Meitai Technology Park, Guanguang Road, Longhua, Shenzhen, China. 518110

# **Lithium Manganese Battery Technology Specification**

Customer	
Part name	Lithium Manganese Battery
Model No	CR123A 1500mAh 3.0V
Serial No	
Produce No	

Approved by	Drafted by	Wenfei liang
Checked by	Signed by	Xiaojun Nie
Prepared by	Valid Date	2018-08-20

Company address: 4th Building, Meitai Technology Park, Guanguang

Road,Longhua,Shenzhen,China. (Tel): +86-755-86670672

(Fax): +86-755-86670609

E-mail: <a href="mailto:pkcell.net">pkcell@pkcell.com</a>
Website: <a href="mailto:http://www.pkcell.com">http://www.pkcell.com</a>

ADD: 4th Building, Meitai Technology Park, Guanguang Road, Longhua, Shenzhen, China. 518110

### 1. SCOPE

The specification applies to CR123A (Li/MnO<sub>2</sub>) battery supplied by Shenzhen pkcell battery Co.,Ltd

# 2. Characteristics and Performance

### Table1

Item	Storage	Performance	Test condition
Nominal Voltage	_	3.0V	_
Normal capacity	_	1500mAh	Continuous Discharge at 10mA To 2.0V at 20±3℃
Max.Constant Current	_	1500mA	_
Max. Pulse Current	_	3000mA	_
Working temperature	_	-40~+85℃	_
	Fresh	3.10V~3.30V	DC
OCV	After 12 months	3.10V~3.30V	Voltmeter:accuracy≥±0.005V Input impedance≥1MΩ
CCV	Fresh	≥3.00V	DC voltmeter:
	After 12 months	≥3.00V	accuracy≥±0.005V load: 15kΩ for 0.8 sec.

# 3. Precautions

 Never charge the battery as it is not designed to be rechargeable, may cause leakage or explosion.

- 2 -


- Insert battery with its positive and negative terminals properly aligned with the corresponding marks on the equipment.
- Never short circuit, heat, incinerate or dismantle the battery.

Fig1. Structure and Dimensions



ADD: 4th Building, Meitai Technology Park, Guanguang Road, Longhua, Shenzhen, China. 518110





- 3 -

.....END.....