

FEATURES

- Ta-MnO₂ technology • •
- Low DCL
- Parameters stability over voltage and time
 - Undertab and J-lead LF


APPLICATIONS

- DC/DC •
- . Industrial
- Telecom
- loT .
- Home applications
- Sensors .






MARKING



W	Pol	Polarity Band (Anode+				
н						
W	A	A	W,			




CASE DIMENSIONS: millimeters (inches)

							<u> </u>
Code	EIA Code	EIA Metric	L±0.10 (0.004)	W±0.10 (0.004)	H±0.10 (0.004)	W1±0.10 (0.004)	A±0.10 (0.004)
М	0603	1608-09	1.60 (0.063)	0.85 (0.033)	0.80 (0.031)	0.55 (0.022)	0.50 (0.020)

CASE DIMENSIONS: millimeters (inches) EIA W±0.20 W1±0.20 A±0.30 EIA L±0.20 H±0.20 (0.008) Code Code Metric (0.008) (0.008) (0.008) (0.012) 1.60 (0.063) 1.20 (0.047) max 1206 0805 3216-18 2012-12 1.20 (0.047) 0.80 (0.031) 0.90 (0.035) 0.45 (0.018) 3.20 (0.126) 1.60 (0.063) A

2.00 (0.079) 1.25 (0.049)

HOW TO ORDER



0G = 4Vdc 0J = 6.3Vdc 1A = 10Vdc 1C = 16Vdc 1D = 25Vdc 1E = 25Vdc

1V = 35Vdc

47	75	
 ita		~

Capacitance Code pF code: 1st two digits represent significant figures, 3rd digit represents multiplier (number of zeros to follow)

	Γ
Toler M = ±	

Μ



8R

sprocket hole

Packaging 8 = Tape width R = Positive electrode on the side opposite to



Discrimination code

KUDCER8 | The Important Information/Disclaimer is incorporated in the catalog where these specifications came from or available online at www.kyocera-avx.com/disclaimer/ by reference and should be reviewed in full before placing any order.

TDS-PTNO-0044 | Rev 1



TECHNICAL SPECIFICATIONS

Technical Data:	All technical data relate to an ambient temperature of +25°C	
Capacitance Range:	1μF to 100μF	
Capacitance Tolerance:	±20%	
Leakage Current DCL:	Please see the ratings and part number reference table below	
Temperature Range:	-55°C to +125°C	

Note: Conductive Polymer Capacitors are designed to operate within the limits of the environmental conditions specified for each series. If operated continuously at their maximum temperature and / or humidity limit, or beyond these limits, capacitors may exhibit a parametric shift in capacitance and increases in ESR. These changes may occur earlier if the specified environmental conditions are exceeded. Similarly, their normal operational time period will be significantly extended if their general duty cycle includes operation below maximum temperature within humidity controlled environments. Careful attention should be paid to maximum temperature with associated high humidity environments as well as voltage derating, ripple current and current surges.

Please reference the KYOCERA AVX Conductive Polymer Capacitor Guidelines for more information or contact factory for application assistance

CAPACITANCE AND RATED VOLTAGE RANGE (LETTER DENOTES CASE SIZE)

Capac	itance		Rated Voltage DC (V _R) @ 85°C						
μF	Code	4V (g)	6.3V (j)	10V (A)	16V (C)	20V(D)	25V(E)	Code	
1.0	105			Р	A,M,P	А	A,M,P	A	
1.5	155				A			E	
2.2	225		Р	A,M,P	A,M			J	
3.3	335			A,P	A		A	N	
4.7	475		A,M,P	A,M,P	A	А	A	S	
6.8	685		Р	А	A			W	
10	106	Р	A,M,P	A,M,P	A			а	
15	156		Р	А				е	
22	226	M, P	A,M,P	А	A			j	
33	336	A	A,M	А				n	
47	476		A					S	
100	107	А						ā	

Released ratings

Note: Voltage ratings are minimum values. KYOCERA AVX reserves the right to supply higher volage ratings in the same case size, to the same reliability standards.

RATINGS & PART NUMBER REFERENCE

Part No.	Case Size	Capacitance (µF)	Rated Voltage (V)	Maximum Operating Temp. (°C)	DCL Max. (µA)	DF Max. (%)	Impedance @100kHz (Ω)	MSL			
4 Volt											
TCP0G106M8R	Р	10	4	125	0.5	20	9.3	1			
TCM0G226M8R	M	22	4	125	0.9	20	9	1			
TCP0G226M8R	Р	22	4	125	0.9	20	7.7	1			
TCA0G336M8R	A	33	4	125	1.3	10	3.5	1			
TCA0G107M8R	A	100	4	125	4.0	30	3	1			
	6.3 Volt										
TCP0J225M8R	Р	2.2	6.3	125	0.5	20	17.5	1			
TCA0J475M8R	A	4.7	6.3	125	0.5	8	4.9	1			
TCM0J475M8R	M	4.7	6.3	125	0.5	20	9	1			
TCP0J475M8R	Р	4.7	6.3	125	0.5	20	11.8	1			
TCP0J685M8R	Р	6.8	6.3	125	0.5	20	9.3	1			
TCA0J106M8R	A	10	6.3	125	0.6	8	4	1			
TCM0J106M8R	M	10	6.3	125	0.6	20	9	1			
TCP0J106M8R	Р	10	6.3	125	0.6	20	8.3	1			
TCP0J156M8R	Р	15	6.3	125	0.9	20	7.7	1			
TCA0J226M8R	A	22	6.3	125	1.4	14	3.5	1			
TCM0J226M8R-V1	M	22	6.3	125	13.0	30	9	1			
TCP0J226M8R	P	22	6.3	125	1.4	25	5	1			
TCA0J336M8R	A	33	6.3	125	2.1	12	3.2	1			
TCM0J336M8R-V1	M	33	6.3	125	208.0	30	9	1			
TCA0J476M8R	A	47	6.3	125	3.0	18	3.2	1			
			10 \	/olt							
TCP1A105M8R	P	1.0	10	125	0.5	10	17.5	1			
TCA1A225M8R	A	2.2	10	125	0.5	6	5.6	1			
TCM1A225M8R	M	2.2	10	125	0.5	20	13.5	1			

KYDICER8 The Important Information/Disclaimer is incorporated in the catalog where these specifications came from or available online at www.kyocera-avx.com/disclaimer/ by reference and should be reviewed in full before placing any order.

TDS-PTNO-0044 | Rev 1

RATINGS & PART NUMBER REFERENCE

Part No.	Case Size	Capacitance (µF)	Rated Voltage (V)	Maximum Operating Temp. (°C)	DCL Max. (µA)	DF Max. (%)	Impedance @100kHz (Ω)	MSL
TCP1A225M8R	Р	2.2	10	125	0.5	20	14.4	1
TCA1A335M8R	A	3.3	10	125	0.5	8	4.9	1
TCP1A335M8R	Р	3.3	10	125	0.5	20	11.8	1
TCA1A475M8R	A	4.7	10	125	0.5	8	4.2	1
TCM1A475M8R	M	4.7	10	125	0.5	20	9	1
TCP1A475M8R	Р	4.7	10	125	0.5	20	9.3	1
TCA1A685M8R	A	6.8	10	125	0.7	8	4	1
TCA1A106M8R	A	10	10	125	1.0	8	3	1
TCM1A106M8R	М	10	10	125	10.0	20	9	1
TCP1A106M8R	Р	10	10	125	1.0	20	7.7	1
TCA1A156M8R	A	15	10	125	1.5	10	3.5	1
TCA1A226M8R	A	22	10	125	2.2	12	3.2	1
TCA1A336M8R	A	33	10	125	3.3	8	1.7	1
			16 \	/olt				
TCA1C105M8R	A	1.0	16	125	0.5	6	7	1
TCM1C105M8R	М	1.0	16	125	0.5	10	15	1
TCP1C105M8R	Р	1.0	16	125	0.5	10	16.1	1
TCA1C155M8R	A	1.5	16	125	0.5	6	5.6	1
TCA1C225M8R	A	2.2	16	125	0.5	6	4.9	1
TCM1C225M8R	М	2.2	16	125	0.5	20	13.5	1
TCA1C335M8R	A	3.3	16	125	0.5	6	4.8	1
TCA1C475M8R	A	4.7	16	125	0.8	6	3.9	1
TCA1C685M8R	A	6.8	16	125	1.1	6	3.8	1
TCA1C106M8R	A	10	16	125	1.6	8	3.5	1
TCA1C226M8R	A	22	16	125	3.5	30	2.3	1
			20 \	Volt				
TCA1D105M8R	A	1.0	20	125	0.5	6	7	1
TCA1D475M8R	A	4.7	20	125	0.9	6	3.9	1
			25 \	/olt				
TCA1E105M8R	A	1.0	25	125	0.5	6	7	1
TCM1E105M8R	М	1.0	25	125	0.5	10	10	1
TCP1E105M8R	Р	1.0	25	125	0.6	20	9.3	1
TCA1E335M8R	A	3.3	25	125	0.8	6	4.8	1

Moisture Sensitivity Level (MSL) is defined according to J-STD-020. All technical data relates to an ambient temperature of +25C.

Capacitance and DF are measured at 120Hz, 0.5RMS with DC bias of 1.5 volts. DCL is measured at rated voltage after 5 minutes. Impedance allowed to move up to 1.25 times catalog limit post mounting.

NOTE: KYOCERA AVX reserves the rights to supply higher voltage rating in the same case size, to the same reliability standards.

The Important Information/Disclaimer is incorporated in the catalog where these specifications came from or available online at www.kyocera-avx.com/disclaimer/ by reference and should be reviewed in full before placing any order.

TDS-PTNO-0044 | Rev 1

🔇 KY<u>OCERa</u>



QUALIFICATION TABLE


тгет	TC series (Temperature range -55°C to +125°C)									
TEST		Condition		Characteristics						
Endurance	Apply rated volta	ge (Ur) at 85°C for	1000brs (for M	Visual examination	no visible damage					
)hrs (for A case) th	· ·	DCL	2x initial limit					
		0Ω. Stabilize at roo	m temperature	ΔC/C	within ±30% of init	ial value (M case), ±	20% (A,P case)			
	for 24 hours befo	ore measuring.		DF	2x initial limit					
				Visual examination	no visible damage					
		90-95% relative hur	,	DCL	2x initial limit					
Humidity		ilize at room tempe		ΔC/C	within ±30% of initial value (M case), ±20% (A,P case)					
	numiality for 24 n	ours before measu	iring.	DF	2x initial limit					
	Step	Temperature°C	Duration(min)		-55°C	+85°C	+125°C			
	1	-55	15							
Temperature	2	+85	15	DCL	n/a	10xIL*	12.5xIL*			
Stability	3 +125 15		ΔC/C	0/-30%	+15/-5%	+20/-5%				
				DF	IL*	IL*	IL*			
	Apply 1 3x rated	voltage (Ur) at 85±2	2°C for	Visual examination	no visible damage					
Surge Voltage	1000 cycles, 300	sec charge and 30s		DCL	2x initial limit					
ourge voltage	resistance 10000).		ΔC/C	±20% of initial limi	t				
				DF	2x initial limit					
	4.17 JIS C 5101-1	1		Visual examination	no visible damage					
Vikustiau	Frequency: 10 to	55 to 10Hz/min.		DCL	initial limit					
Vibration	Amplitude: 1.5mr	m		ΔC/C	within ± 5% of initial value					
	Time: 2hours eac	h in X and Y directi	ions	DF	initial limit					

*Initial Limit

For use outside of recommended conditions and special request, please contact KYOCERA AVX.

Initial measurement max. 1hr after the removal from dry pack or after pretreatment at 85°C for 24 hours.


PACKAGING SPECIFICATIONS



Unit (mm)

Case	A±0.10	B±0.10	W±0.20	E±0.10	F±0.05	P1±0.10	P2±0.05	PO±0.10	DO+0.10/0	t1±0.05	t2±0.10	Standard packaging quantity
А	1.90	3.50	8.00	1.75	3.50	4.00	2.00	4.00	φ1.50	0.25	1.90	2,000 pcs
М	1.00	1.85	8.00	1.75	3.50	4.00	2.00	4.00	φ1.50	0.20	1.00	4,000 pcs
Р	1.55	2.30	8.00	1.75	3.50	4.00	2.00	4.00	φ1.55±0.05	0.25	1.32	3,000 pcs

REEL DIMENSIONS



KUCERE The Important Information/Disclaimer is incorporated in the catalog where these specifications came from or available online at www.kyocera-avx.com/disclaimer/ by reference and should be reviewed in full before placing any order.

TDS-PTNO-0044 | Rev 1