



PCB spring terminal block

Rated current: 20 A

Rated voltage: 300 V

Wire range: 28-12 AWG

Pitch: 7.5 mm

Mounting: Wave soldering



UL/CUL

Use Group	B	C	D
Rate Voltage [V]	300	150	300
Rated Current [A]	20	20	10
Wire Range [AWG]	28~12		
Dielectric Voltage-Withstand	1.6KV		

IEC

Overvoltage Category	III	III	II
Contamination Class	3	2	2
Rated Voltage [V]	500	630	1000
Rated Current [A]	32	32	32
Impulse withstand voltage [KV]	6	6	6
Conductor cross section[solid/flexible] [mm ²]	0.2~4.0		

Material

Insulation Material	PA66
Flame retardant rating	UL94V-0
Conductor Material	Copper alloy
Plating of conductor surface	Sn plated

Other Data

Pitch/Poles [mm]/[P]	7.5/2~24
Stripping Length [mm]	9~10
Screw/Torque(Max)[N.m]	/
Operating temperature [°C]	-40~+105
Soldering temperature	260°C/5S
Pin dimensions [mm]	1.2*0.8
PCB Hole Diameter [mm]	∅1.8

Dimensions

PCB opening diagram

