



PCB spring terminal block

Rated current: 10 A

Rated voltage: 300 V

Wire range: 24-16 AWG

Pitch: 3.5 mm/3.81 mm

Mounting: Reflow soldering



### UL/CUL

Use Group  Rate Voltage [V]	300	-	300	
Rated Current [A]	10	-	10	
Wire Range [AWG]		24~16		
Dielectric Voltage-Withstand		1.6KV		

Overvoltage Category	III	III	П
Contamination Class	3	2	2
Rated Voltage [V]	160	160	320
Rated Current [A]	17.5	17.5	17.5
Impulse withstand voltage [KV]	2.5	2.5	2.5
Conductor cross section[solid/flexible] [mm²]		0.2~1.5	

#### Material



Insulation Material	LCP	
Flame relardant rating	UL94V-0	
Conductor Material	Copper alloy	
Plating of conductor surface	Sn plated	
Other Data		
Pitch/Poles [mm]/[P]	3.5 , 3.81/2~24	
Stripping Length [mm]	7~8	
Screw/Torque(Max)[N.m]	/	
Operating temperature [°C]	-40~+130	
Soldering temperature	285°C/10S	
Pin dimensions [mm]	0.8*0.4	
PCB Hole Diameter [mm]	□1.2	

## Dimensions

# PCB opening diagram

