



416TX

Datasheet

Aiming to create better and safer working environments and life experiences through the products we deliver.



AVCOMM Technologies, Inc

www.avcomm.us

Email: info@avcomm.us

Phone: (713) 933-4534

Address: 333 West Loop North, Suite 460
Houston, TX 77024
United States

Reliable Plug and Play Industrial Ethernet Switch for Automation and Electrical OEM

416TX

Industrial Unmanaged Ethernet Switch

AVCOMM 416TX is a 16-port plug and play fast unmanaged Ethernet switch with reverse polarity protection of AC or DC input for automation and electrical OEM purpose. It has wide operation temperature range, high EMC performance to ensure stable work in harsh industrial environments and supports DIN Rail-mounted to facilitate in various industrial network applications. AVCOMM 416TX is suitable for industrial applications such as industrial automation, intelligent transportation, video surveillance, and electrical OEMs.



Features & Benefits

Fast Ethernet Switching

- Sixteen(16) 10/100BaseT(X) RJ-45 ports
- 8K MAC address table
- Store and forwarding with non-blocking technology

IEEE 802.3u EEE Power Management

- Ultra power consumption efficiency, 19.9W fully loaded
- Energy Efficient Ethernet for low power requirement
- Idle power saving mode for energy efficiency

Rugged Mechanical Design

- Robust design protects from mechanical deformation
- IP40 industrial rating to withstand harsh environments
- Wide operating temperature range -40°C ~ 85°C
- IEC61000-6-2/IEC61000-6-4 heavy industrial EMS

Power protection

- Provide overload protection
- Provide reverse connection protection
- Provide multiple power input options, AC or DC or HV


Ordering Information

Model Name	Description
416TX	16-Port Industrial Unmanaged Ethernet Switch, 16 RJ45 10/100BaseT(X), DIN-Rail, Dual Power Input 10-50VDC, -40°C to +85°C
416TX-AC	16-Port Industrial Unmanaged Ethernet Switch, 16 RJ45 10/100BaseT(X), DIN-Rail, Dual Power Input 90-264VAC, -40°C to +85°C
416TX-HV	16-Port Industrial Unmanaged Ethernet Switch, 16 RJ45 10/100BaseT(X), DIN-Rail, Dual Power Input 90-264VDC, -40°C to +85°C

 Specifications

Technology	
Standard	IEEE 802.3 10Base-T Ethernet
	IEEE 802.3u 100Base-TX Fast Ethernet
	IEEE 802.3x Flow Control and back-pressure
Performance	
Switch Technology	Store and Forwarding Technology with non-blocking
Number of MAC Address	8K
Packet Buffer Memory	3 MB
Backplane bandwidth	11.2 Gbps
Maximum frame length	2 KB
Forwarding rate	148810pps/1488095pps
Interface	
Ethernet Port	16 x 10/100BaseT(x)RJ-45 , Auto Negotiation
System LED	2 x Power: Green On ; 1 x DO Alarm: Red On ;
Ethernet Port LED	Link (Green On), Active (Green Blinking)
Power Input	8-Pin Removable Terminal Connector (V-/N, V+/L, V-/N, V+/L)
Power Requirement	
Input Voltage	12/24/48VDC (10~50VDC) or 110/220VAC(90~264VAC) or 110/220VDC(90~264VDC) , Redundant
Reverse Polarity Protect	Yes
Power Consumption	830mA@24V
Mechanical	
Enclosure Material	Metal
Dimension	70 mmx 150 mm x 120 mm (W x H x D) without DIN Rail Clip
Ingress Protection	IP40
Weight	<1700 g
Installation method	DIN Rail-mounted
Environmental	
Operating Temperature & Humidity	-40°C ~+85°C , 0%~95% Non- Condensing
Storage Temperature	-40°C ~+85°C
MTBF	>2,000,000 hours
Warranty	5 years
Standard	
EMI	FCC Part, CISPR(EN55022)class A
EMS	IEC(EN)61000-4-2(ESD) IEC(EN)61000-4-3(RS) IEC(EN)61000-4-4(EFT) IEC(EN)61000-4-5(Surge) IEC(EN)61000-4-6(CS) IEC(EN)61000-4-8 IEC 60068-2-27(Shock) IEC 60068-2-32(Freefall)

Function interface



Installation dimensions

