

SPECIFICATION SHEET

SPECIFICATION SHEET NO.	R0412- CRRCR06JB12RS1				
DATE	Apr. 12, 2024				
REVISION	A1 Updated With Most Recent Data				
DESCRIPTION AND	General purpose Chip Resistors, 1206 (3216 Metric), RCR06 Series, Dimension L3.10*W1.60*H0.60mm, 2 Terminations,				
MAIN PARAMETRICS	Tolerance: $\pm 5.0\%$, Resistance 12 ohm, Dissipation Max. 1/4W @ 70°C, Temperature Coefficient Rate (TCR) Max. ± 200 ppm/° C Operating Temp. Range -55° C ~+155° C				
	Package in Tape/Reel, 5,000pcs/Reel RoHS/RoHS III compliant and HF				
CUSTOMER					
CUSTOMER PART NO.					
CROSS REF. PART NO.					
ORIGINAL MFG/PART NO.	Aillen/RCR06JB12R				
PART CODE	CRRCR06JB12RS1				

VENDOR APPROVE

Issued/Checked/Approved







DATE: Apr. 12, 2024

CUSTOMER APPROVE	
DATE:	
	_



GENERAL PURPOSE CHIP RESISTORS RCR06 SERIES

DESCRIPTION

The LEAD FREE resistors are constructed in a high grade ceramic body (aluminum oxide). Internal metal electrodes are added at each end and connected by a LEAD FREE resistive paste that is applied to the top surface of the substrate. The composition of the paste is adjusted to give the approximate resistance required and the value is trimmed to nominated value within tolerance which controlled by laser trimming of this resistive layer. The resistive layer is covered with a BLACK protective coat. Finally, the two external end terminations are added. For ease of soldering the outer layer of these end terminations is a Tin (LEAD FREE) alloy.

MAIN FEATURE

- High Reliability And Stability
- · Reduced Size Of Final Equipment
- · Lower Assembly Costs
- · Higher Component And Equipment Reliability
- · RoHS exemption free and Lead free products

ROHS COMPLIANT HF

APPLICATION

- · Consumer Electrical Equipment
- EDP, Computer Application
- Telecom Application
- Automotive Application

HOW TO ORDER

Please indicate pat code OR custom parameters code and send us your RFQ by E-mail



GENERAL PURPOSE CHIP RESISTORS RCR06 SERIES

PART CODE GUIDE



CODE	NAME	KEY SPECIFICATION OPTION
CRRCR	Product code	General purpose Chip Resistors
06	Size Code	0402 (1005): L1.00*W0.50mm; 0603 (1608): L1.60*W0.80mm; 0805 (2012): L2.00*W1.25mm; 1206 (3216:) L3.10*W1.60mm;
		1210 (3225): L3.10*W2.60mm
J	Resistance Range	P: Jumper; B: +/-0.1%; D: +/-0.5%; F: +/-1%; J: +/-5%
	Tolerance Code	
В	Package Code	A: 4Kpcs/7"Reel; B:5kpcs/7"Reel; C:10kpcs/7"Reel; M:15kpcs/7"Reel; D:10kpcs/10"Reel; E:20kpcs/10"Reel
12R	Resistance value	0R: 0ohm; 1R2: 1.2ohm; 12R: 12ohm; 20R: 20ohm; 51R: 51ohm;
	code	240R: 240ohm; 390R: 390ohm; 1K:1Kohm; 2K: 2Kohm; 3K9: 3.9Kohm; 13K7:
		13.7Kohm; 62K: 62Kohm; 100K: 100Kohm; 118K: 118Kohm;
		1M: 1.0Mohm; 2M: 2Mohm
S1	Internal control	Custom letter A~Z, a-z or digits (0-9)
	code,	



GENERAL PURPOSE CHIP RESISTORS RCR06 SERIES


DIMENSION (Unit: mm)





General Marking: Blank

RCR06 series



Item	Dimension				
L	3.10±0.10				
W	1.60±0.10				
Т	0.60±0.15				
Тb	0.45±0.20				
Τt	0.50±0.20				

Resistors Construction For Reference



NextGen Components, Inc.



GENERAL PURPOSE CHIP RESISTORS RCR06 SERIES

GENERAL ELECTRONICAL CHARACTERISTICS

	Item	Unit	Symbol	Characteristic	Condition
Pro	Product Name		CRRCR	General purpose Chip Resistors	
	Size		06	RCR06 Series,	
				L3.10*W1.60*H0.60mm	
Resis	tance Range	Ω		12	
Resista	nce Tolerance	%	J	+/-5	
TCR	R≥1MΩ	ppm/°C		≤±200	Resistance
	1MΩ > R > 10Ω			≤±100	Tolerance:±1%
	R≤10Ω			-300~+500	
TCR	TCR R≥1MΩ			≤±200	Resistance
	1MΩ > R > 10Ω			≤±200	Tolerance:±5%
	R≤10Ω			-300~+500	
Max.	Dissipation	W		1/4	@ Tamb=70°C
Operating Temperature		°C		-55 ~+155	
Max. Ope	Max. Operation Voltage			200	@DC or RMS
Max. Ov	Max. Overload Voltage			400	@DC or RMS

Note

- 1) This is the maximum voltage that may be continuously supplied to the resistor element, see "IEC publication 60115-8"
- 2) Max. Operation Voltage : So called RCWV (Rated Continuous Working Voltage) is determined by $RCWV = \sqrt{Rated\ Power \times Resistance\ Value} \text{ or Max. RCWV listed above, whichever is lower.}$
- 3) The resistance of Jumper is defined as max. 0.05Ω , Test condition for jumper (0 Ω)

Item	Unit	Symbol	Characteristic	Condition
Power Rating At 70°C	W		1/4	
Max. Resistance	mΩ		50	
Rated Current	А		2.0	
Peak Current	А		5.0	
Operating Temperature	°C		-55 ~+155	

GENERAL PURPOSE CHIP RESISTORS RCR06 SERIES

PRODUCT CHARACTERIZATION

Standard values of nominal resistance are taken from the E24 & E96 series for resistors with a tolerance Of +/-0.1%, +/-0.5%, +/-1% & +/-5%, The values of the E24/E96 series are in accordance with "IEC publication 60063"

DERATING

The power that the resistor can dissipate depends on the operating temperature; see Fig.1




Fig 1 Maximum dissipation in percentage of rated power as a function of the ambient temperature for RCR06

MOUNTING

Due to their rectangular shapes and small tolerances, Surface Mountable Resistors are suitable for handling by automatic placement systems. Chip placement can be on ceramic substrates and printed-circuit boards (PCBs). Electrical connection to the circuit is by individual soldering condition. The end terminations guarantee a reliable contact.

NextGen Components, Inc.

GENERAL PURPOSE CHIP RESISTORS RCR06 SERIES

REFLOW SOLDERING CONDITION

The robust construction of chip resistors allows them to be completely immersed in a solder bath of 260 °C for 10 seconds. Therefore, it is possible to mount Surface Mount Resistors on one side of a PCB and other discrete components on the reverse (mixed PCBs). Surface Mount Resistors are tested for solderability at 235 °C during 2 seconds. The test condition for no leaching is 260°C for 30 seconds. Typical examples of soldering processes that provide reliable joints without any damage are given in Fig 2.




Fig 2. Infrared soldering profile for Chip Resistors


LEAD content: below 100ppm with reference to IEC62321, determination of LEAD by ICP-AES



GENERAL PURPOSE CHIP RESISTORS RCR06 SERIES

TEST AND REQUIREMENT (JIS C 5201-1: 1998)

TEST	PROCEDURE / TEST METHOD	REQUIREMENT		
		Resistor	0Ω	
DC resistance Clause 4.5	DC resistance values measured at the test voltages specified below : $<10\Omega@0.1V,<100\Omega@0.3V,<1K\Omega@1.0V,<10K\Omega@3V,\\<100K\Omega@10V,<1M\Omega@25V,<10M\Omega@30V$	Within the specified tolerance	<50mΩ	
Temperature Coefficient of Resistance(T.C.R) Clause 4.8	Natural resistance change per change in degree centigrade. t1:20°C+5°C-1°C R1: Resistance at reference temperature R2: Resistance at test temperature	Refer to "QUICK REFERENCE DATA"	N/A	
Short time overload (S.T.O.L) Clause 4.13	Permanent resistance change after a 5second application of a voltage 2.5 times RCWV or the maximum overload voltage specified in the above list, whichever is less.	1% tol.:Δ R/R max. ±(1%+0.10Ω) 5% tol.:Δ R/R max. ±(2%+0.10Ω)	<50mΩ	
Resistance to soldering heat(R.S.H) Clause 4.18	Un-mounted chips completely immersed for 10±1second in a SAC solder bath at 260C±5°C	1% tol.:Δ R/R max. \pm (0.5%+0.10 Ω) 5% tol.:Δ R/R max. \pm (1%+0.10 Ω)	<50mΩ	
Solderability Clause 4.17	Un-mounted chips completely immersed for 2±0.5second in a SAC solder bath at 235C±5C	95% coverage min., g		
Temperature cycling Clause 4.19	30 minutes at -55°C±3°C, 2~3 minutes at 20°C+5°C-1°C, 30 minutes at +155°C±3°C, 2~3 minutes at 20°C+5°C-1°C, total 5 continuous cycles	1% tol.:Δ R/R max. \pm (0.5%+0.10Ω) 5% tol.:Δ R/R max. \pm (1%+0.10Ω)	<50mΩ	
Damp Heat (Load life in humidity) Clause 4.24	1000 +48/-0 hours, loaded with RCWV or Vmax in humidity chamber controller at 40°C±2°C and 90~95% relative humidity.	1% tol.:Δ R/R max. ±(1%+0.10Ω) 5% tol.:Δ R/R max. ±(2%+0.10Ω)	<50mΩ	



GENERAL PURPOSE CHIP RESISTORS RCR06 SERIES

TEST AND REQUIREMENT (JIS C 5201-1: 1998)


TEST	PROCEDURE / TEST METHOD	REQUIREMENT	
		Resistor	0Ω
Load Life (Endurance) Clause 4.25	1000+48/-0 hours; loaded with RCWV or Vmax in chamber controller 70±2°C, 1.5 hours on and 0.5	1% tol.:Δ R/R max. ±(1%+0.10Ω) 5% tol.:Δ R/R max.	<50mΩ
	hours off	±(2%+0.10Ω)	
Bending strength	Resistors mounted on a 90mm glass epoxy resin	1% tol.: ΔR/R max. ±(0.5%+0.10Ω)	<50mΩ
Clause 4.33	PCB(FR4), bending once 3mm for 10sec, 5mm for WR04	5% tol.: ΔR/R max. ±(1%+0.10Ω)	
Adhesion	Pressurizing force: 5N, Test time: 10±1sec.	No remarkable damage or removal of the terminations	
Clause 4.32			



GENERAL PURPOSE CHIP RESISTORS RCR06 SERIES


REEL DIMENSION (Unit: mm)

7": 5,000Ppcs/Reel



Code	Dimension 7"		
А	178+/-2.0		
В	60.0 +/-1.0		
С	13.0+/-0.20		
D	9.0+/-0.5		

TAPE DIMENSION (Unit: mm)



Code	Dimension		
А	3.60±0.20		
В	2.00±0.20		
W	8.00±0.30		
F	3.50±0.20		
E	1.75±0.10		
P 1	4.00±0. 10		
P0	4.00±0.10		
ФД	1.50+0.10		
Т	1.0 Max.		

TAPING QUANTITY AND TAPE MATERIAL

Таре	Paper Tape						Embossed Tape	Bulk Cassette
		4 mm Pitch		2	2 mm Pitch	4 mm Pitch		
Reel Size	7"	10"	13"	7" 10" 13"			7"	
RCR06	5000	10000	20000	-	-	-	-	5000




GENERAL PURPOSE CHIP RESISTORS RCR06 SERIES

PERFORMANCE OF TAPING

Strength of Carrier Tape and Top Cover Tape

Carrier Tape: When a tensile force 1.02kgf is applied in the direction of unreeling the tape, the tape shall withstand this force. Top cover Tape: When a tensile force 1.02kgf is applied to the tape, the tape shall withstand this force. Peel Force of Top Cover Tape

Unless otherwise specified, the peel force of top cover tape shall be 10.2 to 71.4 g f when the top cover tape is pulled at a speed of 300mm/min with the angle between the taped during peel and the direction of unreeling maintained at 165 to 180°as illustrated in Fig.



NextGen Components, Inc.



GENERAL PURPOSE CHIP RESISTORS RCR06 SERIES

ROHS COMPLIANCE

 The levels of RoHS restricted materials in this product are below the maximum concentration values (also referred to as the threshold limits) permitted for such substances, or are used in an exempted application, in accordance with EU RoHS Directive (EU) 2015/863 EC (RoHS3). RoHS Test Report for this product can be obtained can be obtained at Download Center.

REACH COMPLIANCE

REACH substances of high concern (SVHCs) information is available for this product. Since the European
Chemical Agency (ECHA) has published notice of their intent to frequently revise the SVHC listing for the
foreseeable future, REACH Test Report for this product can be obtained can be obtained at Download Center.

IMPORTANT NOTES AND DISCLAIMER

- All Product parametric performance is indicated in the Electrical Characteristics for the listed herein test
 conditions, unless otherwise noted. Product performance may not be indicated by the Electrical
 Characteristics if operated under different conditions.
- 2. NextGen Component, Inc (*NextGen*) reserves the right to make changes to this document and its products and specifications at any time without notice. Customers should obtain and confirm the latest product information and specifications before final design, purchase or use.
- NextGen makes no warranty, representation or guarantee regarding the suitability of its products for any
 particular purpose, not does NextGen assume any liability for application assistance or customer product
 design.
- 4. NextGen does not warrant or accept any liability with products which are purchased or used for any unintended or unauthorized application. No license is granted by implication or otherwise under any intellectual property rights of NextGen.
- NextGen products are not authorized for use as critical components in life support devices or systems without express written approval by NextGen.
- 6. NextGen requires that customers first obtain an RMA (Returned Merchandise Authorization) number prior to returning any products. Returns must be made within 30 days of the date of invoice, be in the original packaging, unused and like-new condition. At the time of quoting or purchasing, a product may say that it is Non-Cancelable/ Non-Returnable (NCNR). These products are not returnable and not refundable.