
# mosaic-T Compact multi-frequency GNSS timing receiver module





Septentrio mosaic-T<sup>TM</sup> is a **multi-band**, **multi-constellation GNSS timing receiver** designed specifically for providing the highest security and availability for critical infrastructure and other applications where resilient timing is essential. Mosaic-T<sup>TM</sup> is a low power surface-mount **module** with a

Mosaic-1<sup>TM</sup> is a low power surface-mount **module** with a wide array of interfaces including a dedicated timing input for time and frequency synchronization. It offers superior availability by tracking all Global Navigation Satellite System constellations (GNSS) and their current and future signals. With unique **built-in AIM+ technology** for anti-jamming, anti-spoofing and **interference mitigation**, Septentrio offers a highly resilient and precise timing receiver in a very small form factor.

# **KEY FEATURES**

- Accurate and resilient with dedicated timing features
- All-in-view satellite tracking: multi-constellation, multi-frequency
- Dedicated inputs for clock and frequency synchronisation
- OSNMA Support
- Highly secure against jamming and spoofing with AIM+ unique interference mitigation technology
- Industry-leading ultra-low power consumption
- Easy-to-integrate

# BENEFITS

# Top performance without compromises

The best of both worlds: small size with solid performance. Mosaic-T<sup>™</sup> offers a high-precision solution for time and frequency synchronization under challenging conditions such as during GNSS jamming or spoofing. It offers unmatched resilience thanks to its all-constellation multi-frequency capabilities and AIM+ technology.

# More compact than ever

Sized at only 31 x 31 x 4 mm and weighing no more than 7g, mosaic-T<sup>TM</sup> offers unparalleled size to performance ratio.

# Meant for automated assembly

The mosaic-T<sup>™</sup> module is designed for high volume automated assembly lines with minimal amount of additional components required. All interfaces, commands and data messages are fully documented. The complete RxTools software suite is also included with mosaic-T<sup>™</sup>. It enables quick and easy receiver configuration, data logging and analysis.

# Advanced technologies inside

Septentrio's GNSS+ toolset enables accuracy and reliability in the toughest conditions with:

- AIM+ the most advanced on-board interference mitigation technology on the market (mitigating both narrow and wide band chirp jammers).
- **LOCK+** for robust tracking despite mechanical shocks and vibrations.
- ► **APME+** multipath mitigation to distinguish direct signals from those reflected off nearby structures.
- IONO+ provides advanced protection against ionospheric disturbances.

# Your positioning cornerstone

# **FEATURES**

# **GNSS technology**

448 hardware channels for simultaneous tracking of all visible supported satellite signals:

- GPS: L1C/A, L1PY, L2C, L2PY, L5 GLONASS: L1CA, L2CA, L3 CDMA
- ▶ Beidou: B1I, B1C, B2a, B2I, B3
- Galileo: E1, E5a, E5b, E5 AltBoc
- ▶ QZSS: L1C/A, L2C, L5
- ▶ NavIC: L5
- SBAS: Egnos, WAAS, GAGAN, MSAS, SDCM (L1, L5)

# Septentrio's patented GNSS+ technologies

- ▶ AIM+ interference monitoring and mitigation (narrow band, wide band, chirp jammers)
- IONO+ advanced scintillation mitigation
- > APME+ a posteriori multipath estimator for code and phase multipath mitigation
- **LOCK+** superior tracking robustness under heavy mechanical shocks or vibrations
- RAIM+ receiver autonomous integrity monitoring

**OSNMA** Support

4 constellations

#### **Protocols**

Septentrio Binary Format (SBF) NMEA 0183, v2.3, v3.03, V4.0

#### Interfaces

4 UART (LVTTL, up to 4 Mbps) Ethernet (RMII/MDIO), 10/100 Mbps USB device (2.0, HS) SDIO (mass storage) 2 GPIO user programmable 2 Event markers 1 Configurable PPS out<sup>4</sup> Clock sync input Frequency sync input (10 MHz)

# PERFORMANCE

Time precision			
xPPS out <sup>4</sup>		5 ns	
xPPS out with SBAS		2 ns	
Event accuracy		< 20 ns	
Positioning modes acc	uracy <sup>1,2</sup>		
	Horizontal	Vertical	
Standalone	1.2 m	1.9 m	
SBAS	0.6 m	0.8 m	
Velocity accuracy		3 cm/s	
Maximum update rate			
Position		10 Hz	
Latency <sup>3</sup>		<10 ms	
Time to first fix			
Cold start⁵		< 45 s	
Warm start <sup>6</sup>		< 20 s	
Re-acquisition		1 s	
Tuesdaine neuformenes		a a lal)	

#### Tracking performance (C/N0 threshold)

Tracking	20 dB-Hz
Acquisition	33 dB-Hz
Firmware	
Free product lifetime upgrades	

#### Fir

Free product lifetime upgrades

# PHYSICAL AND ENVIRONMENTAL

# Package

Туре	SMT solderable land grid array
Size	31 x 31 x 4 mm / 1.29 x 1.29 x 0.15 in
Weight	6.8 g / 0.24 oz

## **Electrical**

I		
	Antenna pre-amplification range	15-50 dB
	Antenna bias voltage	3.0-5.5 V Build-in current limit (150 mA)
	Input voltage	3.3 VDC
	Power consumption	0.6 W typ 1.1 W max
	Environmental	
	Operating temp	-40 to 85° C
		-40 to 185° F

Storage temp	-55 to 85° C
	-67 to 185° F
Humidity	5% - 95% (non-condensing)
Vibration	MII-STD-810G

Certification



CE, RoHS, WEEE, ISO 9001-2015

- <sup>1</sup> Open sky conditions
- <sup>2</sup> RMS levels
- 3 99.9%
- <sup>4</sup> Incl. software compensation of sawtooth effect
- <sup>5</sup> No information available (no almanac, no approx position)
- <sup>6</sup> Ephemeris and approx. position known

VIS 66/06/2022

# **EMEA**

Greenhill Campus (HQ) Interleuvenlaan 15i 3001 Leuven, Belgium

#### Espoo, Finland

#### **Americas** Suite 200

23848 Hawthorne Blvd Torrance, CA 90505, USA

septentrio.com/contact

# **Asia-Pacific**

Shanghai, China Yokohama, **Japan** Seoul, Korea

septentrio.com





