

SPECIFICATION SHEET

SPECIFICATION SHEET NO.	R0412- CRCP06FB39KS01				
DATE	Apr. 12, 2024				
REVISION	A1 Updated With Most Recent Data				
DESCRIPTION AND MAIN PARAMETRICS	High power Chip Resistors, 1206 (3216 Metric), CP06 Series, Dimension L3.10*W1.60*H0.55mm, 2 Terminations, Tolerance: \pm 1.0%, Resistance 39K ohm, Dissipation Max. 1/2W @ 70°C, Temperature Coefficient Rate (TCR) Max. \pm 100ppm/° C Operating Temp. Range -55° C ~+155° C Package in Tape/Reel, 5,000pcs/Reel RoHS/RoHS III compliant and HF				
CUSTOMER					
CUSTOMER PART NO.					
CROSS REF. PART NO.					
ORIGINAL MFG/PART NO.	Aillen/CP06FB39K				
PART CODE	CRCP06FB39KS	501			

VENDOR APPROVE

Issued/Checked/Approved







DATE: Apr. 12, 2024

CUSTOMER APPROVE	
DATE:	



HIGH POWER CHIP RESISTORS CP06 SERIES

DESCRIPTION

The resistors are constructed in a high grade ceramic body (aluminum oxide). Internal metal electrodes are added at each end and connected by a resistive paste that is applied to the top surface of the substrate. The composition of the paste is adjusted to give the approximate resistance required and the value is trimmed to within tolerance by laser cutting of this resistive layer. The resistive layer is covered with a protective coat. Finally, the two external end terminations are added. For ease of soldering the outer layer of these end terminations is a Tin (lead free) alloy.

MAIN FEATURE

- High power rating and compact size
- · High reliability and stability
- · Reduced size of final equipment
- RoHS compliant and Lead free products
- Flame Retardant

ROHS

APPLICATION

- Power supply / PDA
- Digital meter / PC
- Automotives / Battery charger
- DC-DC power converter

HOW TO ORDER

· Please indicate pat code OR custom parameters code and send us your RFQ by E-mail



HIGH POWER CHIP RESISTORS CP06 SERIES

PART CODE GUIDE



CODE	NAME	KEY SPECIFICATION OPTION
CRCP	Product code	High power Chip Resistors
06	Size Code	0402 (1005): L1.00*W0.50mm; 0603 (1608): L1.60*W0.80mm;
		0805 (2012): L2.00*W1.25mm; 1206 (3216) : L3.10*W1.60mm;
		1210 (3225:) L3.20*W2.60mm; 2512 (6432): L6.30*W3.10mm;
F	Resistance Range	P: Jumper; B: +/-0.1%; D: +/-0.5%; F: +/-1%; J: +/-5%
	Tolerance Code	
В	Package Code	A: 4Kpcs/7"Reel; B:5kpcs/7"Reel; C:10kpcs/7"Reel; M:15kpcs/7"Reel;
		D:10kpcs/10"Reel; E:20kpcs/10"Reel
39K	Resistance value	0R: 0ohm; R75: 0.75ohm; 10R: 10ohm; 20R: 20ohm; 51R: 51ohm;
	code	240R: 240ohm; 390R: 390ohm; 1K:1Kohm; 10K: 10Kohm; 10K5: 10.5Kohm;
		13K7: 13.7Kohm; 39K: 39Kohm; 100K: 100Kohm; 118K: 118Kohm;
		1M: 1.0Mohm; 1M2: 1.2Mohm
S01	Internal control	Custom letter A~Z, a-z or digits (0-9)
	code,	




HIGH POWER CHIP RESISTORS CP06 SERIES

DIMENSION (Unit: mm)

Image for reference

CP06 series




General Marking:


3-digits or 4-digits marking
*Each resistor is marked with
a three or four digits code on
the protective coating to
designate the nominal
resistance value

Item	Dimension				
L	3.10±0.15				
W	1.60±0.15				
Т	0.55±0.10				
T b	0.50±0.25				
Τt	0.50±0.25				

Resistors Construction For Reference



Recommended Solder Pad



Item	Dimension	
W	2.0~2.4	
L	4.4~5.0	
D	1.2~1.8	3

4/12/2024



HIGH POWER CHIP RESISTORS CP06

GENERAL ELECTRONICAL CHARACTERISTICS

Item		Unit	Symbol	Characteristic	Condition
Pro	Product Name		CRCP	High power Chip Resistors	
	Size		06	CP06 Series,	
				L3.10*W1.60*H0.55mm	
Resis	stance Range	Ω		39K	
Resista	ance Tolerance	%	F	+/-1	
TCR	0.02 ~ 0.043Ω	ppm/°C		≤±1000	
	0.047 ~ 0.0976Ω			≤±200	
	0.1 ~ 0.43Ω			≤±100	
	0.47 ~ 0.976Ω			≤±100	
	1~ 10Ω			≤±200	
	≥10Ω			≤±100	
Max	. Dissipation	W		1/2	@ Tamb=70°C
Operati	ng Temperature	°C		-55 ~+155	
Max. Op	peration Voltage	V		200	@DC or RMS
Max. O	verload Voltage	V		400	@DC or RMS


Note

- 1) This is the maximum voltage that may be continuously supplied to the resistor element, see "IEC publication 60115-8"
- 2) Max. Operation Voltage: So called RCWV (Rated Continuous Working Voltage) is determined by

RCWV = $\sqrt{Rated\ Power \times Resistance\ Value}$ or Max. RCWV listed above, whichever is lower.

3) Test condition for jumper (0 Ω)

Item	Unit	Symbol	Characteristic	Condition
Power Rating At 70°C	W		1/2	
Max. Resistance	mΩ		20	
Rated Current	А		5.0	
Peak Current	А		12.5	
Operating Temperature	°C		-55 ~+155	



HIGH POWER CHIP RESISTORS CP06

PRODUCT CHARACTERIZATION

Standard values of nominal resistance are taken from the E24 & E96 series for resistors with a tolerance Of +/-0.1%, +/-0.5%, +/-1% & +/-5%, The values of the E24/E96 series are in accordance with "IEC publication 60063"

DERATING

The power that the resistor can dissipate depends on the operating temperature; see Fig.1





Fig 1 Maximum dissipation in percentage of rated power as a function of the ambient temperature

MOUNTING

Due to their rectangular shapes and small tolerances, Surface Mountable Resistors are suitable for handling by automatic placement systems. Chip placement can be on ceramic substrates and printed-circuit boards (PCBs). Electrical connection to the circuit is by individual soldering condition. The end terminations guarantee a reliable contact.



HIGH POWER CHIP RESISTORS CP06

REFLOW SOLDERING CONDITION

The robust construction of chip resistors allows them to be completely immersed in a solder bath of 260 °C for 10 seconds. Therefore, it is possible to mount Surface Mount Resistors on one side of a PCB and other discrete components on the reverse (mixed PCBs). Surface Mount Resistors are tested for solderability at 235 °C during 2 seconds. The test condition for no leaching is 260°C for 30 seconds. Typical examples of soldering processes that provide reliable joints without any damage are given in Fig 2.




Fig 2. Infrared soldering profile for Chip Resistors



HIGH POWER CHIP RESISTORS CP06

TEST AND REQUIREMENT (JIS C 5201-1: 1998)

TEST	PROCEDURE / TEST METHOD	
Temperature Coefficient of Resistance(T.C.R) Clause 4.8	Natural resistance change per change in degree centigrade. $\frac{R_2-R_1}{R_1(t_2-t_1)}\times 10^6~(\text{ppm/°C})$ t1 : 20°C+5°C-1°C	Refer to quick reference data for T.C.R specification
Short time overload	R1: Resistance at reference temperature R2: Resistance at test temperature 5.0× Rated power or Max. Overload Voltage for 5 sec.	Δ R/R max. J:≦ ±(2%+0.1Ω)
(S.T.O.L) Clause 4.13	Measure resistance after 30 minutes	B,D, F:≦ ±(1%+0.05Ω)
Resistance to soldering heat(R.S.H) Clause 4.18	Un-mounted chips completely immersed for 10±1second in a SAC solder bath at 260°C±5°C	Δ R/R max. J: \leq ±(1%+0.1 Ω) B,D, F: \leq ±(0.5%+0.05 Ω) No visible damage
Solderability Clause 4.17	Un-mounted chips completely immersed for 2±0.5 second in a SAC solder bath at 235°C±5°C	Good tinning (>95% covered) No visible damage
Clause 4.18 Leach Test	Un-mounted chips completely immersed for 60±1second in a solder bath at 260°C±5°C	Ditto
Temperature cycling Clause 4.19	30 minutes at -55°C±3°C, 2~3 minutes at 20°C+5°C-1°C, 30 minutes at +155°C±3°C, 2~3 minutes at 20°C+5°C-1°C, total 5 continuous cycles	Δ R/R max. $J{\le}\pm(1\%{+}0.1\Omega)$ $\label{eq:beta}$ B,D,F ${\le}\pm(0.5\%{+}0.05\Omega$) No visible damage
Damp Heat (Load life in humidity) Clause 4.24	1000 +48/-0 hours, loaded with RCWV or Vmax in humidity chamber controller at 40°C±2°C and 90~95% relative humidity, 1.5hours on and 0.5 hours off	Δ R/R max. J \leq ±(3%+0.1 Ω) B,D,F \leq ±(1%+0.05 Ω) No visible damage
Load life (endurance) JISC5201-1: 1998 Clause 4.25	1000 +48/-0 hours, loaded with RCWV or Vmax in chamber controller 70±2°C, 1.5 hours on and 0.5 Hours off	Δ R/R max. J \leq ±(3%+0.1 Ω) B,D,F \leq ±(1%+0.05 Ω) No visible damage
Bending strength Clause 4.33	Resistors mounted on a 90mm glass epoxy resin PCB(FR4); bending: 2 mm(2512;2010) 3mm(1206), once for 10 seconds	Δ R/R max. $J{\le}\pm(1\%{+}0.1\Omega)$ $B,D,F{\le}\pm(0.5\%{+}0.05\Omega~)$ No visible damage




HIGH POWER CHIP RESISTORS CP06 SERIES

TEST AND REQUIREMENT (JIS C 5201-1: 1998)

TEST	PROCEDURE / TEST METHOD	REQUIREMENT
Adhesion Clause 4.32	Pressurizing force: 5N, Test time: 10±1sec.	No remarkable damage or removal of the terminations
Insulation Resistance Clause 4.6	Apply the maximum overload voltage (DC) for 1minute	R≥10GΩ
Dielectric Withstand Voltage Clause 4.7	Apply the maximum overload voltage (AC) for 1 minute	No breakdown or flashover

STORAGE AND HANDLING CONDITIONS


- 1. Products are recommended to be used up within two years since operation date as ensured shelf life. Check solderability in case shelf life extension is needed.
- 2. To store products with following condition: Temperature : 5 to 40°C Humidity: 20 to 70% relative humidity
- 3. Don't store products in a corrosive environment such as sulfide, chloride gas, or acid. It may cause oxidization of electrode, which easily be resulted in poor soldering b.To store products on the shelf and avoid exposure to moisture. Don't expose products to excessive shock, vibration, direct sunlight and so on.



HIGH POWER CHIP RESISTORS CP06


REEL DIMENSION (Unit: mm)

7": 5,000Ppcs/Reel



Code	Dimension 7"	Dimension 10"	Dimension 13"
А	178.0+/-2.0	254.0+/-2.0	330.0+/-2.0
В	60.0 +/-1.0	100 +/-1.0	100+/-1.0
С	13.0+/-0.20	13.0+/-0.20	13.0+/-0.20
D	9.0±0.5	9.0±0.5	9.0±0.5

TAPE DIMENSION (Unit: mm)



Code	Dimension
А	3.60±0.20
В	2.00±0.20
W	8.00±0.30
F	3.50±0.20
E	1.75±0.10
P 1	4.00±0. 10
P0	4.00±0.10
ФD	1.50±0.10
Т	1.0 Max.

TAPING QUANTITY AND TAPE MATERIAL

Таре		Paper Tape					Embossed Tape	Bulk Cassette
		4 mm Pitch		2 mm Pitch			4 mm Pitch	
Reel Size	7"	10"	13"	7"	10"	13"	7"	
CP06	5000	10000	20000	-	-	-	-	5000




HIGH POWER CHIP RESISTORS CP06

PERFORMANCE OF TAPING

Strength of Carrier Tape and Top Cover Tape

Carrier Tape: When a tensile force 1.02kgf is applied in the direction of unreeling the tape, the tape shall withstand this force. Top cover Tape: When a tensile force 1.02kgf is applied to the tape, the tape shall withstand this force. Peel Force of Top Cover Tape

Unless otherwise specified, the peel force of top cover tape shall be 10.2 to 71.4 g f when the top cover tape is pulled at a speed of 300mm/min with the angle between the taped during peel and the direction of unreeling maintained at 165 to 180°as illustrated in Fig.





HIGH POWER CHIP RESISTORS CP06

ROHS COMPLIANCE

 The levels of RoHS restricted materials in this product are below the maximum concentration values (also referred to as the threshold limits) permitted for such substances, or are used in an exempted application, in accordance with EU RoHS Directive (EU) 2015/863 EC (RoHS3). RoHS Test Report for this product can be obtained can be obtained at Download Center.

REACH COMPLIANCE

REACH substances of high concern (SVHCs) information is available for this product. Since the European
Chemical Agency (ECHA) has published notice of their intent to frequently revise the SVHC listing for the
foreseeable future, REACH Test Report for this product can be obtained can be obtained at Download Center.

IMPORTANT NOTES AND DISCLAIMER

- All Product parametric performance is indicated in the Electrical Characteristics for the listed herein test
 conditions, unless otherwise noted. Product performance may not be indicated by the Electrical
 Characteristics if operated under different conditions.
- 2. NextGen Component, Inc (*NextGen*) reserves the right to make changes to this document and its products and specifications at any time without notice. Customers should obtain and confirm the latest product information and specifications before final design, purchase or use.
- NextGen makes no warranty, representation or guarantee regarding the suitability of its products for any
 particular purpose, not does NextGen assume any liability for application assistance or customer product
 design.
- 4. NextGen does not warrant or accept any liability with products which are purchased or used for any unintended or unauthorized application. No license is granted by implication or otherwise under any intellectual property rights of NextGen.
- NextGen products are not authorized for use as critical components in life support devices or systems without express written approval by NextGen.
- 6. NextGen requires that customers first obtain an RMA (Returned Merchandise Authorization) number prior to returning any products. Returns must be made within 30 days of the date of invoice, be in the original packaging, unused and like-new condition. At the time of quoting or purchasing, a product may say that it is Non-Cancelable/ Non-Returnable (NCNR). These products are not returnable and not refundable.