

TAI-SAW TECHNOLOGY CO., LTD.

No. 3, Industrial 2nd Rd., Ping-Chen Industrial District, Taoyuan, 324, Taiwan, R.O.C. TEL: 886-3-4690038 FAX: 886-3-4697532

E-mail: tstsales@mail.taisaw.com Web: www.taisaw.com

Product Specifications Approval Sheet

Product Description: Dielectric Antenna 1592 MHz Size 25×25mm

TST Parts	s No.: TQ0190AA0000					
Customer Parts No.:						
	Customer signature required					
	Company:					
	Division:			_		
	Approved by :			_		
	Date:			_		
(Checked by:	Nina Chen	Nina	chen		
ļ	Approved by:	Kazuma Lee	Kasum	chen a Jee		
[Date:	2023/04/17				

- 1. Customer signed back is required before TST can proceed with sample build and receive orders.
- 2. Orders received without customer signed back will be regarded as agreement on the specifications.
- 3. Any specifications changes must be approved upon by both parties and a new revision of specifications shall be released to reflect the changes.



TAI-SAW TECHNOLOGY CO., LTD.

No. 3, Industrial 2nd Rd., Ping-Chen Industrial District, Taoyuan, 324, Taiwan, R.O.C. TEL: 886-3-4690038 FAX: 886-3-4697532

E-mail: tstsales@mail.taisaw.com Web: www.taisaw.com

Dielectric Antenna 1592 MHz Size 25×25mm

MODEL NO.: TQ0190AA0000 REV. NO.:1.0

A. Maximum Rating:

1. Operating Temperature Range: -40°C to +105°C

2.Storage Temperature Range: -40°C to +105°C

3. Moisture Sensitivity Level: Level 1 (MSL 1)




Electrostatic Sensitive Device (ESD)

B. <u>Electrical Characteristics</u>:


Parameter	Specification	Notes	
Range Of Receiving Frequency	GPS: 1575.42 ±1.023 MHz GLONASS: 1602±5MHz		
Center Frequency	1592MHz ± 3MHz	With 50×50 mm GND Plane	
VSWR	1.5 max	Center Frequency	
Gain at Zenith	GPS: -0.14 dBi typ. GLONASS: 1.75 dBi typ.		
Gain at 10° Elevation			
Axial Ratio			
Impedance	50 Ohm		
Frequency Temperature Coefficient (1f)	-40°C to +105°C	0 ± 20ppm / °C	

C.Frequency Characteristics:

Return Loss, SWR, Impedance, measured on the test fixture.




D. Dimension:






NOTE: X: manufacture location


Ground Plane Dimension














PCB



E. Packing:






F. Recommended Reflow Profile:

Products can be assembled following Pb-free assembly. According to the Standard IPC/JEDEC J-STD-020C, the temperature profile suggested is as follow:

Phase	Profile features	Pb-Free Assembly (SnAgCu)		
PREHEAT	-Temperature Min(Tsmin) -Temperature Max(Tsmax) -Time(ts) form (Tsmin to Tsmax)	150°C 200°C 60-120 seconds		
RAMP-UP	Avg. Ramp-up Rate (Tsmax to TP)	3°C/second(max)		
REFLOW	-Temperature(TL) -Total Time above TL (t L)	217°C 30-100 seconds		
PEAK	-Temperature(TP) -Time(tp)	260°C 5-10 second		
RAMP-DOWN	Rate	6°C / second max.		
Time from 25℃ to Peak Temperature		8 minutes max.		
Composition of	solder paste	96.5Sn/3Ag/0.5Cu		
Solder Paste Mo	odel	SHENMAO PF606-P26		

Note: All the temperature measure point is on top surface of the component, if temperature over recommend, it will make component surface peeling or damage.

The graphic shows temperature profile for component assembly process in reflow ovens



Soldering With Iron:


Soldering condition : Soldering iron temperature 270±10 ℃.

Apply preheating at 120 $^{\circ}$ C for 2-3 minutes. Finish soldering for each terminal within 3 seconds, if soldering iron over temperature 270±10 $^{\circ}$ C or 3 seconds, it will make component surface peeling or damage.

Soldering iron can not leakage of electricity.

TAI-SAW TECHNOLOGY CO., LTD.

Recommendations of the Antenna Foot Print Tables:



Type/Size	А	В	С	D	E	F
25x25x4	7±0.2	2±0.2	25±0.2	0.65±0.2	11.5±0.2	1.35±0.2

Recommendations of the PCB layout:

- a. It needs at least 5mm clearance between LCD panel/shielding and around antenna.
- b. Keep ground area around antenna as symmetrical as possible.
- c. It's can't be obscured metal in top of antenna space.

