

VFA1-118-5M12

12mm Focal Leng

1/1.8" F2.0 C Mount				Working distance	Optical Magnification	1/1.8" Field of View(mm)		
Focal Length	f=12mm			mm		H	V	
F/NO	F=1: 2.0-C			900	0.013X	538.7	404	
Image Size	1/1.8" (7.2*5.32mm)	1/2.5" (5.76*4.32mm)	1/3" (4.8*3.6mm)	850	0.014X	509	381.7	
Angle	H	33.0°	27.2°	22.9°	800	0.015X	479.3	359.5
	V	24.3°	20.7°	17.6°	750	0.016X	449.6	337.2
	D	40.7°	33.3°	28.1°	700	0.017X	419.9	314.9
Object Dimension at MD. 300mm	H	182.5mm	147.3mm	122.7mm	650	0.018X	390.3	292.7
	V	136.9mm	110.5mm	92.0mm	600	0.020X	360.6	270.4
	D	228.2mm	180.1mm	153.5mm	550	0.022X	330.9	248.2
Distortion(TV)	<0.3%			500	0.024X	301.2	225.9	
Focus distance(min)	0.1mm			450	0.026X	271.5	203.6	
Flange back	17.526mm in air			400	0.030X	241.8	181.4	
Back focus	12.5mm in air			350	0.034X	212.1	159.1	
Filter screw size	M25.5*P0.5			300	0.039X	182.4	136.8	
Front/Rear Effective Dia	Front Φ15.2mm Rear Φ6mm			250	0.047X	152.7	114.5	
Mount	C-Mount			200	0.058X	123	92.3	
Temperature Range	-10~+50° C			150	0.077X	93.3	70	
Storage Temperature Range	-20~+60° C			100	0.113X	63.7	47.8	

