

Magnetic buzzer 4x4x2 mm

CS04M02MN17-4000

Revision

Date	Version	Status	Changes	Approver
2017/08/07	V0.1	Draft	First release	LD/LC


1. Scope

This specification applies magnetic buzzer

2. Specification

No.	Item	Unit	Specification	Condition	
1	Oscillation Frequency	Hz	4000	Vo-p=1/2duty, square wave	
2	Operating Voltage	Vo-p	2~4	V A C	
3	Rated Voltage	Vo-p	3	OV	
4	Current Consumption	mA	MAX. 90	at Rated Voltage	
5	Sound Pressure Level	dB	MIN. 70	at 10 cm at Rated Voltage	
6	Coil Resistance	Ω	17±3		
7	Operating Temperature	°C	-20 ~ +70		
8	Storage Temperature	°C	-30 ~ +80		
9	Dimension	mm	4.0 x 4.0 x H2.0	See appearance drawing	
10	Weight (MAX)	gram	0.1		
11	Housing Material		LCP(Black)		
12	Leading Pin		Tin Plated Brass(Sn)	See appearance drawing	
13	Environmental Protection Regulation		RoHS		

3. Appearance drawing




Tol: ± 0.5 Unit: mm

4. Testing method


Standard Measurement conditions

Temperature:25±2°C Humidity:45-65%


Recommended Setting




Recommended Test Circuit



5. Typical Frequency Response Curve



6. Recommend Driving Circuit




The base current Ib should high enough so that it saturates the collector current of the transistor with the CB load.

7. Soldering Condition

(1)Recommendable reflow soldering condition is as follows (Reflow soldering is twice)

Note: It is requested that reflow soldering should be executed after heat of product goes down to normal.



Heat resistant line

(Used when heat resistant reliability test is performed)

(2)Manual soldering

Manual soldering temperature 350° C within 5 sec.

8. Reliability test

NO.	ITEM	TEST CONDITION AND REQUIREMENT
1	High Temperature Test (Storage)	After being placed in a chamber with 70 2°C for 96 hours and then being placed in normal condition for 2 hours.
		Allowable variation of SPL after test: 10dB.
2	Low Temperature Test (Storage)	After being Placed in a chamber with -30 2°C for 96 hours and then
		being placed in normal condition for 2 hours. Allowable variation of SPL after test: 10dB.
		After being Placed in a chamber with 90-95% R.H. at 40 2°C for 96
3	Humidity Test	hours and then being placed in normal condition for 2 hours.
		Allowable variation of SPL after test: 10dB.
		The part shall be subjected to 5 cycles. One cycle shall be consist of:
		1,000
	Temperature Cycle Test	+60°C
		2700
4		+25°C +25°C
		-20°C
		0.5hr 0.5 0.25 0.5 0.5 0.5 0.25
		3hours
		Allowable variation of SPL after test: 10dB.
		Drop on a hard wood board of 4cm thick, any directions ,6 times,
5	Drop Test	at the height of 75cm.
		Allowable variation of SPL after test: 10dB.
	Vibration Test	After being applied vibration of amplitude of 1.5mm with 10 to 55 Hz band of vibration frequency to each of 3 perpendicular directions for
6		2 hours.
		Allowable variation of SPL after test: 10dB.
7	Solderability Test	Lead terminals are immersed in rosin for 5 seconds and then
		immersed in solder bath of +300 5°C for 3 1 seconds.
		90% min. lead terminals shall be wet with solder
		(Except the edge of terminals).
8	Terminal Strength Pulling Test	The force of 9.8N(1.0kg) is applied to each terminal in axial direction for
		10 seconds. No visible damage and cutting off.
		140 visiole damage and cutting on.

TEST CONDITION.

 Standard Test Condition
 : a) Temperature: +5~+35°C
 b) Humidity: 45-85%
 c) Pressure: 860-1060mbar

 一般测试条件
 : a) 温度: +5~+35°C
 b) 湿度: 45-85%
 c) 气压: 860-1060mbar

 Judgment Test Condition
 : a) Temperature: +25 ± 2°C
 b) Humidity: 60-70%
 c) Pressure: 860-1060mbar

 争议时测试条件
 : a) 温度: +25 ± 2°C
 b) 湿度: 60-70%
 c) 气压: 860-1060mbar

9. Packing standard

