

FEATURES


- For surface mounted applications
- Fast reverse recovery time
- Ideal for automated placement

MECHANICAL DATA

- Case: SOD-123W
- Terminals: Solderable per MIL-STD-750, Method 2026
- Approx. Weight: 16mg/0. 00056oz

PINNING

| PIN | DESCRIPTION |
|-----|-------------|
| 1 | Cathode |
| 2 | Anode |



Absolute Maximum Ratings at 25 °C

| Parameter | Symbols | 1N4448W | Units |
|---|----------------|------------|-------|
| Non-Repetitive Peak Reverse Voltage | V_{RM} | 100 | V |
| Peak Repetitive Reverse Voltage | V_{RRM} | 75 | V |
| Working Peak Reverse Voltage | V_{RWM} | | |
| DC Reverse Voltage | V_R | | |
| RMS Reverse Voltage | $V_{R(RMS)}$ | 53 | V |
| Forward Continuous Current | I_{FM} | 500 | mA |
| Average Rectified Output Current | I_O | 250 | mA |
| Non-Repetitive Peak Forward Surge Current @t=1.0 μs @t=1.0 s | I_{FSM} | 4.0 2.0 | A |
| Power Dissipation | P_d | 350 | mW |
| Thermal Resistance Junction to Ambient Air | R_{thJA} | 357 | °C/W |
| Operating and Storage Temperature Range | T_j, T_{stg} | -65 ~ +150 | °C |

Characteristics at $T_a = 25\text{ °C}$

| Parameter | Symbols | 1N4448W | Units |
|--|-------------|---|----------|
| Reverse Breakdown Voltage at $I_R=1.0\mu A$ | $V_{(BR)R}$ | 75(min) | V |
| Forward Voltage at 5 mA at 10 mA at 100 mA at 150 mA | V_F | 0.62(min) 0.72(max) 0.855(max) 1.00(max) 1.25(max) | V |
| Peak Reverse Current at $V_R=75V$ at $V_R=20V$ | I_R | 2.5(max) 25(max) | μA nA |
| Typical Junction Capacitance f=1MHz, $V_R=0V$ | C_j | 4(max) | pF |
| Maximum Reverse Recovery Time ⁽¹⁾ | t_{rr} | 4 | ns |

(1) Measured with $I_F=I_R=10mA, I_{rr}=0.1 \times I_R, R_L=100\Omega$

Fig.1 Power Derating Curve




Fig.2 Typical Reverse Characteristics




Fig.3 Typical Instaneous Forward Characteristics






Fig.4 Typical Junction Capacitance



PACKAGE OUTLINE

Plastic surface mounted package; 2 leads


SOD-123W



SOD-123W mechanical data

| UNIT | | A | C | D | E | E ₁ | L ₁ | b | A ₁ | ∠ |
|------|-----|-----|------|-----|-----|----------------|----------------|-----|----------------|----|
| mm | max | 1.3 | 0.22 | 1.8 | 2.8 | 3.9 | 0.45 | 0.7 | 0.2 | 9° |
| | min | 0.9 | 0.09 | 1.5 | 2.5 | 3.6 | 0.25 | 0.5 | — | |
| mil | max | 51 | 8.7 | 71 | 110 | 154 | 18 | 28 | 8 | |
| | min | 35 | 3.5 | 59 | 98 | 142 | 10 | 20 | — | |

The recommended mounting pad size



Marking

| Type number | Marking code |
|-------------|--------------|
| 1N4448W | T5 |