

**50Ω Straight Cable Mount, BNC  
Connector, Plug, RG223/U**

**RoHS  
Compliant**

Stock No.: 1934134C005

## FEATURES

- 50Ω impedance
- Up to 4GHz
- Cable Mount




## Product Description

50 Ω BNC RF coaxial crimp plug connectors with bayonet coupling and a crimp/crimp professional coaxial termination. These 50 Ω BNC straight RF coaxial cable plugs have a PTFE insulator, nickel plated body, gold plated centre contact.

## General Specifications

| Attribute                     | Value            |
|-------------------------------|------------------|
| Coaxial Connector Type        | BNC Connector    |
| Gender                        | Male             |
| Mounting Type                 | Cable Mount      |
| Impedance                     | 50Ω              |
| Termination Method            | Crimp            |
| Body Orientation              | Straight         |
| Cable Type                    | RG223/U          |
| Bulkhead                      | No               |
| Operating Frequency           | 0 to 4GHz        |
| Body Plating                  | Nickel           |
| Minimum Operating Temperature | -65°C            |
| Maximum Operating Temperature | +165°C           |
| Contact Material              | Beryllium Copper |
| Contact Plating               | Gold             |

## Product Drawing



Dimensions: Millimeters (Inches)

### Part Number Table

| Part Number | Description  |
|-------------|--|
| 1934134C005 | 50Ω Straight Cable Mount, BNC Connector, Plug, RG223/U |

Important Notice: This data sheet and its contents (the "Information") belong to the members of the EASE group of companies (the "Group") or are licensed to it. No license is granted for the use of it other than for information purposes in connection with the products to which it relates. No license of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate, but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. EASE is the registered trademark of Ease Electronics Co., Limited 2019.