



# RoHS Compliant

## **FEATURES**

- 50Ω Impedance
- N Connector
- Cable Mount



### Product Description

- Straight male N plugs with cable gland.
- The screw coupling on this connector guarantees good HT performance.
- High admissible power.

### **General Specifications**


Attribute	Value
Gender	Male
Coaxial Connector Type	N Connector
Mounting Type	Cable Mount
Impedance	50Ω
Termination Method	Crimp
Body Orientation	Straight
Cable Type	RG165, RG213
Operating Frequency	0 to 11GHz
Minimum Operating Temperature	-55°C
Body Plating	Bronze
Maximum Operating Temperature	+155°C
Contact Material	Brass
Contact Plating	Gold over Nickel

Stock No.: 2956696C022





#### **Product Drawing**



Dimensions: Millimeters (Inches)

#### **Part Number Table**

Part Number	Description
2956696C022	50Ω Straight Cable Mount, N Connector, Plug, RG165, RG213

Important Notice: This data sheet and its contents (the "Information") belong to the members of the EASE group of companies (the "Group") or are licensed to it. No license is granted for the use of it other than for information purposes in connection with the products to which it relates. No license of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate, but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility for less or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. EASE is the registered trademark of Ease Electronics Co., Limited 2019.