

APPROVAL SHEET

Date :	0.6*13.6mm 8 ohm	
APPROVER	CHECKER	DESIGN
		富强
Please kindly make a	pproval of our samples.	And return this form by
or airmail, Thanks for Customer Name:	pproval of our samples, your kind attention and c	o-operation.

NAC HOLDINGS LIMITED. Tel:86-755-23341456 Fax: 86-755-23324431 Http://www.nacoustics.com sales@nacoustics.com





Acoustic Specifications

声学规格书

Product Part Number 产品编号 <u>NS96-136-B29-B</u>

Product Picture 产品图片

N/A

Revision Record 修订记录

No. 序号	Date 日期	Description 修订原因	Revision 版本	Acoustics Engineer 声学工程师

Sample Number 样品流水号_____

Datasheet Version 规格书版本:





目录 Contents

1.	SCOPE AND FEATURES.	. 4
2.	ELECTRICAL AND ACOUSTICAL CHARACTERISTICS.	. 4
3.	GENERAL REQUIREMENTS.	. 4
4.	RELIABILITY TEST.	. 5
5.	MESUREMENT BLOCK DIAGRAM & FREQUENCY RESPONSE CURVE	. 6
6.	DIMENSIONS.	7
7.	PACKAGE.	7







1. SCOPE AND FEATURES.

This specification covers our product of speaker unit for various uses.

2. ELECTRICAL AND ACOUSTICAL CHARACTERISTICS.

	ITEMS	COMMENTS	
2.1	Impedance	8Ω± 15%(@2KHz,1 Vrms input)	
2.2	Sensitivity (SPL) (in 1cc box)	83±3 dB (@1 Vrms/10cm at 2 kHz)	
2.3	Total Harmonic Distortion Limits (in 1cc box)	<15% @700Hz; <8%@1000Hz 1Vrms input <4% from 3K~10KHz 1Vrms input	
2.4	Resonance Frequency	In Free Air,f0:520±120Hz In 1cc Box,f0:800±100Hz	
2.5	Input Power (Normal/ Max) (in 1cc box)	300mW /800mW must be normal at a white noise (800mW) for one minute	
2.6	Audible Noise (in 1cc box)	Must be free audible noise (buzzes and rattles) (500~10KHz frequency range ,input level up to 1.55Vrms)	
2.7	Polarity	Diaphragm shall be move forward when applies a positive DC Current to the "+",the red wire is the "+"	

3. GENERAL REQUIREMENTS.

- 3.1 Weight: Appr 1.2g
- 3.2 Operating Temperature Range:

- 20 $^\circ\!\mathrm{C}$ to + 70 $^\circ\!\mathrm{C}$ without loss of function

- 3.3 Storage Temperature Range:
 - 40 $^\circ\!\mathrm{C}$ to + 85 $^\circ\!\mathrm{C}$ without loss of function





4. RELIABILITY TEST.


The sound pressure as specified shall neither deviate more than ± 4 dB from the initial value, nor any significant damage after any of following testing.

ITEMS		COMMENTS	
4.1	Temperature Test	High temperature: +85±3°C Low temperature: -40±3°C Duration: 1 hours Cycle: 10	
4.2	Humidity Test	Temperature: +40°C±3°C Relative Humidity: 90%~95%RH Duration: 96 hours (recovery 6 hours)	
4.3	Terminal Strength test	Load : 1.0Kg Duration: 5sec. (Shall be normal)	
4.4	Vibration Test	Sensitivity difference shall be within \pm 3dB after test(at 1KHz) Frequency range :10-55 Hz amplitude:1.5mm Duration:2h in each of 3 axis	
4.5	Drop Test	Sensitivity difference shall be within ±3dB after test(at 1KHz) Height: 1.50M Cycle: 10cycles	
4.6	Load Test	Sensitivity difference shall be within ±3dB after test(at 1KHz)Signal:White NoiseInput Power:300mWTest Time:72H	






5. MESUREMENT BLOCK DIAGRAM & FREQUENCY RESPONSE CURVE.



SPEAKER MODE BLOCK DIAGRAM




SPEAKER MODE FREQUENCY RESPONSE CURVE (in 1cc back volume)








6. DIMENSIONS.




Unit:mm Unless otherwise specified: +/-0.15mm Spring force inside working area: 0.25-1.2N







7. Package.



100pcs of speaker in each tray 10 trays in one carton Total:1000 pcs / 1 carton Gross Weight: 3.0KGS Net Weight:1.5 KGS

