

Customer			
Part name	Alkaline Zinc	c-Manganese D	ry Battery
Model No	D LR20 1.	5V	
Serial No			
Produce No			
Approved by		Drafted by	Wenfei liang
Checked by		Signed by	Xiaojun nie
Prepared by		Valid Date	2018-08-15

ELL SHENZHEN PKCELL BATTERY CO., LTD

ADD: 4th Building, Meitai Technology Park, Guanguang Road, Longhua, Shenzhen, China. 518110

1 Scope

This specification defines the technical requirements for 1.5V LR20Alkaline cells distributed by Pkcell. If not otherwise specified, the technical requirements and dimensions for cells should meet or exceed the requirements of GB/T 8897.1-2008, GB 8897.2-2008

2 Reference documents


GB8897.1-2008(IEC60086-1:2000,IDT) Primary batteries-Part 1:General GB8897.2-2008(IEC60086-2:2001,MOD) Primary batteries-Part 2:Physical and technological specifications

GB8897.5-2006(IEC 60086-5:2005,MOD)Primary batteries-Part 5:Safety of batteries with aqueous electrolyte

3 Chemical systems, voltages and designation

- 3.1 Chemical systems: Alkaline manganese battery
 - Zinc-Manganese dioxide
 - 3.2 Nominal voltage:1.5V
- 3.3 Designation
- IEC&GB(China): LR20; ANSI Number: D;

4 LR20 Battery Dimensions



The	LR20		
Measure No	Max	Min	
Α	61.5		
С		18.0	
F	9.5		
G		1.5	
Ø	34.2	32.2	

- 2 -

5 Voltage and Short current

Item	OCV (V)	CCV (V)	SCC (A)
Initial	1.56≤0CV≤1.65	≥1.45	≥7.0
After 12 months	≥1.56	≥1.4	≥6.0

OCV measurment:The inner resistance of Voltage Metre is above $1M\,\Omega$



C.C.V. measurment: After 0.2 $\pm\,0.01\,\text{sec}$ by R=5.0 Ω

SCC measurment: $\pm 0.5\%$

6 LR20 discharge performance :

Discharge conditions			Averge Minimun Discharge time	
Load(Ω)	Daily period	E.P. (V)	Initial	Delayed discharge performance after 12 months
3.9	24h/d	0.9	35H	32Н
2.2	1/d	0.9	18H	17H
10	4h/d	0. 9	110H	100Н

Initial:60 days after pruduction

Test condition: $20\,^\circ\!\!\mathrm{C}\pm 2\,^\circ\!\!\mathrm{C}$ and $60\pm 15\%\mathrm{RH}$

7 Leakage Resistance

Item	Test conditions	Sample size	Requirements	Acceptanc e
Overdischarge	10Ω 24h/d for 48h at 20℃±2℃,	n=9pcs	No leakage;Max of 0.35 mm height increase	Ac=0, Re=1

- 3 -



High Temperature and humidity storage	exposed to a temperature of 60℃± 2℃ and RH90±5% for a period of 3 weeks.	n=20pcs	No leakage	Ac=0, Re=1
45℃ Dry Storage	Stored for 12 weeks at 45℃	n=20pcs	No leakage	Ac=0, Re=1

8 Safety Requirement


Item	Test conditions	Sample size	Requirements of IEC60086-5:2005& GB8897.5-2006	Acceptanc e ⁴
Partial Use	Stored at 45℃±2℃ for 30days after undischarged batteries were test discharged 3.9Ω 24h/d,EPV=1.0V.	n=5pcs	No leakage;No explosion	Ac=0, Re=1
Thermal shock	See the following note 1,Total 10 Cycles	n=5pcs	No explosion	Ac=0, Re=1
Incorrect installation(3 + 1 anti- charge test)	Place three undischarged and unconditioned batteries in a series with one	n=5pcs	No explosion	Ac=0, Re=1



				,
	test sample battery reversed, Complete the circuit until vent activation or until the temperature of the reversed battery returns to ambient.			
Item	Test conditions	Sample size	Requirements of IEC60086-5:2005& GB8897.5-2006	Acceptanc e
Free fall	Drop each undischarged battery Two times, oriented in each of three mutually perpendicular face (six total) from a height 1 meter, onto a concrete surface, see the following note 2	n=5pcs	No explosion	Ac=0; Re=1




Overdischarge	Discharge one test sample battery(C1) with 43Ω resistance load until EPV is 0.6V,Connect three undischarged batteries and the sample battery in series with a 7.5 Ω resistance load(R1)as shown in note 3, Maintain the circuit until the CCV of the series string reaches 1.2V	n=5pcs	No explosion	Ac=0, Re=1
---------------	---	--------	--------------	------------



- 6 -

Note 2: Free fall



9 Inspection rules

10.1 Deliver inspection: Depending on GB2828



Number	Test	Item	IL	AQL
1	Dimensions	5	S-2	0.4
2	Appearance		II	1.0
3	Discharge capacity	7		
4	Open-circuit voltage	4.5	II	1.0

Routine inspection: Depending on GB2829 and QB/T2389

10 Inspection for service output:

- 10.1 9 samples shall be tested for service output
- 10.2 If the average value is equal to or more than the value of table 1, and if the number of batteries showing a value less than 80% of the value of table 1 is 1 or less. The batteries are considered to conform to the requirement.
- 10.3 If the average value is less than the value of table 1, or if the number of batteries
- showing a value less than 80% is 2 or more, the test shall be repeated with other 9 pieces. At the second test, if the average value is equal to or more than the value of table 1, and if the number of batteries showing a value less than 80% of the value of table 1 is 1 or less, these batteries are considered to conform to the requirement.
- 10.4 At above second test, if the average value is less than the value of table 1, or if the number of batteries showing a value less than 80% of the value of table 1 is 2 or more, the batteries are considered not to conform to the requirement. third test shall not be performed.

11 Instructions for use

- 11.1 Always select correct size and grade of battery most suitable fot intended use.
- 11.2 Replace all batteries of a set at the same time
- 11.3 Clean the battery contacts and also those of the equipment prior to battery installation

IENZHEN PKCELL BATTERY CO.,LTD

ADD: 4th Building, Meitai Technology Park, Guanguang Road, Longhua, Shenzhen, China. 518110

- 11.4 Ensure that batteries are installed correctly with regard polarity (+ and -):
- 11.5 Remove batteries from equipment which is not be used for an extend period of time;
- 11.6 Remove exhausted batteries promptly..

12. Disply and storage

- 12.1 Batteries shall be stored in well-ventilateddry and cool conditions
- 12.2 Battery cartons should not be piledup in severa layers, or should not exceed a specified height;
- 12.3 Batteries should not be exposed to direct sun ray for a long time or placed in areas where they get wet by rain.;

- 8 -

12.4 Do not mix unpacked batteries so as to avoid mechanical damage and/or short circuit among each other


13 Storage life

Storage life of batteries are ten years long at $20^{\circ}C \pm$

2℃ and RH $60\pm15\%$

14 Marks

- 15.1 Designation;
- 15.2 Polarity of terminals;
- 15.3 Nominal voltage;
- 15.4 Mercury content;
- 15.5 Name or trade mark , manufacturer or supplier ;
- 15.6 Cautionary advice



If manufacturer want to modify the product technology specification, we won't inform you additionally)

- 8 -