

# HDM500U SERIES



500 Watts

AC-DC ITE and Medical Switching Power Supply

### **KEY FEATURES**

- U Bracket Medical Switching Power Supply
- Remote ON/OFF Function
- 200 Watt with Free Air Convection
- 500 Watt with 30CFM FAN Forced Air
- 4000VAC Input to Output 2MOPP Insulation
- Built-in 12V/0.3A Auxiliary Output
- Standby 5V@1A with Fan, @0.4A without Fan
- High Efficiency up to 93%
- With P.F.C. Function >0.94
- Current Share Function for Option (except for 115)
- Suitable for BF Application with Appropriate System Consideration
- Ultra Compact Size: 5.5 x 3.25 x 1.6 Inches





(except for 115)

### **ELECTRICAL SPECIFICATIONS**

All specifications valid at normal input voltage, full load and +25°C after warm-up time unless otherwise stated.

Model No.			HDM500U-112	HDM500U-115	HDM500U-124	HDM500U-148		
Max Output V	Vattage (W)		500 W (30CFM FAN)					
May Output V	Mottogo (M)		Others: 190 W (1	Others: 190 W (115 VAC) / 200 W (230 VAC)				
wax Output v	Max Output Wattage (W)			15 VAC) / 180 W (230	VAC)			
Voltage (Note 3)			90-264 VAC or 127	-370 VDC				
	Frequency (Hz)		47-63 Hz					
lanat	Current (Full load)		< 6.3 A max. (115 V	/AC) / <3.15 A max. (	230 VAC)			
Input	Inrush Current (<2ms) (Clod Start)		< 40 A max. (115 V	AC) / < 80 A max. (23	30 VAC)			
	Leakage Current		< 0.1mA / 264 VAC	(Touch Current)				
	Power Factor (at 230 VAC)		PF>0.94 at Full Loa	ad		_		
	Voltage (V.DC.)		12V	15V	24V	48V		
	Voltage Accuracy		±2%					
	Voltage Adj. Range (V.DC)		±4% Output Voltage					
	Current (with 30CFM FAN) (A) max	×	41.5	33.3	20.8	10.41		
	Current	at 115 VAC	15.83	11.33	7.91	3.96		
	(Free air Convection) (A) max	at 230 VAC	16.6	12	8.33	4.17		
Output	Line Regulation (115-264 VAC)		±0.5%					
	Load Regulation (10-100%) (typ.)		±1%					
	Minimum Load		3%					
	Maximum Capacitive Load		5,000μF	3,750µF	2,500µF	1,250µF		
	Ripple & Noise (typ.)		160mV	160mV	240mV	480mV		
	Efficiency (at 230 VAC)		90.5%	90.5%	92%	93%		
	Hold-up Time (at 115 VAC)		8 ms min.					
	Over Power Protection		Auto recovery					
	Over Voltage Protection		Auto recovery					
Protection	Over Temperature Protection		Auto recovery					
	Short Circuit Protection		Protection level 1 (nominal) : Continuous, Auto recovery					
	Short Circuit Protection		Protection level 2 (instantaneous high current) : Latch					
	Input-Output (V.AC)	Input-Output (V.AC)			4000VAC or 5656VDC			
Isolation	Input-PE (V.AC)		2000V					
	Output-PE (V.AC)		1500V					



## HDM500U SERIES

A 30cm twisted pair of no.18 AWG copper wire is connected to a

47uF and 0.1uF capacitor of proper polarity and voltage rating. The oscilloscope probe ground led should connect right to the

The oscilloscope bandwidth should be at 20MHz and connected

ground ring of the probe and be as short as possible.


### **ELECTRICAL SPECIFICATIONS**

All specifications valid at normal input voltage, full load and +25°C after warm-up time unless otherwise stated.

Model No.		HDM500U-112 HDM500U-115 HDM500U-124 HDM500U-148					
	Operating Temperature	-30°C+70°C (with derating)					
	Storage Temperature	-35°C+85°C					
	Tomporature Coefficient	±0.03%/°C ( 0~50°C )					
	Temperature Coefficient	±0.06%/°C ( -30~0°C )					
	Altitude During Operation	5000m					
Environment	Humidity	95% RH					
	Atmospheric Pressure	56 kPa to 106 kPa					
	MTBF	>160,000 h @ 25°C (MIL-HDBK-217F)					
	Vibration	IEC60068-2-6 (10~500Hz, 2G 10min./1cycle, 60min. each along X, Y, Z axes)					
	Shock	IEC60068-2-27					
	Dimension s(L x W x H)	5.5 x 3.25 x 1.6 Inches (139.7 x 82.55 x 40.6 mm) Tolerance ±0.5 mm					
Physical	Weight	580 g					
	Cooling Method	Free convection / 30 CFM FAN					
		112/124/148:					
	Approval	UL / IEC / EN 60601 3.1 <sup>rd</sup> Edition (2 x MOPP), UL / IEC / EN 60950 AM2, UL / IEC / EN 62368					
Safety		115:					
	Approval / Meet	UL / IEC / EN 60601 3.1 <sup>rd</sup> Edition (2 x MOPP),					
		UL / IEC / EN 60950 AM2 (meet), UL / IEC / EN 62368 (meet)					
EMC	Conducted and Radiated EMI	EN55011 / conducted class B, Radiated Class A					
EIVIC	EMS	EN60601-1-2 4th edition					

### **NOTE**

1. Ripple & Noise are measured at 20MHz of bandwidth with ceramic 0.1uF & chemi-con KY 47uF parallel capacitor.



Twisted Pair: #18AWG-30cm

- 2. Hold-up Time measured at 90% Vout.
- 3. Please check the derating curve for more details.
- 4. Main Vout >3% Load, 12V (Aux) / 0.3A., 12V (Aux) need 0.1A Minimum Load, Auxiliary voltage output ground 10.2~13.3V


to AC ground.

5. Strongly recommend to conduct this test with DC Voltage. If customer wishes to test with AC Voltage, please disconnect all Y-Capacitors from Digital Power Corporation power supply.



### **NOTE**


- 6. Current Share Board (Optional):
  - (a.) The output voltage difference of each parallel single element should be less than 0.2V.
  - (b.)Output power at parallel operation = rated power per unit x number of unit x 90%
  - (c.)Connect in parallel no more than 2 units. Please contact Digital Power Corporation for advice if more than 2 is needed. (d.)Minimum Load Should be 15%.




7. CAUTION: Double pole, neutral fusing. Disconnect mains before servicing.

(ATTENTION: 2 poles avec fusible sur le neutre. Deconnecter le secteur avant intervention.)

### **DERATING**




### **BLOCK DIAGRAM**





### (Top View) **MECHANICAL DIMENSIONS**

### **HDM500U**




В	Brands	Al	ex	JST			
PIN#	Single	Mating Housing	Terminal	Mating Housing	Terminal		
A,B	PE	_		_	_		
1	AC IN (N)						
2	NO PIN	9396-3	96T series	VHR-3N	SVH-41T-P1.1		
3	AC IN (L)						
4	+DC OUT	Terminal : M5 Pan HD screw in 2 positions Torque to 8 lbs-in(90 cNm) max.					
5	-DC OUT						

Connector Pin (CN1)							
	Brands	Chern	g Weei	JST			
PIN#	Single	Mating Terminal		Mating Housing	Terminal		
C1	-5V SB						
C2	+5V SB						
C3	GND		PHD-H20- 2X4P PHD-T20	PHDR- 08VS	SPHD-001T- P0.5		
C4	DC-OK	PHD-H20-					
C5	-RC						
C6	+RC						
C7	-S	]					
C8	+S	1					

Connector Pin (FAN)							
Brands		Chern	g Weei	JST			
PIN#	Single	Mating Housing	Terminal	Mating Housing	Terminal		
F1	+12V	CX-H250-02	CX-T2501	XHP-2	SXH-002T-		
F2	GND				P0.6		

\*U Case T=1.5mm Customer is advised to screw into the threads no more than 1.5mm



13.0

12.0

O A

80.0

30 CFM

вф

В.Ф

50.0

16.28

Torque:3±0.5 Kgf.cm

40.6 21.6

A=M3x0.5P

B=M3x0.5P

A= For fixture to chassis only

B=For fixture to pcb/chassis only

фв

фΒ

9.85

30.1


BQ

63.35



### MECHANICAL DIMENSIONS (Top View)

### **HDM500U** with Current Share Function



В	Brands		ex	JST		
PIN#	Single	Mating Housing	Terminal	Mating Housing	Terminal	
A,B	PE	_	_		_	
1	AC IN (N)	9396-3	96T	VHR-3N	SVH-	
2	NO PIN		series	series 41T	VIII ( 01 (	41T-
3	AC IN (L)				P1.1	
4	+DC OUT	Terminal:  M5 Pan HD screw in 2 positions Torque to 8 lbs-in(90 cNm) max.				
5	-DC OUT					

Connector Pin (CN1)							
Bra	ınds	Chern	g Weei	JST			
PIN#	Single	Mating Housing	ο I I Δrminal I		Terminal		
C1	-5V SB						
C2	+5V SB						
C3	GND						
C4	DC-OK	PHD-	PHD-	PHDR-	SPHD-		
C5	-RC	H20- 2X4P	T20	08VS	001T- P0.5		
C6	+RC						
C7	-S						
C8	+S						

Connector Pin (FAN)							
Bra	inds	Cherng Weei		JST			
PIN#	Single	Mating Housing	Terminal	Mating Housing	Terminal		
F1	+12V	CX-	CX-	XHP-2	SXH- 002T-		
F2	GND	H250-02	T2501		P0.6		

12.05		- Mou	nting Surface
ASSEMBLY INSTRUCTIONS *U Case T=1.5mm Customer is advised to screw into threads no more than 1.5mm	the Chassis of HDM500U Series		-Mounting Screw

				1 1.0111111				
Connector Pin (CN2)								
Brands		Cherng Weei		JST				
PIN#	Single	Mating Housing	Terminal	Mating Housing	Terminal			
C1	-S	CP-	CP-	DUD 0	SPH- 002T-			
C2	+S	H20-02	T20B	PHR-2	P0.5L			

Mating Housing Pin (CN3)							
Brands		Cherng Weei	JST				
PIN#	Single	Connector	Connector				
C1	-5V SB						
C2	+5V SB						
C3	GND	OD 14/00 00	DOD DILLK O				
C4	DC-OK	CP-W20-06	B6B-PH-K-S				
C5	-RC						
C6	+RC						

Connector Pin (CN4)							
Brands		Chern	g Weei	JST			
PIN#	Single	Mating Housing	Terminal	Mating Housing	Terminal		
C1	LS	CP-	CP-	DUD 0	SPH- 002T-		
C2	LS	H20-02	T20B	PHR-2	P0.5L		



# HDM500U SERIES


### FUNCTION DESCRIPITON of CN1 and CN3 (CN3 without C7 and C8 pin)


Pin No.	Function	Description	
C1	-5VSB	This pin connects to the negative terminal(-V). Return for DC-OK and -RC signal output.	
C2	+5VSB	Stand by voltage output ground 4.2~5.5V, referenced to pin C1(-5VSB).  The maximum load current is 1A with Fan, 0.4A without Fan	
C3	GND	This pin connects to the negative terminal(-V). Return for DC-OK and -RC signal output.	
C4	DC OK	DC-OK Signal is a DC output, referenced to pin C3(DC-OK GND).	
C5	-RC	This pin connects to the negative terminal(-V). Return for DC-OK and -RC signal output.	
C6	+RC	Turns the output on and off by electrical or dry contact between pin C5 (-RC), Short: Power OFF, Open: Power ON. The input voltage must be less than 1V in order to disable VOUT and greater than 3.3V (up to 5V) to enable it.	
C7	-S	Negative sensing. The -S signal should be connected to the negative terminal of the load. The -S and +S leads should be twisted in pair to minimize noise pick-up effect.	
C8	+S	Positive sensing. The +S signal should be connected to the positive terminal of the load. The +S and -S leads should be twisted in pair to minimize noise pick-up effect.	

### **FUNCTION MANUAL & APPLICATION NOTE**

### 1. DC-OK Signal

Between DC-OK and GND	Output Status
3.7~6V	ON
0~1V	OFF






### 2. Remote Control

It can be turned ON/OFF by using the "Remote Control" function.

Between +RC and -RC	Output Status
SW ON (Short)	OFF
SW OFF (Open)	ON

# 



### 2. +S and -S Sense

Shorter wiring to each unit is recommended, as well as twisting +S and -S in pairs, as shown below

