

PRODUCT SPECIFICATION

DOCUMENT NO. 0000071XXXXX						
DESCRIPTION	DRAWN BY	DESIGNED BY	CHECKED BY	APPROVED BY		
MLVG0603DG Series	Sandy	James	James	Shawn Yeh		





MLVG0603DG Series Engineering Specification

1. Scope

- (1) Lead free type
- (2) SMD type zinc oxide based ceramic chip
- (3) Insulator over coat keeps excellent low and stable leakage current
- (4) Plating termination provided good solder-ability characteristic
- (5) Wide operating voltage range, VCD : 5.5V to 18V
- (6) Quick response time (<1ns)
- (7) Low clamping voltage
- (8) Meet IEC 61000-4-2 standard
- (9) Low capacitance can meet high speed single transient voltage protection

Applications

Low Capacitance Product Applications for High Speed I/O port such as HDMI, DVI, USB, and IEEE1394 etc.

Normal capacitance product applications for I/O Port such as RS232, USB, PS2, VGA, Audio on Mother Board and Notebook, Set-Top Box, MP3 Players, DVD Players, and Docking System etc.

2. Explanation of Part Number


<u>MLV</u>	<u>G</u>	<u>0603</u>	<u>3R0</u>	T	<u>V18</u>	<u>DG</u>	
(1)	(2)	(3)	(4)	(5)	(6)	(7)	(8)
<u>MLV</u>	<u>G</u>	<u>0603</u>	<u>100</u>	<u>N</u>	<u>V18</u>	<u>DG</u>	
(1)	(2)	(3)	(4)	(5)	(6)	(7)	(8)


- (1) Series Type: MLV Multilayer Varistor
- (2) Model Code
- (3) Chip Size (EIA): 0603
- (4) Capacitance:Value-XRX=0.XpF,Ex:3R0=3.0pF; XXx10^N \rightarrow XXN Ex: 10pF=10x10⁰ \rightarrow 100
- (5) Capacitance Tolerance: I $\pm 0.3 pF,$ T -±1.4pF Q (or L) $\pm 2.0 pF$, N -±30% and U-±0.9pF
- (6) Working Voltage: V_{DC}
- (7) Inpaq Special Code
- (8) Special Code

TITLE : MLVG0603DG Series Engineering Specification	DOCUMENT NO. 0000071XXXXX	SPEC REV.: A19	Page 1 of 9	



3. Construction & Dimension





Size EIA (EIAJ)	0603 (1608)
L	1.60 ± 0.20
W	0.80 ± 0.20
Т	0.80 ± 0.20
С	0.30 ± 0.20

TITLE : MLVG0603DG Series Engineering Specification	DOCUMENT NO. 0000071XXXXX	SPEC REV.: A19 Page 2 of 9
--	------------------------------	----------------------------



4. Part Characteristics

General Characteristics

Part Number	Rated Voltage	Varistor Voltage	Clamping Voltage	Capacitance
	V _{DC} (V)	Vv (V)	Vc (V)	C _P (pF)
MLVG06030R5IV18BPDG	~18	90~120	250*	0.5
MLVG06031R0IV18BPDG	~18	46~60	110*	1.0
MLVG06031R5TV18BPDG	~18	46~60	110	1.5
MLVG06033R0TV18BPDG	~18	22~34	58	3.0
MLVG06033R0QV18BPDG	~18	46~60	110	3.0
MLVG06035R0QV18BPDG	~18	22~34	58	5.0
MLVG0603100NV18BPDG	~18	22~34	58	10
MLVG0603120NV18BPDG	~18	22~34	58	12
MLVG0603150NV18BPDG	~18	22~34	58	15
MLVG0603220NV18BPDG	~18	22~34	58	22
MLVG0603400NV18BPDG	~18	22~34	58	40
MLVG0603101NV18BPDG	~18	22~34	58	100
MLVG0603221NV18BPDG	~18	22~34	58	220
MLVG0603331NV18BPDG	~18	22~34	58	330
MLVG06031R0UV18CPDG	~18	46~60	110*	1.0
MLVG06030R5IV28BPDG	~28	90~120	250*	0.5

Part Number	Rated Voltage	Varistor Voltage	Clamping Voltage	Capacitance
	V _{DC} (V)	Vv (V)	V _C (V)	C _P (pF)
MLVG06035R0QV05BPDG	~5.5	7.6~12	25	5.0
MLVG0603100NV05BPDG	~5.5	7.6~12	25	10
MLVG0603220NV05BPDG	~5.5	7.6~12	25	22
MLVG0603951NV05BPDG	~5.5	7.6~12	25	950

Specification 0000071XXXXX 3FL	O. SPEC REV.: A	A19 Page 3 of 9
--------------------------------	-----------------	-----------------



Part Number	Rated Voltage	Varistor Voltage	Clamping Voltage	Capacitance
	V _{DC} (V)	V _V (V)	V _C (V)	C _P (pF)
MLVG06035R0QV09BPDG	~9	11~17	35	5.0
MLVG0603100NV09BPDG	~9	11~17	35	10
MLVG0603220NV09BPDG	~9	11~17	35	22
MLVG0603221NV09BPDG	~9	11~17	35	220
MLVG0603331NV09BPDG	~9	11~17	35	330
MLVG0603551NV09BPDG	~9	11~17	35	550

Part Number	Rated Voltage	Varistor Voltage	Clamping Voltage	Capacitance
	V _{DC} (V)	$V_V(V)$	Vc (V)	C _P (pF)
MLVG06033R0LV42BP	~42	46~75	135	3.0

** For special part number which is not shown in the above table, please contact with our sales department if you needed.

 V_{DC} – Maximum DC operating voltage the varistor can maintain and not exceed 10µA leakages current

Vv – Voltage across the device measured at 1mA DC current. Equivalent to Vb, "break down voltage".

Vc - Maximum peak voltage across the varistor measured at 8/20us waveform and 1A pulse current

*: Maximum peak current across the varistor with 8/20µs waveform and 0.5A pulse current.

C_p – Device capacitance measured with 1 Vrms at 1MHz.

5. General Electrical Specifications

5.1 General Technical Data

Operating temperature	-40°C∼ +85°C
Storage temperature (on board)	-40°C ~ +85°C
Response time	<1 ns
Solderability	245±5℃, 3±1sec
Solder leach resistance	260±5℃, 10±1sec

TITLE : MLVG0603DG Series Engineering DOCUMENT NO. SPEC Specification 0000071XXXXX SPEC	REV.: A19	Page 4 of 9
---	-----------	-------------



5.2 Environmental Performance


Characteristics	Specifications	Test condition
Bias humidity	$\Delta V_V/V_V \leq \pm 10\%$	90%RH, 40℃, Working voltage, 1000 hours
Thermal shock	$\Delta V_V/V_V \leq \pm 10\%$	-40° \mathbb{C} to 85° \mathbb{C} , 30 min. Cycle, 5 cycles
Full load voltage	$\Delta V_V / V_V \leq \pm 10\%$	Working voltage, 85° C, 1000 hours

5.3 Storage Condition with Package

Storage Time: 12 months max. Storage Temperature: 5° C to 40° C Relative Humidity: 65°

6. Taping Package and Label Marking


6.1 Carrier Tape Dimensions



TITLE : MLVG0603DG Series Engineering DOCUMENT NO. SPEC REV.: A19 Page 5 of 9 Specification 0000071XXXXX SPEC REV.: A19 Page 5 of 9	•••		SPEC REV.: A19	Page 5 of 9	
---	-----	--	----------------	-------------	--



6.2 Taping Reel Dimensions



6.3 Taping Specifications

There shall be the portion having no product in both the head and the end of taping, and there shall be the cover tape in the head of taping.

6.4 Label Marking

The label specified as follows shall be put on the side of reel.

- (1) Part No.
- (2) Quantity
- (3) Lot No.

* Part No. And Quantity shall be marked on outer packaging.

6.5 Quantity of Products in the Taping Package

- (1) Standard quantity : 4000pcs/Reel for MLVG 0603 series
- (2) Shipping quantity is a multiple of standard quantity.

TITLE : MLVG0603DG Series Engineering Specification	DOCUMENT NO. 0000071XXXXX	SPEC REV.: A19 Pa	ge 6 of 9




7. Precautions for Handling

7.1 Solder Cream in Reflow Soldering

Refer to the recommendable land pattern as printing mask pattern for solder cream.

(1)Print solder in a thickness of 150 to 200 μ m. Dimensions: millimeters (inches)



7.2 Precaution for Handling of Substrate

Do not exceed to bend the board after soldering this product extremely. (Reference examples)

- Mounting place must be as far as possible from the position, which is close to the break line of board, or on the line of large holes of board.
- Do not bend extremely the board, in mounting another component. If necessary, use back-up pin (support pin) to prevent from bending extremely.
- Do not break the board by hand. We recommend using the machine or the jig to break it.

7.3 Precaution for Soldering


Note that rapid heating, rapid cooling or local heating will easily damage this product. Do not give heat shock over 100°C in the process of soldering. We recommend taking preheating and gradual cooling.

	TITLE : MLVG0603DG Series Engineering Specification	DOCUMENT NO. 0000071XXXXX	SPEC REV.: A19 Page 7 of 9
--	--	------------------------------	----------------------------



7.4 Recommendable Reflow Soldering

Profile Feature	Pb-Free Assembly
Average Ramp-Up Rate	3°C/second max.
(Tsmax to Tp)	
Preheat	
– Temperature Min (Tsmin)	150 °C
– Temperature Max (Tsmax)	200 °C
- Time (tsmin to tsmax)	60-180 seconds
Time maintained above:	
– Temperature (TL)	217 ℃
– Time (tL)	60-150 seconds
Peak/Classification Temperature (Tp)	260 °C
Time within 5 ℃ of actual Peak	
Temperature (tp)	20-40 seconds
Ramp-Down Rate	6 ℃/second max.
Time 25 °C to Peak Temperature	8 minutes max.



^{*}According to J-STD-020C

TITLE : MLVG0603DG Series Engineering Specification	DOCUMENT NO.	SPEC REV.: A19	Page 8 of 9
Specification	0000071XXXXX		_



7.5 Soldering Gun Procedure

Note the follows, in case of using solder gun for replacement.

- (1) The tip temperature must be less than 280 $^\circ\!C$ for the period within 3 seconds by using soldering gun less than 30 W.
- (2) The soldering gun tip shall not touch this product directly.

7.6 Soldering Volume

Note that excess of soldering volume will easily get crack the body of this product.

TITLE : MLVG0603DG Series Engineering Specification	DOCUMENT NO. 0000071XXXXX	SPEC REV.: A19 Page 9 of 9