

# PRODUCT SPECIFICATION

DOCUMENT NO. ENS000079430						
DESCRIPTION	DRAWN BY	DESIGNED BY	CHECKED BY	APPROVED BY		
MLVS 0603DG Lead Free Series	Sandy	Hungtsai	Shawn Yeh	Shawn Yeh		



# **ROHS** MLVS 0603DG Lead Free Series Engineering Specification

### 1. Scope


- (1) SMD type zinc oxide based ceramic chip
- (2) Lead free plating termination provided good solderability characteristic
- (3) Insulator over coat keeps excellent low and stable leakage current
- (4) Quick response time (<1ns)
- (5) Low clamping voltage
- (6) High transient current capability
- (7) Compact size for EIA 0603

#### Applications

**Applications** for Mother Board and Notebook, Cellular Phone, PDA, handheld device, DSC, DV, Scanner, and Set-Top Box etc.

Suitable for Push-Button, Power Line and Low Frequency single line over voltage protect.


#### 2. Explanation of Part Number




TITLE: MLVS 0603DG Lead Free Series Engineering Specification	DOCUMENT NO. ENS000079430	SPEC REV.: A7	Page 1 of 9



## 3. Construction & Dimension





Unit: mm	0603
L	1.60±0.15
W	0.80±0.1
Т	0.80±0.1
С	0.30±0.20

TITLE: MLVS 0603DG Lead Free Series Engineering Specification	DOCUMENT NO. ENS000079430	SPEC REV.: A7	Page 2 of 9	
	EN3000079430			



#### 4. Part ratings and characteristics:

4.1. Rating(25±5℃)

		rking tage	Varistor voltage	Clamping Voltage	Capacitance	Peak current	Transient energy
Symbol	VRMS	VDC	Vv	Vc	Ср	İmax	W <sub>max</sub>
Units	Volts	Volts	Volts	Volts	pF	Amps	Joules
Units	VOIIS	(Max.)	VOIIS	(Max.)	(Typical)	(Max.)	(Max.)
Test Condition		< 10 µ A	1mA DC	1A 8/20 μ s	1MHz	8/20 μ s	10/1000 $\mu$ s
MLVS 0603 L04DG	4	5.5	8 ~ 18	24	270	30	0.1
MLVS 0603 L04MDG	4	5.5	6.4 ~ 9.6	19	300	30	0.1
MLVS 0603 L06DG	7	9	11.5 ~ 21.5	41	210	30	0.1
MLVS 0603 L11DG	11	14	16.5 ~ 26.5	45	220	30	0.1
MLVS 0603 L14DG	14	18	23 ~ 33	54	150	30	0.1
MLVS 0603 L14JDG	14	18	22 ~ 28	45	150	30	0.1
MLVS 0603 L20DG	20	26	32 ~ 42	70	100	30	0.1
MLVS 0603 L21DG	21	29	38~ 48	70	80	30	0.1
MLVS 0603 LE06DG	-	12	25 ~ 40	60 (Typical)	40	-	-
MLVS 0603 LE08DG	-	12	25 ~ 40	110	40	-	-
MLVS 0603 LE10DG	-	12	45 ~ 65	150	3.5	-	-
MLVS 0603 LE12DG	-	26	45 ~ 65	145	4	-	-

- V<sub>RMS</sub> Maximum AC operating voltage the varistor can maintain and not exceed10µA leakage current
- $V_{DC}$  Maximum DC operating voltage the varistor can maintain and not exceed 10µA leakage current
- $V_V$  Voltage across the device measured at 1mA DC current.
  - Equivalent to Vb, "Breakdown Voltage".
- Cp Device capacitance measured with zero volt bias 1Vrms at 1MHz.
- Vc Maximum peak voltage across the varistor measured at 8/20us waveform and 1A pulse current
- imax Maximum peak current which may be applied with 8/20us waveform without device failure
- W<sub>max</sub> Maximum energy that may be dissipated with the 10/1000us waveform without device failure

Engineering Specification ENS000079430 SPEC REV.:
---



#### 5. General electrical specifications

#### 5.1. General technical data

Operating temperature	<b>-40 +85</b> ℃
Storage temperature (on board)	-40… +85℃
Response time	<1 ns
Solderability	245±5℃, 5+0/ -0.5sec
Solder leach resistance	260±5℃,10 ±1sec

#### 5.2. Environmental Specifications

Characteristics	Specifications	Test condition
Bias humidity	$\Delta V_V/V_V \leq \pm 10\%$	90%RH, 40 $^\circ\!$ C, Working voltage, 1000 hours
Thermal shock	$\Delta V_V/V_V \leq \pm 10\%$	-40 $^{\circ}$ C to 85 $^{\circ}$ C, 30 min. Cycle, 5 cycles
Full load	$\Lambda M = \Lambda M = \pm 1.09/$	Working voltage $85^{\circ}$ 1000 beurs
voltage	$\Delta V_V/V_V \leq \pm 10\%$	Working voltage, $85^{\circ}$ C, 1000 hours

#### 5.3. Storage Condition with package


Storage Time: 12 months max Storage Temperature : 5 to  $40^{\circ}$ C Relative Humidity: to 65 %

TITLE: MLVS 0603DG Lead Free Series Engineering Specification	DOCUMENT NO. ENS000079430	SPEC REV.: A7	Page 4 of 9	



# 6. Taping Package and Label Marking


6.1. Carrier tape dimensions



U	Nľ	T:	mm
<u> </u>		•••	

Α	В	С	D	E	F	L	W	
8.00±	3.50±	1.75±	2.00±	4.00±	1.50±	1.90±	1.05±	
0.30	0.05	0.10	0.05	0.10	0.10	0.15	0.15	

#### 6.2. Taping reel dimensions



TITLE: MLVS 0603DG Lead Free Series Engineering Specification	DOCUMENT NO. ENS000079430	SPEC REV.: A7	Page 5 of 9	

# INPAQ TECHNOLOGY CO., LTD.



#### 6.3. Taping specifications

There shall be the portion having no product in both the head and the end of taping, and there shall be the cover tape in the head of taping.

#### 6.4. Label Marking

The label specified as follows shall be put on the side of reel.

- (1) Part No.
- (2) Quantity
- (3) Lot No.
- \* Part No. And Quantity shall be marked on outer packaging.

#### 6.5. Quantity of products in the taping package

- (1) Standard quantity: 4000pcs/Reel for MLVS 0603 Lead Free series
- (2) Shipping quantity is a multiple of standard quantity.

TITLE: MLVS 0603DG Lead Free SeriesDOCUMENT NO.Engineering SpecificationENS000079430	SPEC REV.: A7	Page 6 of 9
--	---------------	-------------

# INPAQ TECHNOLOGY CO., LTD.




#### 7. Precautions for Handling

#### 7.1. Solder cream in reflow soldering

Refer to the recommendable land pattern as printing mask pattern for solder cream.

- (1) Print solder in a thickness of 150 to 200  $\mu m.$
- (2) Dimensions: millimeters (inches)



#### 7.2. Precaution for handling of substrate

Do not exceed to bend the board after soldering this product extremely. (Reference examples)

- Mounting place must be as far as possible from the position, which is close to the break line of board, or on the line of large holes of board.
- Do not bend extremely the board, in mounting another components. If necessary, use back-up pin (support pin) to prevent from bending extremely.
- Do not break the board by hand. We recommend using the machine or the jig to break it.

#### 7.3. Precaution for soldering

Note that rapid heating, rapid cooling or local heating will easily damage this product.

Do not give heat shock over 100°C in the process of soldering. We recommend taking preheating and gradual cooling.

TITLE: MLVS 0603DG Lead Free Series	
Engineering Specification	


DOCUMENT NO. ENS000079430

SPEC REV.: A7 Page 7 of 9



#### 7.4. Recommendable reflow soldering

Profile Feature	Pb-Free Assembly
Average Ramp-Up Rate	3°C/second max.
(Tsmax to Tp)	
Preheat	
– Temperature Min (Tsmin)	150 °C
– Temperature Max (Tsmax)	200 °C
<ul> <li>Time (tsmin to tsmax)</li> </ul>	60-180 seconds
Time maintained above:	
– Temperature (TL)	217 ℃
– Time (tL)	60-150 seconds
Peak/Classification Temperature (Tp)	260 °C
Time within 5 ℃ of actual Peak	
Temperature (tp)	20-40 seconds
Ramp-Down Rate	6 °C/second max.
Time 25 °C to Peak Temperature	8 minutes max.



\*According to J-STD-020C

	CUMENT NO. SPEC REV.: A7	Page 8 of 9
--	--------------------------	-------------

# INPAQ TECHNOLOGY CO., LTD.



#### 7.5. Soldering gun procedure

Note the follows, in case of using solder gun for replacement.

- (1) The tip temperature must be less than 350°C for the period within 3 seconds by using soldering gun less than 30 W.
- (2) The soldering gun tip shall not touch this product directly.

#### 7.6. Soldering volume

Note that excess of soldering volume will easily get crack the body of this product.

TITLE: MLVS 0603DG Lead Free Series Engineering Specification	DOCUMENT NO. ENS000079430	SPEC REV.: A7	Page 9 of 9