
PD-9501GO Midspan



Single-port, Outdoor PoE Midspan, 60W, IEEE802.3at Compliant



Overview

Microsemi's PD-9501GO Power over Ethernet (PoE) single-port Midspan offers a cost effective, IEEE 802.3at compliant solution for outdoor installations, guaranteeing 60 Watts of power and ensuring safe and reliable operation in outdoor environment of any standard PoE data terminal. It allows wireless LAN access points, security network cameras and other IP terminals to receive power, along with data, over standard Ethernet cables, leaving network infrastructure completely unaltered. The PD-9501GO also offers surge protection for both the AC and the PoE ports ensuring the indoor equipment is protected from outdoor surges.

PD-9501GO Features

- Outdoor rated: IP66
- Extended temperature range -40°C, +55°C
- IEEE802.3at standard compliant
- Power provided using all 4 pairs
- Supports 10/100/1000Mbps data rates
- Plug 'n Play installation (installer does not have to open unit)
- Supports both 802.3af and 802.3at Powered devices
- Includes integral surge protection

PD-9501GO Specifications

No. of Ports	1	
Pass Through Data Rates	10/100/1000 Mbps	
Power over Ethernet	Pin Assignment and Polarity:	
Output	4/5 (+), 7/8 (-), 1/2(-), 3/6(+) Output Power Voltage: 55 VDC User Port Power: 60W guaranteed	
Input Power	AC Input Voltage: 100 to 240 VAC	
Requirements	AC Input Current: 2.0A @100-240 VAC AC Frequency: 50 to 60 Hz	
Dimensions	214 mm x 150 mm x 70 mm 8.42 in. x 5.90 in. x 2.75 in	
Weight	1.65 lbs (750g)	
Indicators	No LED indicators	
Connectors	Shielded rugged RJ-45 (with gasket)	
Environmental Conditions	Operating Ambient Temperature: -40° to 122°F (-40 to 50°C) for 60W -40° to 131°F (-40 to 55°C) for 30W	
Operating Humidity	Maximum 95%, Non-condensing	
Storage Temperature	-40° to 185°F (-40° to 85°C)	
Storage Humidity	Maximum 95%, Non-condensing	
Operating Altitude	Up to 6,560 ft. (2000 m)	
Weather Rating	IP66, NEMA 4X	
Reliability	MTBF: 189,000 hrs. @25°C	
Thermal Rating	45 BTU/Hr (@240VAC)	
Warranty	1-year	
Regulatory Compliance	IEEE 802.3af (PoE, PoH Type1) IEEE 802.3at (PoE+ including 2-event, PoH Type 2), RoHS Compliant, WEEE Compliant, CE	
Electromagnetic	FCC Part 15, Class B	
Emission & Immunity	EN 55022 Class B EN 55024, EN61000-4-5 Class 5 (6kV CM) VCCI	
Surge Protection	Meets Surge Protection as specified in GR-1089-CORE Issue 4 ITU-T K.20 6 kV on AC lines	
Safety Approvals	UL60950-1 & UL60950-22 GS Mark	
Other Standards and	Dust and water intrusion: EN60529,	
Approvals	Level1P66; NEMA 250, Level 4X ASTM B-117 Corrosion Resistance	

PD-9501GO with outdoor mounting bracket







Ordering Information

Part Number	Name	Description	
PD-9501GO/AC-NA	Microsemi PD-9501GO	1-port, 60W 802.3at Gigabit PoE outdoor midspan with North American power connector	
PD-9501GO/AC-INTL	Microsemi PD-9501GO	1-port, 60W 802.3at Gigabit PoE outdoor midspan with international power cord	
PD-OUT/MBK	Microsemi OUT MBK	Mounting brackets for outdoor unit	



One Enterprise, Aliso Viejo, CA 92656 USA Within the USA: +1 (800) 713-4113 Outside the USA: +1 (949) 380-6100 Sales: +1 (949) 380-6136 Fax: +1 (949) 215-4996 email: sales.support@microsemi.com

www.microsemi.com

Microsemi Corporation (Nasdaq: MSCC) offers a comprehensive portfolio of semiconductor and system solutions for communications, defense & security, aerospace and industrial markets. Products include high-performance and radiation-hardened analog mixed-signal integrated circuits, FPGAs, SoCs and ASICs; power management products; timing and synchronization devices and precise time solutions, setting the world's standard for time; voice processing devices; RF solutions; discrete components; security technologies and scalable anti-tamper products; Power-over-Ethernet ICs and midspans; as well as custom design capabilities and services. Microsemi is headquartered in Aliso Viejo, Calif., and has approximately 3,400 employees globally. Learn more at www.microsemi.com.