CLIFF

VARIANTS


MODEL	P/No.	VERSION	DIM A
MS1 X/S	CL19192	Α	2.1
MS1 X/SB	CL19192B	В	2.1
MS1 X/A	CL19194	1/4" TAGS	2.1
MS1 X/S1	CL19191	Α	1.1
MS1 X/A1	CL19193	14" TAGS	1.1
MS1 X2P/A1	CL191930	14" TAGS	1.1
MS1 X/A1 WHITE	CL191931	14" TAGS	1.1


USES INSULATING BOOT CL1928

R4.0 RECOMMENDED PANEL CUT-HUT SIZE 0 Ċ

ISS. **AMEND** DATE REDRAWN ERROR CORRECT 01/03/90 06/07/95 8 9 10 CL191930 ADD 30.5 WAS 30.8 24/02/98 15/12/98 MS1X/SB ADDED 26/03/99 CORRECTIONS 30/04/99 11 12 13 14 15 30.3 WAS 30.5 27/03/01 FINS REMOVED 08/01/02 ENEC17 ADD 07/03/03 REMOVE CSA RoHS + 16/06/08 UL MARK REMOVED 31/01/17

NOTE: MODELS S1/A1 SUITABLE FOR PANEL THICKNESS 0.8mm TO 1.1mm. MODELS S/A SUITABLE FOR PANEL THICKNESS 1.0mm TO 2.1mm.





RoHS, **▼**COMPLIANT

TOLERANCE NO DEC. PLACE ± 1 DEC. PLACE ± 0.20 2 DEC. PLACE ± HOLE ر ANGLES ± 1° UNLESS OTHERWISE STATED

Cliff Electronic Components Ltd.
76 Holmethorpe Avenue, Holmethorpe Industrial Estate,
Redhill, Surrey, RH1 2PF, England, UK

Tel: 01737-771375 Fax: 01737-766012 Website: www.cliffuk.co.uk THE CONTENTS OF THIS DOCUMENT MUST NOT BE COPIED OR DISCLOSED TO A 3rd PARTY WITHOUT WRITTEN PERMISSION OF CLIFF UK.

DIMENSIONS IN MILLIMETERS UNLESS OTHERWISE STATED, WORK TO DIMENSIONS, REMOVE ALL BURRS, IF IN DOUBT ASK,

POLYAMIDE UL94HB / BRASS MATERIAL: AS MOULDED / Ni PLATED FINISH: DRAWN: C.A.M.J. APPROVED: RWT

APPROVED ENEC17 FOR ALL EC COUNTRIES.

TITLE: AC INLET MS1 X SNAP IN TYPE

CL 19192 DRWG. No.

DO NOT SCALE

FORM: A4DRWGH