



# Infrastructure product

## Anybus Unmanaged L2 Switch

The Anybus L2 Switch provide full Gigabit and ultra-high throughput.

Support for dual power supplies ensures uninterrupted operations.



### FEATURES & BENEFITS

#### FULL GIGABIT SWITCHING

- 8 port Gigabit Ethernet with Auto Negotiation
- 4k MAC address table
- Supports 9 kB Jumbo Frame
- IEEE 802.1p QoS/802.1Q VLAN
- Broadcast storm protection
- Store and forward with non-blocking switch fabric

#### IEEE 802.3AZ ENERGY EFFICIENT POWER MANAGEMENT

- Ultra-low power consumption, max 2.6W
- Energy efficient with idle power saving mode
- Support for dual power supplies

#### RUGGED MECHANICAL DESIGN

- IP40 ingress protection
- DIN-rail mount
- Wide operating temperature range, -40 to 70°C

Europe  
 North America  
 CE  
 FCC

<b>Ethernet ports</b>	8 x 1 Gbit/s RJ45, auto negotiation Auto MDI/MDIX
<b>Operating temp.</b>	-40°C-70°C, 5-95 % non-condensing
<b>Data speeds</b>	1000Base-TX

	100Base-TX
	10Base-T
<b>Power</b>	12/24/48 VDC (9.6-60 VDC)
	IEEE 802.3az EEE Power management: Ultra low power design (max 2.6 W), Energy efficient Ethernet with idle power saving mode
	Support for dual power supplies
<b>Weight</b>	560 g
<b>Housing material</b>	Steel
<b>Ingress protection</b>	IP40
<b>Dimensions</b>	145 x 100 x 40 mm (without DIN rail clip)
<b>Mounting</b>	DIN rail mount (bracket included)

File	Version	Size	Read online
------	---------	------	-------------

---

#### Content of delivery

Switch

1 x DIN-rail mounting bracket

## Ordering Information

<b>Order code</b>	AWB5001
-------------------	---------

3 year guarantee. For purchasing instructions and terms and conditions, see: → [How to buy](#)

---

Copyright © 2020 HMS Industrial Networks - All rights reserved.