






PCB LAYOUT



2\*3P-2-9P



SHORT LATCH



LONG LATCH

■ Specifications :

- Voltage rating: 250V AC / DC
- Current rating: 3A AC / DC
- Withstanding voltage: 1500V AC/minute
- Temperature Range: -25° C~+85° C
- Insulation Resistance: 1000MΩ Min.
- Contact Resistance: 20mΩ Max.

Reference Informations:

\*Material:

PIN: Brass/Gold-flash

Wafer: PBT,UL94V-0

Color: BK-Black



A2544 W V A - 2NP - P0 BK G X

① ②③④ ⑤ ⑥⑦⑧⑨

- ① Series No.
- ② Category:W-wafer
- ③ Welding Board Angle: V- Straight 180° , R-Vertical 90°
- ④ Colloid Feature: Blank-Common,A-A type( ...
- ⑤ Circuit No.: 230-2\*15PIN,
- ⑥ Material: 6T-Nylon6T,UL94V-0; P0-PBT,UL94V-0;
- ⑦ Color: BK-Black, WT-White
- ⑧ Plating Method: G-Gold-flash, T-Tin-plated,
- ⑨ Option: Blank-Standard type( ), 2-B type( )

Ordering Information & Dimensions

Poles	Dimensions (mm)			Poles	Dimensions (mm)		
	A	B	C		A	B	C
2*3P	26.92	16.76	5.08	2*18P	65.02	54.86	43.18
2*4P	29.46	19.30	7.62	2*19P	67.56	57.40	45.72
2*5P	32.00	21.84	10.16	2*20P	70.10	59.94	48.26
2*6P	34.54	24.38	12.70	2*21P	72.64	62.48	50.80
2*7P	37.08	26.92	15.24	2*22P	75.18	65.02	53.34
2*8P	39.62	29.46	17.78	2*23P	77.72	67.56	55.88
2*9P	42.16	32.00	20.32	2*24P	80.26	70.10	58.42
2*10P	44.70	34.54	22.86	2*25P	82.80	72.64	60.96
2*11P	47.24	37.08	25.40	2*26P	85.34	75.18	63.50
2*12P	49.78	39.62	27.94	2*27P	87.88	77.72	66.04
2*13P	52.32	42.16	30.48	2*28P	90.42	80.26	68.58
2*14P	54.86	44.70	32.02	2*29P	92.96	82.80	71.12
2*15P	57.40	47.24	35.56	2*30P	95.50	85.34	73.66
2*16P	59.94	49.78	38.10	2*31P	98.04	87.88	76.20
2*17P	62.48	52.32	40.64	2*32P	100.58	90.42	78.74

2022.07.07	A1	A2	依据实物优化图纸			一般公差 GENERAL TOLERANCE .X ±0.3 .XX ±0.2 .XXX ±0.1		料号 PART NO A2544WVA-2NP-P0BKGX			
2021.05.13	A	A1	增加缺口标示					核准 APPD	审核 CHK	绘图 DR	日期 DATA
日期 DATE	旧版次 OLD REV	新版次 NEW REV	变更内容 DESCRIPTION	审核 CHK	核准 APPD	角法 PROJECT 		单位 UNIT MM	比例 SCALE 1/1	图号 NUMBER	版次 REV A2