IN HIGH TEMPERATURE, LOW TEMPERATUEE. HIGH HUMIDITY ENVIRONMENT. CONDENSATION OF ATMOSPHERE MUST BE AVOIDED IN MOTER USAGE OR OPENING THE PACKAGING OF THE MOTOR.

7.4 马达应适当的操作、储存和运转环境中均不可存在腐蚀性气体。例如: H2S、S02、N02、CL2 等。另外存储环境中不可有诸如硅、氰、甲醛水和苯酚等能放射出腐蚀性气体的物质,在电机的机械构造或装置中,如果存在腐蚀性气体,那么这会引起马达不运转。

FOR PROPER OPERATION, STORAGE AND OPERATING ENVIRONMENT MUST NOT CONTAIN CORROSIVE GASES.

FOR EXAMPLE H2S. SO2. NO2. CL2. ETC. IN ADDITION STORAGE ENVIRONMENT MUST NOT HAVE MATERIALS

THAT EMIT CORROSIVE GASES ESPECIALLY FROM SILICON, CYANIC. FORMALIN AND PHENOL GROUP. IN

THE MECHANISM OR THE SET. EXISTENCE OF CORROSIVE GASES MAY CAUSE NO ROTATION IN MOTOR.


7.5 注意马达的工作环境,避免含铁质等物体被马达吸住,否则马达将会产生噪声,性能会降低,从而减少产品可靠性。


DUE ATTENTION MUST BE PAID TO THE HANDLING AND WORKING ENVIRONMENTS BECAUSE SUCH OBJECTS
AS IRON POWDER IF ATTRACTED BY THE MOTOR MAGNENT, WILL CAUSE NOISE, CHARACTERISTIC
DETERIORATION THUS REDUCING THE TELIABILITY.

7.6 请不要在接近强磁场或有强磁场的仪器设备处保存或工作

PLEASE DO NOT KEEP OR WORK AT THE INSTRUMENTS AND EQUIPMENT CLOSE TO OR WITH STRONG MAGNETIC FIELD.

8、产品外形图 / PRODUCE OUTLINE DRAWING /JYLRA1040ZF





Technical Requirements:
Rated Voltage (Vac RMS):2.5v
Rated Current MAX (mA): 110 mArms
Rated Frequency: 180Hz
Resonant Frequency: 180±10Hz
Vibration Force (Grms):2.2
Vibration Direction: Z-AXIS

硬度	投影角 第一角	未注公差 ±0.05/±0.5	材料	比例 日期 2022.09.09
设计	审 核	批准: YCD	名称	
JIE YI ELECTRONICS LIMITED			캪号	JYLRA1040ZF
			图号	