PART4

KL Series KH–8005 Series KH–8010 Series



KL Series

Features

Housing is made of durable aluminum die-casting.

Heat-resistance, oil-resistance, vibration-resistance structure (protection IP67)

Built-in double-pole double-break standard micro-switches

Operation Indicator (LED or Neon lamp) helps easier inspection and maintenance

Microload models are available

	Roller lever		75°	90°	Roller lever, adjustable roller lever, adjustable rod lever, fork lever lock		
Actuator	Plunger		0		Top plunger, top roller plunger, sealed top roller plunger, top ball plunger, side roller plunger		
	Flexible rod		0		Coil spring, coil spring aluminum rod		
	Standard load	1a1b	0		Using of normal double pole, double break switch		
LUAU	Microload	1a1b					
Environment- resistance specification	High enclosed				Using of hermetic sealed built-in switch		
	Mold terminal		0		Lead wire attached Improved hermetic property with epoxy resin in receptacle part		
	Temperature- resistance	KLoo-T			Silicon rubber is used to improve temperature-resistance Available operation temperature (-40°C ~+120°C)		
Operation indicating lamp		KLoo-LE	0		Operation state can be monitored easily.		
operation indic		KL==-LD	(C	Turn on lamp when operating, available to turn on lamp when not-in-operating		





CLASSIFICATION

① Electric rating

-	Standard load			
1	Microload			

Actuator

Code	Actuator			
CA2	Roller lever (75° actuation)			
CA2-2	Roller lever (90° actuation)			
CA12	Adjustable roller lever (75° actuation)			
CA12-2	Adjustable roller lever (90° actuation)			
CL	Adjustable rod lever (75° actuation)			
CL-2	Adjustable rod lever (90°actuation)			
CA32-41	Fork lever lock			
CA32-42	Fork lever lock			
CA32-43	Fork lever lock			
CA32-44	Fork lever lock			
D	Top plunger			
D2	Top roller plunger			
D28	Sealed top roller plunger			
D3	Top ball plunger			
SD2	Side roller plunger			
NJ	Coil spring			
NJ-A2	Coil spring aluminum rod			

③ Environment-resistance specification

-	Standard			
Т	Corrosion-resistance			
А	Hermetic			

④ Identification of operation

Code	Element
-	Standard
LE	Neon lamp
LD	LED

⑤ Lamp Wiring

2	Connecting with NC: Light ON when operating
3	Connecting with NO: Light ON when not operating

(6) Temperature Specification

-	Standard -10°C ~ +80°C			
Т	Temperature-resistance -40°C ~ +120°C			

% Product for heat or cold resistance can be applied to roller lever type, adjustable roller lever type and adjustable rod lever type product.

⑦ Lever order specification

-	Standard			
SA	Forged lever (Aluminum)			
SS	STS lever			
S50	S lever (Roller O.D. Ø50)			
SA50	Forged lever (Roller O.D. Ø50)			

③ Connector order specification

SC-D6SW	Seal connector (DC)
SC-A6SW	Seal connector (AC)



ACTATION RANGE GUIDE



OF	Required force to actuate	Required force to move from free position (FP) to operating position (OP)
RF	Return force	Required force to return from total travel position (TTP) to return position (RP)
PT	Movement to actuation	Distance or angle of movement from free position (FP) to operating position (OP)
MD	Movement differential	Distance or angle of movement from operating position (OP) to return position (RP)
ОТ	Movement after actuation	Distance or angle of movement from operating position (OP) to total travel position (TTP)
OP	Operating position	Actuator position when a contact point (NO (normal open)) is actuated (On) at free position (FP).
FP	Free position	Actuator position when no external force is applied to actuator
TTP	Total travel position	Actuator position when actuator arrives at stop.
RP	Return position	Actuator when a contact point (NO) is off at operating position (OP).
TT	Entire movement	Distance or angle of movement from free position (FP) to total travel position (TTP).

RATINGS

Normal open circuit

_	Non-inductive load				Inductive load			
Rated Voltage	Resistance load		Lamp load		Resistance load		Motor load	
renage	NC	NO	NC	NC	NC	NO	NC	NO
AC125	10	10	3	1.5	6	3	5	2.5
AC250	10	10	2	1	6	3	3	1.5
AC480	6	6	1.5	0.8	3	3	1.5	0.8
AC600	3	1	1	0.5	1.	.5	1	0.5
DC8	10		6	3	6		6	
DC14	10		6	3	6		6	
DC30	6		4	3	6		6	
DC125	0.8		0.2	0.2	0.8		0.2	
DC250	0	.4	0.1	0.1	0.	.4	0	.1

DPDB Operation

Double-pole, Double-break structure for circuit breaking





PROPERTY DATA

Electrical durability (cosØ=1)



Rated Voltage (V)	Resistance load (A)		
AC 125	0.1		
DC 30	0.1		

Operational load range: DC5~30V, 0.5~100mA

UL, cUL Safety standards, UL508						
Rated Voltage Rated current						
250VAC	10A(resistance load)					
125VAC	10A(resistance load)					



CHARACTERISTICS

		Actuator		Dellarlayer	Adjustable	Adjustable	Fork lever	Dlunger	Flexible	
				Roller lever	roller lever	rod lever	lock	Plunger	Rod	
				KLCA2	KLCA12	KLCL	KLCA32-41	KLD	KLNJ	
Itomo	Model number		KLCA2-2	KLCA12-2	KLCL-2	KLCA32-42	KLD2	KLNJ-A2		
nems			KLCA2-S50			KLCA32-43	KLD28			
				KLCA2- SA50			KLCA32-44	KLD3		
								KLSD2		
External	Stand	dard specif	ication	IEC						
specification	Certi	fied specifi	ication	CE, certified	for electric p	roduct safety	/			
	Co	ntact point	type	Dual termina	l 2 circuit swi	tch				
Ctructure	Lood	Standa	rd load	Silver alloy						
Structure	Load	Micro	oload	Silver (gold p	lating)					
	Prot	tection stru	icture	IP67(IEC605	29), KLD2(IF	947)				
	10/3		4	Between live parts: AC1,000V 60/60Hz for 1minute						
Floctrical	VVI	Instand voi	tage	Between dea	d parts: AC2	,000V 50/60	Hz for 1 minu	te		
properties	Isol	ation resist	tance	Isolation resistance 100M Ω or more(DC500V isolation resistance gauge)						
	Contact (initia	resistance l value)	Standard load	25mΩ or below						
Allow	/ed opera	ating velocit	ty	1 mm/s ~ 1 m/s						
				Roller lever : 200 m/s2 of total travel position						
	Im	nact resists	ance	Non-directive actuation: 300 m/s2 of total travel position						
Mechanical		paol 1031312		Others: 300 m/s2 free position and total travel position						
performance				(Contact point in free position and total travel position or total travel position						
P				Double vibration width: 1.5 mm, frequency 10~55Hz, for 2 consecutive						
	Vibr	ation-resis	tance	hours						
				(Others: free position and total travel position)						
		Mechanica	al	10 million op	erations <plu< td=""><td>nger typeà5</td><td>million operat</td><td>ions, fork le</td><td>ver lock</td></plu<>	nger typeà5	million operat	ions, fork le	ver lock	
Durability			typeà2million operations>							
2	Electrical		750,000 opei	750,000 operations (when resistance is loaded 250VAC 10A)						
	Electrical (microload)		1 million operations							
Operating	Mechanical		120operations/min							
frequency		Electrical		30operations	/min					
Environment conditions	Amb	ient tempe	rature	-10°C ~ +80 [°] C (UL certified 40°C)						



Model No.	Actuator	Model No.	Actuator	
KLCA2(75° Max.) KLCA2-2(90° Max.) Poller lever		KLCA-S50 Ø50 Roller lever		
Right / Left		Right / Left	•	
KLCA12(75° Max.) KLCA12-2(90° Max.) Adjustable roller lever		KLSD2 Side roller plunger		
Right / Left		Right / Left		
KLCL(75° Max.) KLCL-2(90° Max.) Rod lever		KLNJ-A2 Coil spring aluminium rod		
Right / Left		Non-directional		
KLCA32-41, 42, 43, 44 FORK roller lever		KLD3 Top ball plunger		
Right / Left (90° Max.)		Up / Down		
KLNJ Coil spring		KLD28 Sealed top roller plunger		
Non-directional		Up / Down	•	
KLD2 Top roller plunger	P	KLD Top plunger		
Up / Down	(()	Up / Down		



15

3

LEVER TYPES & FIGURE



ROLLER LEVER(ON-DEMAND)-SA Forging





24.8

۲

12.1

ADJUSTABLE ROLLER LEVER (STANDARD)



FORK LEVER(CA32-41)



FORK LEVER(CA32-43)





ROLLER LEVER(ON-DEMAND)-SS Stainless





ADJUSTABLE ROD LEVER(STANDARD)





FORK LEVER(CA32-42)



FORK LEVER(CA32-44)





STRUCTURE

Return Spring - Secures minimum 90 degree of lever rotary angle by using Roller - made of stainless steel spring, mechanical durability is improved. (increased mechanical durability and abrasion resistance) Shaft - Increased sealing property by fitting of O-ring (protection IP67) Lever - made of forged anti-Return Gum - allowing corrosive aluminum alloy smooth actuation and (Optional) improving protection structure Plate to indicate adjust Plunger - allowing smooth position actuation by using spring inside. Built-in switch - double-pole double- break type 1a+1b Cover seal - Increased sealing property by fitting of O-ring in cover. Insulator - Isolation has been improved by using isolation paper.

> Conduit entrance – Screw for PF1/2 pipe is used and SC type is used with connector to improve sealing property.



KLCA2 Roller lever type







KLCA2 KLCA2-2



KLCA2-LD KLCA2-2LD

ACTUATION PROPERTY

Model	OF Max.	RF Max.	PT	OT Min.	MD Max.	Material	
KLCA2	910g	100g	20°	30°	12°	Body: Aluminium alloy die-	RF OF MD OT
KLCA2-2	910g	100g	30°	70°	10°	casting	
KLCA2-LE						Head: Aluminium alloy die- casting Roller: Stainless steal	
KLCA2-2LE		0	ational n	arta			
KLCA2-LD		U,	buonai pa	ans			
KLCA2-2LD						Protection degree: IP67	

NOTE

- Excessive force or impact to limit switch roller lever to activate switch may cause unstable actuation of actuator, shortening electrical and mechanical durability.
- Right and wrong examples of installation.





KLCA12 Adjustable roller lever type



KLCA12 KLCA12-2



KLCA12-2



KLCA12-LD KLCA12-2LD

ACTUATION PROPERTY

Model	OF Max.	RF Max.	PT	OT Min.	MD Max.	Material	
KLCA12	290g	25g	20°	30°	12°	Body: Aluminium alloy die-	RF OF MD
KLCA12-2	290g	25g	20°	70°	10°	casting	$ \langle \overline{1} / \overline{2} \rangle$
KLCA12-LE						Head: Aluminium alloy die- casting	
KLCA12-2LE		0	ation of m				
KLCA12-LD		Optional parts			Roller: Stainless steal		
KLCA12-2LD						Protection degree: IP67	

NOTE



Please adjust the length of the lever by loosening the screw. (0~64mm)

FOOT SWITCH

CONTROL

MICRO SWITCH



KLCL Adjustable rod lever type



ACTUATION PROPERTY

Model	OF Max.	RF Max.	PT	OT Min.	MD Max.	Material	
KLCL	290g	25g	20°	30°	12°	Body: Aluminium alloy die-	RE OF MD
KLCL-2	290g 25g 20° 70° 10°		casting				
KLCL-LE						Head: Aluminium alloy die-	
KLCL-2LE		0	ation of m			casting	
KLCL-LD		Op	buonai pa	arts		Roller: Stainless steal	
KLCL-2LD						Protection degree: IP67	1 - ale al

NOTE



Please adjust the length of the rod by loosening the screw. (0~115mm)





KLCA32 Fork roller lever type CONTROL COMPONENTS 60.5 Max KLCA32-42 MICRO SWITCH KLCA32-43 . M6×15 21.6 29.2 PF1/2 42 Max. FOOT SWITCH KLCA32-41 KLCA32-41 ~ 44 KLCA32-44

ACTUATION PROPERTY

Model	OF Max.	PT	OT Min.	Material	PT PT
KLCA32	1,220g	30°	30°	Body: Aluminium alloy die-casting	
KLCA32-LE			1	Head: Aluminium alloy die-casting	
KI CA32-I D	Ор	tional pa	rts	Roller: Stainless steal	
				Protection degree: IP67	

NOTE



NO current

LIMIT

POWER SWITCH

HOIST SWITCH

CAM SWITCH



KLD Top plunger type







KLD-LD

ACTUATION PROPERTY

KLD

Model	OF Max.	RF Min.	PT Max.	OT Min.	MD Max.	Material
KLD	2,720g	820g	1.7mm	6.4mm	1mm	Body: Aluminium alloy die-casting
KI D-I F		1	1		1	Head: Aluminium alloy die-casting
		C	optional part	ts		Roller: Stainless steal
KI D-I D			puonai pari			
						Protection degree: IP67

NOTE



KLD2 Roller plunger type







KLD2-LD

ACTUATION PROPERTY

Model	OF Max.	RF Min.	PT Max.	OT Min.	MD Max.	Material
KLD2	2,850g	810g	1.7mm	5.6mm	1mm	Body: Aluminium alloy die-casting
KLD2-LE)ntional par	to	1	Head: Aluminium alloy die-casting
KLD2-LD			puonai par	IS		Protection degree: IP67

NOTE

For side actuation of the product, recommended dimension is indicated as shown in the diagram.





CONTROL

MICRO SWITCH



KLD28 Sealed top roller plunger type







KLD28-LD

ACTUATION PROPERTY

Model	OF Max.	RF Min.	PT Max.	OT Min.	MD Max.	Material
KLD28	1,700g	450g	1.7mm	5.6mm	1mm	Body: Aluminium alloy die-casting
KI D28-I F		1	1	1	Head: Aluminium alloy die-casting	
		C)ntional par	ts	Roller: Stainless steal	
KI D28-I D			puonai pai			
				Protection degree: IP67		

NOTE

For side actuation of the product, recommended dimension is indicated as shown in the diagram.







KLD3 Top ball plunger type







KLD3-LD

ACTUATION PROPERTY

Model	OF Max.	RF Min.	PT Max.	OT Min.	MD Max.	Material
KLD3	2,720g	820g	1.7mm	4mm	1mm	Body: Aluminium alloy die-casting
KI D3-I F					Head: Aluminium alloy die-casting	
NED0-EE		C	Optional par	ts		Roller: Stainless steal
KLD3-LD						Protection degree: IP67

NOTE

For side actuation of the product, recommended dimension is indicated as shown in the diagram.



L(Degree)	Vmax(m/s)	У
30°	0.25	0.6~0.8(TT)
20°	0.5	0.5~0.7(TT)



CONTROL



KLSD2 Side roller plunger type







KLSD2

KLSD2

KLSD2-LD

ACTUATION PROPERTY

Model	OF Max.	RF Min.	PT Max.	OT Min.	MD Max.	Material
KLSD2	4,087g	97g	2.77mm	5.6mm	1mm	Body: Aluminium alloy die-casting
KI SD2-I F					1	Head: Aluminium alloy die-casting
		C	ptional par	ts	Roller: Stainless steal	
KLSD2-LD					Protection degree: IP67	





Model	OF Max.	PT Max.	Material	
KLNJ	150g	20mm ±10	Body: Aluminium alloy die-casting	
KI N.I-I F			Head: Aluminium alloy die-casting	SWO
	Optiona	al parts	Roller: Stainless steal	ITCH
KLNJ-LD			Protection degree: IP67	

CAM SWITCH



KLNJ - A2 Coil spring & Aluminium rod type





KLNJ

KLNJ-A2

KLNJ-LD

ACTUATION PROPERTY

Model	OF Max.	PT Max.	Material
KLNJ-A2	150g	28.6mm	Body: Aluminium alloy die-casting
		I	Head: Aluminium alloy die-casting
KLNJ-A2LE	Option	al parts	Roller: Stainless steal
KLNJ-A2LD	o pilotiai parte		
			Protection degree: IP67



Mounting





⊕

¢

30

To install the Switch, make a mounting panel, as shown in the diagram

L = 29.2mm+Tap depth Tap depth = 8mm min.

M6

CAM SWITCH

HOIST SWITCH

CONTROL COMPONENTS

MICRO SWITCH

FOOT SWITCH

LIMIT

POWER SWITCH

58.7



USING THE SWITCHES

Instructions	Applicable actuators	Description
The position to install actuator can be changed. Actuator position can be adjusted 360° by loosening hex bolt at actuator lever. In case the actuation indicating lamp is attached, please be careful to set the lever rotation because actuator lever may touch the top of lamp cover. Symmetrical lever does not touch the lamp cover.	Roller lever, Adjustable roller lever, Adjustable rod lever	Loosen M5 bolt and adjust its position. And then fix the bolt.
Head direction can be changed. By unscrewing 4 of corner screws of the head it can be adjusted to any of 4 directions. In this case the control plunger inside shall be adjusted as same.	Roller lever, Adjustable roller lever, Adjustable rod lever, Roller plunger, Side roller, Plunger	Screw Head
Roller can be installed inside. Roller can be installed inside by attaching roller upside down. (Please set to stop actuation within 180° horizontal range).	Roller lever, Fork lever LOCK	Loosen hex bolt or nut.
Lever rod length can be adjusted. Lever or rod length can be adjusted by loosening hex bolt.	Adjustable roller lever, Adjustable roller lever,	Loosen hex bolt and adjust lever length. Rod length can be adjusted by unscrewing nut.



LAMP INDICATOR

- It is convenient to check operation state and circuit and to find actuation by neon lamp (for AC power) or LED (for DC power).
- Lamp terminal (indicating lamp cover) connection is made through contact spring (coil spring) by using terminal screw of built-in switch. No wiring is required for lamp terminal.
- Indicating lamp cover is made of transparent resin together with aluminum die-casting so as to assure high sealing property, which allows normal operation even in the environment with cutting oil. Also, it enables monitoring the operating state. Further, it is easy to switch either light ON when Operating or light ON when not operating.
- This is most suitable to verify passing of goods in conveyor line or verifying operation in an area where verification is not easy.
- It's not necessary to change polarity for LED type because LED type has rectifying element internally.

Ratings

	Deted voltage	Lookogo ourront	Switch to install lamp	Lamp cover
	Raled vollage	Leakage current	Switch to install lamp	Туре
Neon lamp	125VAC	0.7mA Max	KL□-LE	KL-LE
LED	AC/DC 12~25V	4mA Max	KL□-LE	KL-LD

Operation



Factory setting is at "light ON when operating" mode.

For "light ON when not operating" mode, please switch LED to downward direction as shown in the figure.

SEAL CONNECTOR & CABLE

KL Series

KL series main body can be used as connector type by assembling components .

SEAL CONNECTOR

ITEM	PRODUCT NAME	POWER	NUMBER OF COR WIRES
KL□□-SC-D6SW	Soci connector tuno	Direct current (DC)	4 wires
KL□□-SC-A6SW	Sear connector type	Alternating current (AC)	4 wires

SPECIFICATION

Rated Current	10A	6A				
Rated voltage	AC125V	AC 250V				
Contact resistance	40mΩ or below(DC20mV or below, at 100mA α	or below)				
Insulation resistance	100MΩ or above(at DC500V)					
Dielectric strength	AC 1500V 1min.(Between live parts / Between	dead parts)				
Protection	IP67(IEC529)					
Tightening torque	0.8 NM					
Tensile strength	98N					
Operating temperature	-25°C ~+70°C					
Contact pin material	Brass (gold plating)					
Fixture material	Brass (nickel plating)					
Pin block material	PBT Glass(UL94-V0)					
O-ring material	NBR					
Housing material	Polyester elastomer					
Cord property (cable)	Increased resistance to oil / increased flexibility	ncreased resistance to oil / increased flexibility (300V 80°C)				

COMBINATION

+

Seal connector

Connector cable

CONNECTOR CABLE

ITEM	CORE WIRE	POWER	CORD LENGTH	WIRE COLOR	MATERIAL
D6SW-1	4 wires	Direct current (DC)	2 m	1(brown), 2(white), 3(blue), 4(black)	Soft PVC
A6SW-1	4 wires	Alternating current (AC)	2 m	1(brown), 2(white), 3(blue), 4(black)	Soft PVC

HOIST SWITCH

CAM SWITCH

MINI LIMIT SWITCH

KH-8005 Series

CLASSIFICATION

KH - 80 05 - S

1 2

① CONTACT RATING	05	250VAC, 5A(RESISTANCE LOAD)
② ACTUATOR	S	ROLLER LEVER
	С	ADJUSTABLE ROLLER LEVER
	R	ROD LEVER
	Р	PUSH PLUNGER
	PR	ROLLER PLUNGER
	CPR	CROSS-ROLLER PLUNGER
	SR	COIL SPRING

MODEL	OF(MAX.)	RF(min.)	PT	MD(MAX.)	OT(min.)	TT(min.)	MATERIAL
KH-8005-S	600g	50g	±150°	10°	75°	90°	Body, head: zinc-alloy die-casting Cover, roller: nylon glass Lever: Stainless steel
KH-8005-C	800g	21~50g	±150°	10°	75°	90°	Body, head: zinc-alloy die-casting Cover, roller: nylon glass Lever: Stainless steel
KH-8005-R	208~800g	12~50g	±150°	10°	75°	90°	Body, head: zinc-alloy die-casting Cover: nylon glass Rod: Stainless steel
KH-8005-P	900g	150g	2.0mm±1.0	0.7mm	4mm	4.5mm	Body, head: zinc-alloy die-casting Cover: nylon glass Shaft: free-cutting steel
KH-8005-PR KH-8005-CPR	900g	150g	1.5mm±0.5	0.7mm	4mm	5.5mm	Body, head: zinc-alloy die-casting Cover: nylon glass Roller : Stainless steel
KH-8005-SR	90g	-	10mm±5	-	20mm	20°	Body, head: zinc-alloy die-casting Cover: nylon glass Spring lever: Stainless steel

CONTROL COMPONENTS

CAM SWITCH

ACTATION RANGE GUIDE

OF	Required force to actuate	Required force to move from free position (FP) to operating position (OP)
RF	Return force	Required force to return from total travel position (TTP) to return position (RP)
PT	Movement to actuation	Distance or angle of movement from free position (FP) to operating position (OP)
MD	Movement differential	Distance or angle of movement from operating position (OP) to return position (RP)
ОТ	Movement after actuation	Distance or angle of movement from operating position (OP) to total travel position (TTP)
OP	Operating position	Actuator position when a contact point (NO (normal open)) is actuated (On) at free position (FP).
FP	Free position	Actuator position when no external force is applied to actuator
TTP	Total travel position	Actuator position when actuator arrives at stop.
RP	Return position	Actuator when a contact point (NO) is off at operating position (OP).
TT	Entire movement	Distance or angle of movement from free position (FP) to total travel position (TTP).

Installation

※ Maximum panel thickness must

be less than 5mm.

Front side installation

※ Hole depth must be 15mm(minimum). Back side installation

※ Maximum panel thickness must be less than 7mm.

Terminal lug

6.4 Max

3-3.7

[40] 하

Without insulation sleeve

With insulation sleeve

Ø 6.4 Max

[40]하

6.4 Max

3-3.7

3-3.7

(4이하

Without terminal lug

NO

With terminal lug

NC

σ

CAM SWITCH

Dimensions

KH-8005-C

KH-8005-R

7

KH-8005-P

KH-8005-S

KH-8005-PR

KH-8005-CPR

Technical Information

Ratings

Rated Voltage	Resistive Load	Inductive Load
125VAC	5A	3A
250VAC	5A	2A
125VDC	0.4A	0.1A

Mechanical Characteristics

Mechanical Lifetime Minimum 1,000,000 operation

Switching Frequency 120 operation per 1min.

Allowed Operating Rate 1mm/s ~ 1m/s

Electrical Characteristics

Standards

This product comply with " Standards for low-voltage switching devices" EN IEC 60947-5-1

Insulation Resistance Minimum 100MΩ (500VDC)

Contact Resistance Maximum 25mΩ

Electrical Lifetime 100,000 cycles of operation

Dielectric Strength Between Live Parts: 1,000VAC(50/60Hz) for 1 minute Between Live and Dead Parts: 2,000VAC(50/60Hz) for 1 minute

Contacts

Environmental conditions

Operational Temperature -25°C ~+50°C

Operational Humidity 45~85%RH

Protection Degree IP65

Shock Resistance Approximately 100G(1,000m/s2) Approximately 30G(300m/s2) at false operation

Vibration Resistance 10~55Hz double amplitude 1.5mm (at X, Y and Z axis)

Approvals

Approbations N/A

Declaration of Conformity CE

LIMIT SWITCH - MOUNTING TYPE

KH-8010 Series

KH-8010-RP

KH-8010-V1

CLASSIFICATION

KH-8010-RP - LEVER PUSH TYPE

KH-8010-V1 TERMINAL

KH-8010-V1 - CAM ROLLER ARM TYPE

Technical Information

Operation Specification

MODEL	MAX. OF	MIN. RF	PT	MIN. OT	MAX. MD
KH-8010-RP	1,500g	-	-	-	-
KH-8010-V1	682g	114g	15±5	55°	10°

Material

BODY KH-8010-RP: Aluminum Alloy Die Casting KH-8010-V1: Aluminum Alloy Die Casting

LEVER KH-8010-RP: Zinc Alloy Die Casting KH-8010-V1: Stainless Steel

ROLLER KH-8010-RP: Stainless Steel KH-8010-V1: Stainless Steel

Mechanical Characteristics

Mechanical Lifetime Minimum 1,000,000 operation

Switching Frequency 120 operation per 1min.

Allowed Operating Rate 1mm/s ~ 1m/s

Electrical Characteristics

Standards This product comply with "Standards for low-voltage switching devices" EN IEC 60947-5-1

Contact Ratings KH-8010-RP: 380VAC, 10A (resistive load) KH-8010-V1: 125VAC , 15A (resistive load)

Insulation Resistance Minimum 100MΩ (500VDC)

Contact Resistance Maximum $25m\Omega$

Electrical Characteristics—continues Electrical Lifetime Minimum 100,000 operation

Dielectric Strength Between Live Parts: 1,000VAC(50/60Hz) for 1 minute Between Live and Dead Parts: 2,000VAC(50/60Hz) for 1 minute

Environmental conditions

Operational Temperature -25 °C~+50°C (UL certified 40°C)

Operational Humidity 45~85%RH

Protection Degree IP40

Shock Resistance Approximately 100G(1,000m/s2) Approximately 30G(300m/s2) at false operation

Vibration Resistance 10~55Hz double amplitude 1.5mm (at X, Y and Z axis)

Approvals

Approbations UL

Declaration of Conformity N/A

