# Garant

Torque screwdriver, fixed setting, set torque: 1,5N·m



### Order data

Order number	211750 1,5
GTIN	4045197552396
Item class	21B

### Description

#### Version:

Torque screwdriver with easy-grip 2-component T-handle. The torque is fixed. Toolholder with permanent magnet.

#### **Function:**

When the torque is reached the screwdriver triggers **with clearly audible and perceptible signal**. The long-travel indication gives the user an unmistakable signal that the set torque has been reached.

#### **Application:**

In conjunction with **1/4 inch bits** with **C 6.3** or **E 6.3 shank,** e.g. **Torx Plus® bit** No. **674252.** Ideal for precise tightening of indexable inserts to the specified torque.

#### Standard:

Geprüft nach DIN EN ISO 6789.

#### Note:

#### Supplied without bit.

The guaranteed measuring accuracy of the torque is achieved only once the torque range has been calibrated to DIN EN ISO 6789.

Direction of tightening: Right-hand tightening

Torque measuring accuracy: ±15 %

Bit socket: D 6,3

## Data sheet

Bit socket: F 6.3 Torque measuring accuracy:  $\pm 15$  % Overall length L: 107 mm Blade length: 50 mm set torque: 1.5 N·m

# **Technical description**

set torque	1.5 N⋅m
Blade length	50 mm
Torque measuring accuracy	±15 %
Bit socket	D 6,3
Bit socket	F 6.3
Trigger principle	Mechanical long travel release
Overall length L	107 mm
Setting the trigger value	preset
Reversible reading	Nm
Feedback	triggering
Adjustable trigger value	non-adjustable
Standard	DIN EN ISO 6789
Connection format	Bit holder 1/4 inch
Measurement process	Torque
Direction of tightening	Right-hand tightening
Data can be recorded	no
Measurement technology	mechanical
Release signalling	akustisk
Release signalling	haptisk
Type of product	Torque screwdriver

## Accessories

"TQ-Station" – storage station for torque screwdrivers

659964