

**Garant**
**Torque screwdriver, fixed setting, set torque: 1,8N·m**


## Order data

Order number	211750 1,8
GTIN	4045197643865
Item class	21B

## Description

### Version:

Torque screwdriver with easy-grip 2-component T-handle. The torque is fixed. Toolholder with permanent magnet.

### Function:

When the torque is reached the screwdriver triggers **with clearly audible and perceptible signal**. The long-travel indication gives the user an unmistakable signal that the set torque has been reached.

### Application:

In conjunction with **1/4 inch bits** with **C 6.3** or **E 6.3 shank**, e.g. **Torx Plus® bit No. 674252**. Ideal for precise tightening of indexable inserts to the specified torque.

### Standard:

Geprüft nach DIN EN ISO 6789.

### Note:

Supplied **without** bit.

The guaranteed measuring accuracy of the torque is achieved only once the torque range has been calibrated to DIN EN ISO 6789.

Direction of tightening: Right-hand tightening

Torque measuring accuracy:  $\pm 15\%$

Bit socket: D 6,3

Bit socket: F 6.3  
 Torque measuring accuracy:  $\pm 15\%$   
 Overall length L: 107 mm  
 Blade length: 50 mm  
 set torque: 1.8 N·m

## Technical description

set torque	1.8 N·m
Blade length	50 mm
Torque measuring accuracy	$\pm 15\%$
Bit socket	D 6,3
Bit socket	F 6.3
Feedback	triggering
Adjustable trigger value	non-adjustable
Measurement process	Torque
Setting the trigger value	preset
Standard	DIN EN ISO 6789
Connection format	Bit holder 1/4 inch
Overall length L	107 mm
Reversible reading	Nm
Trigger principle	Mechanical long travel release
Direction of tightening	Right-hand tightening
Data can be recorded	no
Release signalling	akustisk
Release signalling	haptisk
Measurement technology	mechanical
Type of product	Torque screwdriver

## Accessories

"TQ-Station" – storage station for torque screwdrivers

659964