

Non-contact voltage testers



Order data

Order number	473011
GTIN	4045197838742
Item class	421

Description

Version:

Compact two-component plastic casing with integral LED torch. Prods with visual indication of voltage by colour change (green to red) and additional acoustic signal. Easily transported, fits any pocket.

Additional illumination of probe points and 12 V mode for low voltages.

Function:

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

Application:

For non-contact detection of live conductors, e.g. in cables, sockets, junction boxes etc.

Standard:

IEC/EN 61010-1.

Supplied with:

2 batteries No. 081551 size LR3. IP Index of Protection: IP 67 Display range AC: 12 - 1000 V

Overvoltage category: CAT IV / 1000 V

Article no of the battery / rechargeable battery fitted: 081561 LR3

Technical description

Overvoltage category	CAT IV / 1000 V
IP Index of Protection	IP 67
Display range AC	12 - 1000 V
Number of batteries contained	2



Article no of the battery / rechargeable battery fitted	081561 LR3
Power supply	Battery-powered
Type of product	Voltage tester

Accessories

Alkaline-manganese batteries International size LR3	081556 LR3
Alkaline-manganese batteries International size LR3	081561 LR3