

Telescopic roller cabinet, Number of containment trays: 3



Order data

Order number	914500 3
GTIN	4045197892058
Item class	9GT

Description

Version:

The telescopic roller cabinet has a stable, deep-drawn sheet metal construction with spacious base container, 2 storage trays, and cover with all-round protection edging and X-ABS mat.

Two telescopic columns with integral gas pressure springs (each with 20 kg spring force) provide support for opening and closing the cabinet, particularly when loaded. When closing, the telescopic columns slide into each other, so that there is no projection when closed. With fold-away handle for pulling and pushing.

Centrally lockable by means of a **cylinder lock**. With roller bearing wheels (2 castors with parking brake, 2 fixed wheels).

Supplied with:

Dividing material. 6 divider partitions 365 mm, 1 divider partition 435 mm, 1 divider partition for the base tray.

Colour:

Two-tone **powder-coated**, silver combined with RAL 7016 anthracite.

Cylinder lock: modular lock barrel

Height open: 935 mm Height closed: 520 mm

Width: 670 mm Depth: 365 mm



Storage compartment usable width: 435 mm Storage compartment usable depth: 330 mm

Technical description

Height open	935 mm
Storage compartment usable width	435 mm
Storage compartment usable depth	330 mm
Load capacity per cover/storage compartment	20 kg
Load capacity of base container	40 kg
Height closed	520 mm
Weight	24.4 kg
Depth	365 mm
Width	670 mm
Total number of troughs	3
Cylinder lock	modular lock barrel
Type of product	Roller cabinet

Accessories

Barrel sleeve 225-010-43 without lock barrel	914208
Set of anti-slip mats 5-piece for roller cabinets Type 3	914996 3