



50Ω Straight Flange Mount, SMA Connector, jack

# RoHS Compliant

## **FEATURES**

- 50Ω Impedance
- SMA Connector
- Flange Mount



Stock No.: 4141357C045

### Product Description

- SMA crimp termination types for use with a variety of flexible and semi-rigid cables
- Cable plugs in captive contact form for mechanical reliability in adverse conditions, or non-captive form for optimum electrical performance

### **General Specifications**


Attribute	Value
Gender	Female
Coaxial Connector Type	SMA Connector
Mounting Type	Flange Mount
Impedance	50Ω
Termination Method	Solder
Body Orientation	Straight
Bulkhead	No
Operating Frequency	0 to 18GHz
Body Plating	BBR
Minimum Operating Temperature	-65°C
Maximum Operating Temperature	+165°C
Contact Material	Beryllium Copper
Contact Plating	Gold over Nickel

After every difficulty, there is always ease.





#### **Product Drawing**



Dimensions: Millimeters (Inches)

#### **Part Number Table**

Part Number	Description
4141357C045	50Ω Straight Flange Mount, SMA Connector, jack

Important Notice: This data sheet and its contents (the "Information") belong to the members of the EASE group of companies (the "Group") or are licensed to it. No license is granted for the use of it other than for information purposes in connection with the products to which it relates. No license of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate, but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. EASE is the registered trademark of Ease Electronics Co., Limited 2019.