



#### 50Ω Straight Cable Mount, SMA Connector, jack

## RoHS Compliant



# 50Ω Impedance

**FEATURES** 

SMA Connector



### **Product Description**

50Ω Straight Cable Mount, SMA Connector, jack.


### **General Specifications**

| Attribute                     | Value                       |
|-------------------------------|-----------------------------|
| Gender                        | Female                      |
| Coaxial Connector Type        | SMA Connector               |
| Mounting Type                 | Cable Mount                 |
| Impedance                     | 50Ω                         |
| Termination Method            | Crimp                       |
| Body Orientation              | Straight                    |
| Cable Type                    | RG174/U, RG188 A/U, RG316/U |
| Bulkhead                      | No                          |
| Operating Frequency           | 0 to 18GHz                  |
| Minimum Operating Temperature | -65°C                       |
| Body Plating                  | Gold                        |
| Maximum Operating Temperature | +165°C                      |
| Contact Material              | Beryllium Copper            |
| Contact Plating               | Copper Nickel Gold Alloy    |





#### **Product Drawing**



Dimensions: Millimeters (Inches)

#### **Part Number Table**

| Part Number | Description                                   |
|-------------|---|
| 7123248C077 | 50Ω Straight Cable Mount, SMA Connector, jack |

Important Notice: This data sheet and its contents (the "Information") belong to the members of the EASE group of companies (the "Group") or are licensed to it. No license is granted for the use of it other than for information purposes in connection with the products to which it relates. No license of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate, but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility for less or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. EASE is the registered trademark of Ease Electronics Co., Limited 2019.