

# ELECTRIC DOUBLE LAYER SNAP-IN ULTRACAPACITOR

# **FEATURES**

- Over 500,000 duty cycles
- Extremely low ESR
- 10 year life capability
- Higher energy vs. electrolytic
- Higher power vs. batteries
- UL recognized
- RoHS compliant
- Halogen free
- Snap-In Termination

### **APPLICATIONS**

- Peak power handling
- Industrial automation
- UPS/voltage hold up






### **GENERAL SPECIFICATIONS**


Item	Performance						
Operating temperature	-40°C to +65°C @ 2.7V						
Operating temperature	-40°C to +85°C @ 2.3V						
Storage temperature	-40°C to +70°C						
Capacitance	800F						
Rated voltage	2.7 VDC / 2.3 VDC						
Surge voltage	2.85 VDC						
Temperature characteristics	Capacitance change: Within ±5% of initial measured value at +25°C (-40°C to +65°C)						
	Internal resistance: Within ±50% of initial measured value at +25°C (at -40°C)						
Endurance	After 1500 hours:						
(At rated voltage & max. operating	Capacitance change: Within ±20% of initial rated value						
temp)	Internal resistance: Within 2 times of initial specified value						
Projected Load life (At rated voltage & 25°C)	10 years:						
	Capacitance change: Within ±20% of initial rated value						
	Internal resistance: Within 2 times of initial specified value						
Projected cycle life	500,000 cycles:						
(From rated voltage to 1/2 rated	Capacitance change: Within ±20% of initial rated value						
voltage at 25°C)	Internal resistance: Within 2 times of initial specified value						
Shelf life	After 4 years at 25°C without load, the capacitor shall meet the specified endurance limits.						



# ELECTRIC DOUBLE LAYER SNAP-IN ULTRACAPACITOR

## **DIMENSIONS**





## **STANDARD PRODUCTS**

Part Number	Nom. Cap. (F)	GMV DO	ESR DC	ESR AC (mΩ)	Leakage Current (mA) (72 hrs @ 25C)	Dimensions (mm)		Rated Current	Weight/Unit
			(m?)			D	L	(A)	(grams)
TPLH-2R7/800PS35X71	800	760	3	2.8	1.7	35	71	318	95

\*NOTE: GMV = Guaranteed Minimum Value.