

## Broadcast and Professional AV Solutions



**Broadcast and Audio Video  
Products and Systems**

**Be certain.**

## Table of Contents


Table of Contents	Page	Table of Contents	Page
<p>This guide features Belden's most popular Broadcast and Audio/Visual products. Please visit <a href="http://www.belden.com">www.belden.com</a> or call 1,800,Belden,1 (1,800,235,3361) to learn more about our complete offering.</p>			
<b>Audio Solutions</b>	<b>3-4</b>	<b>Networking Solutions</b>	<b>10</b>
Microphone Cable	3	AV Multimedia Modules	10
Digital Microphone Cable	3	KeyConnect Faceplates	10
Analog Multi-Pair Snake Cable	3	<b>Networking Solutions — 10GX (TIA/EIA Category 6A LAN)</b>	<b>10-11</b>
Digital Multi-Pair Snake Cable	3	10GX KeyConnect Modular Jacks	10
Other Digital Audio Products	4	10GX KeyConnect Patch Panels	10
Line Level Cable	4	Category 6 Field-Installable Metal Body Ruggedized Plug	10
Intercom/Paging/Public Address Cable	4	10GX KeyConnect Patch Panels (featuring designation strips)	10
Speaker Cable	4	10GX Modular Cords (Bonded-Pairs CMR)	11
Class 1 Speaker Cable	4	10GX Category 6A Horizontal Cable	11
<b>Video Distribution Solutions (HD-SDI)</b>	<b>5</b>	10GXS Small Diameter Category 6A Cable	11
Miniature Coax Cable	5	10GX Pre-Terminated System	11
RG-59 Coax Cable	5	<b>Networking Solutions — CAT6+ (TIA/EIA Category 6 LAN)</b>	<b>11-12</b>
RG-6 Coax Cable	5	CAT6+ KeyConnect Modular Jacks	11
RG-7 Coax Cable	5	CAT6+ KeyConnect Patch Panels	11
RG-11 Coax Cable	5	CAT6+ KeyConnect Patch Panels (featuring designation strips)	11
<b>Video Camera Solutions</b>	<b>6</b>	CAT6+ Modular Cords (Bonded-Pairs CMR)	11
Triax Cable	6	CAT6+ Horizontal Cable	12
Electronic News Gathering (ENG) Cable	6	3600 Pre-Terminated System	12
SMPTE311M Cable	6	CAT6+ Shielded Cabling System	12
Tactical Fiber Cable	6	CAT6+ Accessories	12
<b>Video Display Solutions</b>	<b>6-8</b>	<b>Networking Solutions — CAT5E (TIA/EIA Category 5e LAN)</b>	<b>12-13</b>
RGB Cable	6	CAT5E KeyConnect Modular Jacks	12
S-Video Cable	6	CAT5E KeyConnect Patch Panels	12
Low Skew Cable	7	CAT5E Modular Cords (Bonded-Pairs CMR)	13
Nano Skew Patch Cords	7	CAT5E Horizontal Cable	13
HDMI Cable	7	CAT5E Shielded Cabling System	13
PerfectPath™ Locking HDMI - 700 Series	7	CAT5E Accessories	13
10GX Horizontal Cable	7	<b>Networking Solutions — FiberExpress® System</b>	<b>14-16</b>
CAT6+ Horizontal Cable	7	FX Brilliance Universal Connectors	14
CAT5E Horizontal Cable	7	FX Breakout Kits	14
Satellite and CATV Cable	8	FX Brilliance Installation Kit	14
CCTV Cable	8	FX UHD Housings	14
Distributed Antenna Systems (DAS) Cable	8	FX UHD Shelves	14
Video Display Accessories	8	FX UHD and FX Ultra Type-A Cassettes	14
<b>Commercial Automation and Control Solutions</b>	<b>8-9</b>	FX UHD and FX Ultra Type-A-Alternative Cassettes	15
Fiber Cabling and Connectors for Automation and Control	8	FX UHD and FX Ultra Frames	15
AMX™ and Crestron® Control System Cable	9	FX MPO Trunk Assemblies	15
DMX® System Cable	9	FX Patch Cords	16
<b>Cable Management Solutions</b>	<b>9</b>	FX Color-coded Pigtail Kits	16
Free Standing Enclosures	9	FX Cable	16
2 and 4 Post Racks	9	<b>Broadcast Cable Assemblies</b>	<b>17</b>
Vertical Cable Managers	9	<b>Part Number Index</b>	<b>18-19</b>
Wall Mount Enclosures	9	<b>Recommended Transmission Distance at Serial Digital Data Rates</b>	<b>20</b>
		<b>Return Loss Headroom (1694A)</b>	<b>20</b>

Be certain.



## Audio Solutions


### Microphone Cable

	Description	Belden Part Number	
		Non Plenum	
	26 AWG, Star Quad	1172A	
	24 AWG, Star Quad	1192A	
	24 AWG, 1 Pair, Braid Shield, Analog/Digital, CMR Rated	1800F	
	20 AWG, 2 Conductor, Rugged All-Rubber Construction	8412	
	20 AWG, 2 Conductor, High Strength Construction	1776	


### Digital Microphone Cable

	Description	Belden Part Number	
		Non Plenum	
	26 AWG, 1 Pair, Braid Shield	2221	
	24 AWG, 1 Pair, Braid Shield, Analog/Digital, CMR Rated	1800F	

### Analog Multi-Pair Snake Cable


	Description	Belden Part Number			
		Non Plenum	Plenum	Banana Peel Plenum	Waterblocked
	24 AWG, 4 Pair, Individually Shielded/Jacketed, Flexible	1510C	—	—	—
	24 AWG, 6 Pair, Individually Shielded/Jacketed, Flexible	1511C	—	—	—
	24 AWG, 8 Pair, Individually Shielded/Jacketed, Flexible	1512C	—	—	—
	24 AWG, 12 Pair, Individually Shielded/Jacketed, Flexible	1513C	—	—	—
	24 AWG, 16 Pair, Individually Shielded/Jacketed, Flexible	1514C	—	—	—
	22 AWG, 2 Pair, Bonded Foil, Siamese Construction	9451D	9451DP	—	—
	22 AWG, 2 Pair, Individually Shielded/Jacketed, Install	1814R	—	—	1814WB
	22 AWG, 4 Pair, Individually Shielded/Jacketed, Install	1815R	1815P	9451PS4	1815WB
	22 AWG, 6 Pair, Individually Shielded/Jacketed, Install	1816R	1816P	9451PS6	1816WB
	22 AWG, 8 Pair, Individually Shielded/Jacketed, Install	1817R	1817P	—	1817WB
	22 AWG, 12 Pair, Individually Shielded/Jacketed, Install	1818R	1818P	—	1818WB
	22 AWG, 16 Pair, Individually Shielded/Jacketed, Install	1819R	—	—	—
	22 AWG, 20 Pair, Individually Shielded/Jacketed, Install	1820R	—	—	—
	22 AWG, 24 Pair, Individually Shielded/Jacketed, Install	1821R	—	—	—
	22 AWG, 26 Pair, Individually Shielded/Jacketed, Install	1822R	—	—	—
	22 AWG, 32 Pair, Individually Shielded/Jacketed, Install	1823R	—	—	—
	22 AWG, 2 Pair, Individually Shielded	—	6541PA	—	—
	22 AWG, 3 Pair, Individually Shielded	—	6542PA	—	—
	22 AWG, 4 Pair, Individually Shielded	—	6543PA	—	—
	22 AWG, 6 Pair, Individually Shielded	—	6545PA	—	—
	22 AWG, 8 Pair, Individually Shielded	—	6546PA	—	—
	22 AWG, 12 Pair, Individually Shielded	—	6548PA	—	—
	22 AWG, 16 Pair, Individually Shielded	—	6549PA	—	—

### Digital Multi-Pair Snake Cable


	Description	Belden Part Number	
		Non Plenum	Plenum
	24 AWG, 1 Pair, Foil Shield	1800B	1801B
	24 AWG, 2 Pair, Foil Shield, Siamese Construction	1802B	1801BD
	26 AWG, 4 Pair, Individually Shielded/Jacketed Pairs	7890A	SPECIAL - Call for Details
	26 AWG, 8 Pair, Individually Shielded/Jacketed Pairs	7880A	—
	26 AWG, 12 Pair, Individually Shielded/Jacketed Pairs	7892A	—
	26 AWG, 16 Pair, Individually Shielded/Jacketed Pairs	7893A	—
	24 AWG, 2 Pair, Individually Shielded/Jacketed Pairs	1802F	—
	24 AWG, 4 Pair, Individually Shielded/Jacketed Pairs	1803F	—
	24 AWG, 4 Pair, Individually Shielded/Jacketed, Banana Peel Construction	—	1801BS4
	24 AWG, 6 pair, Individually Shielded/Jacketed, Banana Peel Construction	—	1801BS6
	24 AWG, 8 Pair, Individually Shielded/Overall Shield	1805F	—
	24 AWG, 12 Pair, Individually Shielded/Overall Shield	1806F	—
	24 AWG, 16 Pair, Individually Shielded/Overall Shield	1850F	—
	24 AWG, 24 Pair, Individually Shielded/Overall Shield	1852F	—
	24 AWG, 32 Pair, Individually Shielded/Overall Shield	1854F	—

## Audio Solutions (continued)


### Other Digital Audio Products

	Description	Belden Part Number	
		Non Plenum	
	AES/EBU Digital Audio, 1 Pair, Category 5E, Patch	1353A	
	CatSnake, 4 Pair, Category 5E, Heavy Duty	1304A	
	CatSnake, 16 Pair, Category 5e, Individually and Overall Jacketed	1304A4	
	CatSnake, 4 Pair, Category 5E, Heavy Duty, Flexible, Upjacketed	1305A	
	Digital Audio Coax	See Video Distribution Solutions on page 5.	


### Line Level Cable

	Description	Belden Part Number		
		Non Plenum	Plenum	Waterblocked
	22 AWG, 1 Pair	8451	—	—
	22 AWG, 1 Pair, Bonded Foil	9451	9451P	9451WB
	22 AWG, 2 Pair, Bonded Foil, Siamese Construction	9451D	9451DP	—
	22 AWG, 2 Pair, Individually Shielded	8723	82723	—


### Intercom/Paging/Public Address Cable

	Description	Belden Part Number				
		Bare Copper		Tinned Copper		
		Non Plenum	Plenum	Non Plenum	Plenum	Waterblocked
	22 AWG, 1 Pair, Shielded	5500FE	6500FE	5500FH	6500FH	5500F1
	22 AWG, 1 Pair, Shielded, Foil Bonded to Jacket for Easy Stripping	—	—	—	6500PE	—
	20 AWG, 1 Pair, Shielded	5400FE	6400FE	5400FH	6400FH	—
	18 AWG, 1 Pair, Shielded	5300FE	6300FE	5300FH	6300FH	5300F1
	16 AWG, 1 Pair, Shielded	5200FE	6200FE	5200FH	6200FH	5240F1
	14 AWG, 1 Pair, Shielded	5100FE	6100FE	5100FH	6100FH	5140F1
	12 AWG, 1 Pair, Shielded	5000FE	6000FE	5000FH	6000FH	—
	22 AWG, 1 Pair, Shielded + 22 AWG, 2 Conductor	5502GE	6502GE	—	—	—
	18 AWG, 1 Pair, Shielded + 18 AWG, 2 Conductor	5302GE	—	—	—	—
	22 AWG, 4 Conductor, Shielded	5502FE	6502FE	—	—	—
	18 AWG, 4 Conductor, Shielded	5302FE	6302FE	—	—	—
	22 AWG, 2 Pair, Individually Shielded	—	—	1325R	1325A	—
	22 AWG, 3 Pair, Individually Shielded	—	—	1326R	1326A	—

### Speaker Cable

	Description	Belden Part Number				
		Bare Copper		Tinned Copper		
		Non Plenum	Plenum	Non Plenum	Plenum	Waterblocked
	18 AWG, 2 Conductor, 7 strand	5300UE	6300UE	5300UH	6300UH	5300U1
	18 AWG, 4 Conductor, 7 strand	5302UE	6302UE	5302UH	6302UH	5302U1
	16 AWG, 2 Conductor, 19 strand	5200UE	6200UE	—	—	5240U1
	16 AWG, 4 Conductor, 19 strand	5202UE	6202UE	5202UH	6202UH	5202U1
	14 AWG, 2 Conductor, 19 strand	5100UE	6100UE	—	—	5140U1
	14 AWG, 4 Conductor, 19 strand	5102UE	6102UE	5102UH	6102UH	5102U1
	12 AWG, 2 Conductor, 19 strand	5000UE	6000UE	5000UH	6000UH	—
	10 AWG, 2 Conductor, 65 strand	5T00UP	6T00UP	—	—	—
	16 AWG, 2 Conductor, Oxygen-free High Conductivity, Indoor/Outdoor	1307A	—	—	—	—
	16 AWG, 4 Conductor, Oxygen-free High Conductivity, Indoor/Outdoor	1308A	—	—	—	—
	14 AWG, 2 Conductor, Oxygen-free High Conductivity, Indoor/Outdoor	1309A	—	—	—	—
	14 AWG, 4 Conductor, Oxygen-free High Conductivity, Indoor/Outdoor	1310A	—	—	—	—
	12 AWG, 2 Conductor, Oxygen-free High Conductivity, Indoor/Outdoor	1311A	—	—	—	—
	12 AWG, 4 Conductor, Oxygen-free High Conductivity, Indoor/Outdoor	1312A	—	—	—	—
	10 AWG, 2 Conductor, Oxygen-free High Conductivity, Indoor/Outdoor	1313A	—	—	—	—

### Class 1 Speaker Cable

	Description	Belden Part Number		
		Non Plenum	Waterblocked	High Strand
	8 AWG Class 1 Speaker Cable	8808	8808WB	8808H
	10 AWG Class 1 Speaker Cable	8810	8810WB	8810H
	12 AWG Class 1 Speaker Cable	8812	—	—
	14 AWG Class 1 Speaker Cable	8814	—	—



Be certain.



## Video Distribution Solutions (HD-SDI)

### Miniature Coax Cable

Description	Belden Part Number								
	Cable	4.5 GHz Compression				4.5 GHz Crimp			
		BNC Connectors	BNC Locking	Compression Tool	Strip Tool	BNC 3 Piece	Crimp Tool	Strip Tools	Boots
SubMiniature, 28.5 AWG, Precision Video, Non Plenum	179DT	179DTBHD1	179DTBHDL	CPLCRBC-BR	PS59/6/RGB	179DTBHD3	BB3PHCT	BB3PST	SLS-RGB-*
Miniature 23 AWG Precision Video, Non Plenum and Plenum	1855A	1855ABHD1	1855ABHDL	CPLCRBC-BR	PS59/6/RGB	1855ABHD3	BB3PHCT	BB3PST	SLS-RGB-*
Miniature RG59 Precision Video, Non Plenum and Plenum	1855P	1855ABHD1	1855ABHDL	CPLCRBC-BR	PS59/6/RGB	1855ABHD3	BB3PHCT	BB3PST	SLS-RGB-*
5 Cond Miniature 23 AWG Precision Video, Non Plenum, Banana Peel	1855SS	1855ABHD1	1855ABHDL	CPLCRBC-BR	PS59/6/RGB	1855ABHD3	BB3PHCT	BB3PST	SLS-RGB-*
VideoFlex 5 Pack Snake, Non Plenum (1855A)	7789A	1855ABHD1	1855ABHDL	CPLCRBC-BR	PS59/6/RGB	1855ABHD3	BB3PHCT	BB3PST	SLS-RGB-*

\* indicate color when ordering, Yellow, Red, White or Black

### RG-59 Coax Cable

Description	Belden Part Number								
	Cable	4.5 GHz Compression				4.5 GHz Crimp			
		BNC Connectors	BNC Locking	Compression Tool	Strip Tool	BNC 3 Piece	Crimp Tool	Strip Tools	Boots
RG59 Precision Video, Non Plenum	1505A	1505ABHD1	1505ABHDL	CPLCRBC-BR	PSA59/6	1505ABHD3	BB3PHCT	BB3PST	SLS-59/6
RG59 Precision Video, Plenum	1506A	1506ABHD1	1506ABHDL	CPLCRBC-BR	PSA59/6	1506ABHD3	BB3PHCT	BB3PST	SLS-59/6
RG59 Precision Video, Flexible	1505F	1505ABHD1	1505ABHDL	CPLCRBC-BR	PSA59/6	1505ABHD3	BB3PHCT	BB3PST	SLS-59/6
5 Cond RG59 Precision Video, Non Plenum, Banana Peel	1505SS	1505ABHD1	1505ABHDL	CPLCRBC-BR	PSA59/6	1505ABHD3	BB3PHCT	BB3PST	SLS-59/6
VideoFlex 5 Pack Snake, Non Plenum (1505A)	7796A	1505ABHD1	1505ABHDL	CPLCRBC-BR	PSA59/6	1505ABHD3	BB3PHCT	BB3PST	SLS-59/6

### RG-6 Coax Cable

Description	Belden Part Number								
	Cable	4.5 GHz Compression				4.5 GHz Crimp			
		BNC Connectors	BNC Locking	Compression Tool	Strip Tool	BNC 3 Piece	Crimp Tool	Strip Tools	Boots
RG6 Precision Video, Non Plenum	1694A	1694ABHD1	1694ABHDL	CPLCRBC-BR	PSA59/6	1694ABHD3	BB3PHCT	BB3PST	SLS-59/6
RG6 Precision Video, Plenum	1695A	1695ABHD1	1695ABHDL	CPLCRBC-BR	PSA59/6	1694ABHD3	BB3PHCT	BB3PST	SLS-59/6
RG6 Precision Video, Flexible	1694F	1694ABHD1	1694ABHDL	CPLCRBC-BR	PSA59/6	1694ABHD3	BB3PHCT	BB3PST	SLS-59/6
RG6 Precision Video, Dual Link	1694D	1694ABHD1	1694ABHDL	CPLCRBC-BR	PSA59/6	1694ABHD3	BB3PHCT	BB3PST	SLS-59/6
RG6 Precision Video, Indoor/Outdoor Waterblocked	1694WB	1694ABHD1	1694ABHDLW*	CPLCRBC-BR	PSA59/6	1694ABHD3	BB3PHCT	BB3PST	SLS-59/6
5 Pack Snake, Non Plenum (1694A), Banana Peel	1694SS	1694ABHD1	1694ABHDL	CPLCRBC-BR	PSA59/6	1694ABHD3	BB3PHCT	BB3PST	SLS-59/6
5 Pack Snake, Plenum (1695A), Banana Peel	1695SS	1695ABHD1	1695ABHDL	CPLCRBC-BR	PSA59/6	1694ABHD3	BB3PHCT	BB3PST	SLS-59/6
VideoFlex 5 Pack Snake, Non Plenum (1694A)	7712A	1694ABHD1	1694ABHDL	CPLCRBC-BR	PSA59/6	1694ABHD3	BB3PHCT	BB3PST	SLS-59/6

\*Connector is also watertight.

### RG-7 Coax Cable


Description	Belden Part Number			
	Cable	Connectors 4.5 Gig BNC Compression	Compression Tool	Strip Tool
RG7 Precision Video, Non Plenum	1794A	1794ABHD1	CPLCRBC1794	PS-11

### RG-11 Coax Cable

Description	Belden Part Number					
	Cable	Connectors 3.0 Gig BNC Compression	BNC Compression Tool	Connectors 3.0 Gig F Compression	F Compression Tools	Strip Tool
RG11 Precision Video, Non Plenum	7731A	FSNS11QHBC	SNSUNI, CPLCCT-11BNC	716SNS1P11HQ	SNSUNI, L3011B, CPLCCT-SS59/11	PS-11
RG11 Precision Video, Plenum	7732A	FSNS11HBCPLA	SNSUNI, CPLCCT-11BNC	716SNS1P11HPLA	SNSUNI, L3011B, CPLCCT-SS59/11	PS-11
RG 11 Precision Video, Waterblocked	7731WB	FSNS11QHBC	SNSUNI, CPLCCT-11BNC	716SNS1P11HQ	SNSUNI, L3011B, CPLCCT-SS59/11	PS-11


## Video Camera Solutions

### Triax Cable


	Description	Belden Part Number		
		Non Plenum	Plenum	Waterblocked
	RG59 Triax	8232, 8232A or 1856A	88232	—
	RG59 High Flex Triax	1857A	—	—
	RG11 Triax	8233A	8233P	8233WB
	RG11 High Flex Triax	1858A	1859A	—

For information about Triax Cable Assemblies, please see page 17.

### Electronic News Gathering (ENG) Cable


	Description	Belden Part Number
	2 RG59 20 AWG digital coax (150A) + 4 Pair 22 AWG, Shielded, for analog audio (9451)	1347A
	RG59 ENG EFP Applications (Connectors and Tools)	1505ABHD1, CPLCRBC-BR, PSA59/6, SLS-59/6

### SMPTE 311M Cable

	Description	Belden Part Number		
		Non Plenum	Plenum	Waterblocked
	Light Duty	7804LW	—	—
	12 mm Double Jacket Studio	7817A	—	—
	Outdoor Harsh Environment	7818A	—	—
	Industry Standard SMPTE 311M HDTV - (2) fiber, (2) 24 AWG, (4) 20 AWG	7804R	7804P	7804WB
	Heavy Gauge SMPTE 311M HDTV - (2) fiber, (2) 24 AWG, (2) 16 AWG	7804C	—	—
	3 Channel SMPTE Stadium Cable	7824R	7824P	7824WB
	Electrical Camera Cable	7825R	7825P	—

For information about SMPTE 311M Cable Assemblies, please see page 17.


### Tactical Fiber Cable

	Description	Belden Part Number	
		Singlemode	62.5/125 µm
	2 Channel *Neutrik Certified for use with OpticalCON Connectors	B96566	B96571
	4 Channel *Neutrik Certified for use with OpticalCON Connectors	B96639	B96551
	6 Channel	B96567	B96572
	8 Channel	B96568	B96573
	10 Channel	B96569	B96574
	12 Channel	B96570	B96575


For information about Tactical Fiber Cable Assemblies, please see page 17.

## Video Display Solutions

### RGB Cable

	Description	Belden Part Number			
		Cable	3.0 Gig BNC Compression	Compression Tool	Strip Tool
	5 Conductor Mini Hi-Res RGB, Non Plenum	1279R	FS1BNC	CPLCCT-SLM	PS59/6/RGB
	5 Conductor Mini Hi-Res RGB, Plenum	1279P	FS1BNC	CPLCCT-SLM	PS59/6/RGB
	Banana Peel 5 Conductor Mini Hi-Res RGB, Non Plenum	1281S5	FS1BNC	CPLCCT-SLM	PS59/6/RGB
	Banana Peel 5 Conductor Mini Hi-Res RGB, Plenum	1282S5	FS1BNC	CPLCCT-SLM	PS59/6/RGB
	3 Conductor Mini Hi-Res RGB, Non Plenum	1277R	FS1BNC	CPLCCT-SLM	PS59/6/RGB
	3 Conductor Mini Hi-Res RGB, Plenum	1277P	FS1BNC	CPLCCT-SLM	PS59/6/RGB
	1 Conductor, 75 Ohm Miniature Coax, Non Plenum	1281R	FS1BNC	CPLCCT-SLM	PS59/6/RGB
	1 Conductor, 75 Ohm Miniature Coax, Plenum	1281P	FS1BNC	CPLCCT-SLM	PS59/6/RGB

### S-Video Cable


	Description	Belden Part Number
	S-Video Dual 30 AWG Coax Twin Parallel Flat, Non Plenum	1807A
	S-Video Dual 30 AWG Coax Twin Parallel Flat, Plenum	7700A
	S-Video Dual 30 AWG Coax Round, Non Plenum	1808A

Be certain.



## Video Display Solutions (continued)


### Low Skew Cable

	Description	Belden Part Number	
		Cable	RJ-45 Plugs
	Nano Skew, Non Plenum	7987R	R301602, R301601
	Nano Skew, Plenum	7987P	R301602, R301601
	Low Skew Cat 5E, Non Plenum	7988R	R301602, R301601
	Low Skew Cat 5E, Plenum	7988P	R301602, R301601


### Nano Skew Patch Cords

Description	Ft	M	Belden Part Number	
			Non Plenum CMR	Plenum CMP
Nano Skew UTP/3	3	0.9	AC303569	AC303579
Nano Skew UTP/6	6	1.8	AC303570	AC303580
Nano Skew UTP/12	12	3.7	AC303571	AC303581
Nano Skew UTP/25	25	7.6	AC303572	AC303582
Nano Skew UTP/35	35	10.7	AC303573	AC303583
Nano Skew UTP/50	50	15.2	AC303574	AC303584
Nano Skew UTP/75	75	22.8	AC303575	AC303585
Nano Skew UTP/100	100	30.5	AC303576	AC303586

### HDMI Cable


	Description	Belden Part Number
	HDMI Cable Assemblies, 1 Meter	HD2001
	HDMI Cable Assemblies, 2 Meter	HD2002
	HDMI Cable Assemblies, 3 Meter	HD2003
	HDMI Cable Assemblies, 4 Meter	HD2004
	HDMI Cable Assemblies, 7 Meter	HD2007

### Perfect Path™ Locking HDMI - 700 Series

	Description	Belden Part Number
	High Speed Cable w/ Ethernet Channel and PerfectLock™ Connectors, 2 feet	HD-700-2
	High Speed Cable w/ Ethernet Channel and PerfectLock™ Connectors, 4 feet	HD-700-4
	High Speed Cable w/ Ethernet Channel and PerfectLock™ Connectors, 8 feet	HD-700-8
	High Speed Cable w/ Ethernet Channel and PerfectLock™ Connectors, 16 feet	HD-700-16
	High Speed Cable w/ Ethernet Channel and PerfectLock™ Connectors, 25 feet	HD-700-25
	High Speed Cable w/ Ethernet Channel and PerfectLock™ Connectors, 35 feet	HD-700-35
	High Speed Cable w/ Ethernet Channel and PerfectLock™ Connectors, 50 feet	HD-700-50


Features Perfect Lock™ locking connectors with 25lbs retention.

### 10GX Horizontal Cable

	Description	Belden Part Number				
		Bonded		Non-Bonded		
		Blue	White	Blue	White	Purple
	10GX Solution - CMR	10GX32 0061000	10GX32 0091000	10GX12 0061000	10GX12 0091000	10GX12 0071000
	10GX Solution - CMP	10GX33 D151000	10GX33 0091000	10GX13 D151000	10GX13 0091000	10GX13 0071000


Other colors available

### CAT6+ Horizontal Cable

	Description	Bonded			Non-Bonded			
		Blue	White	Black	Blue	White	Purple	Black
		3600 Solution - CMR	3632 006A1000	3632 009A1000	3632 010A1000	3612 006A1000	3612 009A1000	3612 007A1000
3600 Solution - CMP	3633 D15A1000	3633 009A1000	3633 010A1000	3613 D15A1000	3613 009A1000	3613 007A1000	3613 010A1000	
2400 Solution - CMR	1872A 006A1000	1872A 009A1000	1872A 010A1000	2412 006A1000	2412 009A1000	2412 007A1000	2412 010A1000	
2400 Solution - CMP	1874A D15A1000	1874A 009A1000	1874A 010A1000	2413 D15A1000	2413 009A1000	2413 007A1000	2413 010A1000	

Other colors available


### CAT5E Horizontal Cable

	Description	Bonded			Non-Bonded			
		Blue	White	Black	Blue	White	Purple	Black
		1200 Solution - CMR	1700A 006U1000	1700A 009U1000	1700A 010U1000	1212 006U1000	1212 009U1000	1212 007U1000
1200 Solution - CMP	1701A D15U1000	1701A 009U1000	1701A 010U1000	1213 D15U1000	1213 009U1000	1213 007U1000	1213 010U1000	

Other colors available


## Video Display Solutions (continued)

### Satellite and CATV Cable

	Description	Belden Part Number					
		Cable	F	RCA	BNC	Connector Tool BNC Compression	Strip Tool
	DBS/Satellite - RG-6 18 AWG Solid BC Dual Shield, Non Plenum	1829AC	FSNS6U	FSNS6RCAU	FSNS6BNCU	CPSNSCT-596 or CPLCCT-SLM	PSA59/6
	CATV - RG-6 18 AWG Solid CCS Dual Shield, Non Plenum	9116	FSNS6U	FSNS6RCAU	FSNS6BNCU	CPSNSCT-596 or CPLCCT-SLM	PSA59/6
	CATV - RG-6 18 AWG Solid CCS Dual Shield, Plenum	9116P	FSNS6PL	FSNS6RCAPL	FSNS6BNCPL	CPSNSCT-596 or CPLCCT-SLM	PSA59/6
	CATV - RG-6 18 AWG Solid CCS Quad Shield, Non Plenum	1189A	FSNS6U	FSNS6RCAU	FSNS6BNCU	CPSNSCT-596 or CPLCCT-SLM	PSA59/6
	CATV - RG-6 18 AWG Solid CCS Quad Shield, Plenum	1189AP	FSNS6PLQ	FSNS6RCAPLQ	FSNS6BNCPLQ	CPSNSCT-596 or CPLCCT-SLM	PSA59/6
	CATV - RG11 14 AWG Solid CCS Dual Shield, Non Plenum	1523A	716SNS1P11H	—	FSNS11HBNC	SNSUNI or CPLCCT-11BNC	PS-11
	CATV - RG11 14 AWG Solid CCS Dual Shield, Plenum	1523AP	716SNS1P11HPLA	—	FSNSHBNCPLA	SNSUNI or CPLCCT-11BNC	PS-11
	CATV - RG11 14 AWG Solid CCS Quad Shield, Non Plenum	7999A	—	—	—	—	—
	CATV - RG11 14 AWG Solid CCS Quad Shield, Plenum	7999AP	—	—	—	—	—

\* RG11 BNC Compression Connectors to 1.0 Gig

### CCTV Cable

	Description	Belden Part Number				
		Cable	Connectors F Compression	BNC Compression	Connector Tool BNC Compression	Strip Tool
	CCTV - RG59 20 AWG Solid BC 95% Braid Shield Non Plenum	543945	FSNS59U	FSNS59BNC SL	CPSNSCT-596 or CPLCCT-SLM	PSA59/6
	CCTV - RG59 20 AWG Solid BC 95% Braid Shield Plenum	643948	FSNS59PL	FSNS59BNC PL	CPSNSCT-596 or CPLCCT-SLM	PSA59/6
	CCTV - RG59 20 AWG Solid BC 95% Braid Shield + 18/2 Non Plenum	549945	FSNS59U	FSNS59BNC SL	CPSNSCT-596 or CPLCCT-SLM	PSA59/6
	CCTV - RG59 20 AWG Solid BC 95% Braid Shield + 18/2 Plenum	649948	FSNS59PL	FSNS59BNC PL	CPSNSCT-596 or CPLCCT-SLM	PSA59/6
	CCTV - RG6 18 AWG Solid BC 95% Braid Shield Non Plenum	533945	FSNS6U	FSNS6BNCU	CPSNSCT-596 or CPLCCT-SLM	PSA59/6
	CCTV - RG6 18 AWG Solid BC 95% Braid Shield Plenum	633948	FSNS6PL	FSNS6BNCPL	CPSNSCT-596 or CPLCCT-SLM	PSA59/6
	CCTV - RG6 18 AWG Solid BC 95% Braid Shield + 18/2 Non Plenum	539945	FSNS6U	FSNS6BNCU	CPSNSCT-596 or CPLCCT-SLM	PSA59/6
	CCTV - RG6 18 AWG Solid BC 95% Braid Shield + 18/2 Plenum	639948	FSNS6PL	FSNS6BNCPL	CPSNSCT-596 or CPLCCT-SLM	PSA59/6

### Distributed Antenna Systems (DAS) Cable

Description	Belden Part Number
Wireless - RG58	8240

### Video Display Accessories

Description	Belden Part Number
Strain Relief Boot for RGB/Mini Coax	SLS-RGB
Strain Relief Boot for RG-59 and RG-6	SLS-59/6

## Commercial Automation and Control Solutions

### Fiber Cabling and Connectors for Automation and Control

Description	Belden Part Number
For use in AV control systems: 4 fiber OM4 50/125 Multi-mode breakout style cable Non plenum	B9E006
For use in AV control systems: 4 fiber OM4 50/125 Multi-mode breakout style cable Plenum	B9E014
Brilliance SC FiberExpress Connector for 900 Micron Fiber	AX105207-S1 / AX105207-B25
Precision Installation Kit (Basic Kit, Fiber Preparation Tools, Precision Cleaver and Visual Fault Locator)	AX104271
FX PATCH CORD, OM4, LC DUPLEX - LC DUPLEX, OFNR, DUPLEX ZIP 2.0 MM, A-TO-B, ERIKA VIOLET JACKET, 20 M	FP4LDLD020MR2XE
FX PATCH CORD, OM4, LC DUPLEX - LC DUPLEX, OFNR, DUPLEX ZIP 2.0 MM, A-TO-B, ERIKA VIOLET JACKET, 30 M	FP4LDLD030MR2XE
FX PATCH CORD, OM4, LC DUPLEX - LC DUPLEX, OFNR, DUPLEX ZIP 2.0 MM, A-TO-B, ERIKA VIOLET JACKET, 40 M	FP4LDLD040MR2XE
FX PATCH CORD, OM4, LC DUPLEX - LC DUPLEX, OFNR, DUPLEX ZIP 2.0 MM, A-TO-B, ERIKA VIOLET JACKET, 50 M	FP4LDLD050MR2XE
FX PATCH CORD, OM4, LC DUPLEX - LC DUPLEX, OFNR, DUPLEX ZIP 2.0 MM, A-TO-B, ERIKA VIOLET JACKET, 60 M	FP4LDLD060MR2XE

Trademarks are the property of their respective owners.




Be certain.




## Commercial Automation and Control Solutions (continued)

### AMX™ and Crestron® Control System Cable

	Description	Belden Part Number	
		Non Plenum	Plenum
	22 AWG, 1 Shielded TC Pair (100Ω), + 18 AWG, 2 TC Conductor	1502R	1502P
	22 AWG, 1 Shielded BC Pair (100Ω), + 18 AWG, 2 BC Conductor	1392A	1392P


### DMX® System Cable

	Description	Belden Part Number	
		Non Plenum	Plenum
	24 AWG, 1 Pair DMX Cable	9841	82841
	22 AWG, 1 Pair DMX Cable	3105A	—
	24 AWG, 2 Pair DMX Cable	9842	82842
	22 AWG, 2 Pair DMX Cable	3107A	—


For DMX on Ethernet, see pages 10-13 for networking, or visit [Belden.com](http://Belden.com) to download a dedicated Lighting Cable catalog.

## Cable Management Solutions

### Free Standing Enclosures


	Description (H x W x D)	Model	RU'S	Width (in)	Depth (in)	Belden Part Number
	84" x 29" x 30" Black, 19" MTG, Vented top, Perf front & rear w/sides	XST	25, 39, 42, 45	29	30	XST84-3-154420
	84" x 29" x 34" Black, 19" MTG, Vented top, Perf front & rear w/sides	XDP	25, 39, 42, 45	29	34	XDP84-3-154420
	47u" x 19.9" x 24" Black, 19" MTG, Frame Only	XSF	10-48	19	36	XSF47-24-100000
	45u" x 22" x 24" Black, 19" MTG, Vented top, Vented front and rear, flush mount sides	XMF	11-57	22	24, 30, 36, 40	XMF45241222200
	44u" x 22" x 26" Black, 19" MTG, Vented top, Solid rear, sides	XME	24-44	22	20, 26.5	XME442620210
	44u" x 22" x 36" Black, 19" MTG, Vented top, Perf front, perf rear, sides	XMER	24-44	22	26.5, 31.5, 36	XMER4436233200

### 2 and 4 Post Racks

	Description (H x W x D)	Model	RU	Width (in)	Depth (in)	Screw	Type	Belden Part Number
	84" x 19" x 3" Channel Knock down	BHRR	45	19	—	12-24	Alum	BHRR194
	84" x 19" x 6" Channel Knock down	BHRR	45	19	—	12-24	Alum	BHRR6194
	84" x 23" x 3" Channel Knock down	BHRR	45	23	—	12-24	Alum	BHRR234
	84" x 19" x 3" Channel Knock down	XDR	44	19	—	12-24	Steel	XDR8419-312
	84" x 19" x 3" Channel Knock down	XDR	44	19	—	10-32	Steel	XDR8419-310
	84" x 19" x 3" Channel Welded	XDR	44	19	—	10/12	Steel	XDR8419-310W
	84" x 23" x 3" Channel Welded	XDR	44	23	—	10/12	Steel	XDR8423-31XW
	84" x 19" x 6" Channel Seismic	XDR	44	19	—	10-32	Steel	XDRS8419-610
	84" x 19" x 3" Channel 4 Post Knock down	XDR	44	19	24, 28, 32, 36	10/12	Steel	XDR8419-3#XXX
	84" x 23" x 3" Channel 4 Post Knock down	XDR	44	23	24, 28, 32, 36	10/12	Steel	XDR8423-31#XX


# = Screw Size Variable 0=10-32, 2=12-24 Screw, Depth 24, 28, 32, 36

### Vertical Cable Managers

	Description	Model	Width (in)	Depth (in)	Belden Part Number
	Single Sided Vertical organizer low density	BHVL	3.6, 6, 10, 12	8.75	BHVLOXX
	Single sided Vertical organizer high density	BHVH	3.6, 6, 10, 12	8.75	BHVH0XX
	Double sided Vertical organizer high/low density	BHVHL	3.6, 6, 10, 12	17.37	BHVHLXX
	Double sided Vertical organizer high/high density	BHVHH	3.6, 6, 10, 12	17.37	BHVHHXX

X = Width Variable 03=3.6", 06=6", 10=10", 12=12"

### Wall Mount Enclosures


	Description (H x W)	Model	RU	Width (in)	Depth (in)	Belden Part Number
	24" x 19" Black Wall mount w/glass door	XWM	12	19	20, 24	XWM-24XX-GD-3
	24" x 19" Black Wall mount w/steel door	XWM	12	19	20, 24	XWM-24XX-SD-3
	36" x 19" Black Wall mount w/glass door	XWM	18	19	20, 24	XWM-36XX-GD-3
	36" x 19" Black Wall mount w/steel door	XWM	18	19	20, 24	XWM-36XX-SD-3
	48" x 19" Black Wall mount w/glass door	XWM	25	19	20, 24	XWM-48XX-GD-3
	48" x 19" Black Wall mount w/steel door	XWM	25	19	20, 24	XWM-48XX-SD-3

Depth Variable 20=20", 24=24"


Consult Belden Cable Management Catalog to access enclosure configuration matrix and accessories listing. NEMA compliant enclosures also available.

## Networking Solutions

### AV Multimedia Modules

	Description	Belden Part Number		
		Almond	Elec. White	Black
	3.5mm Audio Coupler, F/F, Gold	AX105334-AL	AX105334-EW	AX105334-BK
	3.5mm Audio Coupler, F/Solder, Gold	AX105335-AL	AX105335-EW	AX105335-BK
	S-video Coupler, F/F	AX105336-AL	AX105336-EW	AX105336-BK
	RCA Gold-plated Coupler, F/F, Red	AX105337-AL	AX105337-EW	AX105337-BK
	RCA Gold-plated Coupler, F/F, White	AX105338-AL	AX105338-EW	AX105338-BK
	RCA Gold-plated Coupler, F/F, Yellow	AX105339-AL	AX105339-EW	AX105339-BK
	RCA Gold-plated Coupler, F/F, Green	AX105340-AL	AX105340-EW	AX105340-BK
	RCA Gold-plated Coupler, F/F, Blue	AX105341-AL	AX105341-EW	AX105341-BK
	Video F Coax 3GHz, Recessed, Gold-Plated	AX105346-AL	AX105346-EW	AX105346-BK
	Video F Coax, Recessed	AX102903	AX102904	AX102905
	Video F Coax, Flush	AX102906	AX102907	AX102908
	Video BNC Coax, Flush	AX104573	AX104575	AX104574
	USB 3.0 Coupler, A to A	AX105342-AL	AX105342-EW	AX105342-BK
	USB 2.0 Coupler, B to B	AX105344-AL	AX105344-EW	AX105344-BK
HDMI Coupler (Version 1.4)	AX105345-AL	AX105345-EW	AX105345-BK	

### KeyConnect Faceplates

	Description	Belden Part Number		
		Elec. White*	Stainless Steel*	Stainless Steel**
	1-Port, Single Gang	AX102660	—	AX102006
	2-Port, Single Gang	AX102665	AX104231	AX102007
	4-Port, Single Gang	AX102249	AX104232	AX102009
	6-Port, Single Gang	AX102251	AX104233	AX102010
	4-Port, Double Gang	—	AX104479	AX102011
	6-Port, Double Gang	AX102671	AX104480	AX102012
	Wall Mount Phone Plates	—	—	AX102005
	Single-gang Back Box, 1.89 in.	AX102657	—	—
	Double-gang Back Box, 1.89 in.	AX104131	—	—

Other configurations (i.e. numbers of ports) available; \* With ID window; \*\* Without ID window


## Networking Solutions – 10GX (TIA/EIA Category 6A LAN)

### 10GX KeyConnect Modular Jacks

	Color	Belden Part Number
	White	AX102282
	Black	AX102283
	Red	AX104153
	Blue	AX104156
	Purple	AX104157


A broad range of dark and pastel colors are also available

### 10GX KeyConnect Patch Panels


	Description	Belden Part Number
	KeyConnect, 24-Port, 1U*	AX103254
	KeyConnect, 48-Port, 2U*	AX103256
	AngleFlex, 24-Port, 1U**	AX103248
	AngleFlex, 48-Port, 2U**	AX103249
	KeyConnect, 24-Port, 1U**	AX103114
	KeyConnect, 48-Port, 1U**	AX103121
KeyConnect, 48-Port, 2U**	AX103115	

\* Preloaded (Titanium); \*\* Modular patch panels

### Category 6 Field-Installable Metal Body Ruggedized Plug

	Description	Belden Part Number
	DataTuff® Industrial Ethernet Ruggedized Modular Plug Kit UTP/STP, T568A	R301601
	DataTuff® Industrial Ethernet Ruggedized Modular Plug Kit UTP/STP, T568B	R301602

### 10GX KeyConnect Patch Panels (featuring designation strips)


	Description	Belden Part Number
	10GX KeyConnect Patch Panel featuring designation strips, 24-port, 1U, Black	AX105152
	10GX KeyConnect Patch Panel featuring designation strips, 48-port, 2U, Black	AX105153

Be certain.




## Networking Solutions – 10GX (TIA/EIA Category 6A LAN) (continued)

### 10GX Modular Cords (Bonded-Pairs CMR)

	Description	Belden Part Number			
		Black	Blue	Purple	White
	2 ft. (0.6 m)	CA21100002	CA21106002	CA21107002	CA21109002
	4 ft. (1.2 m)	CA21100004	CA21106004	CA21107004	CA21109004
	7 ft. (2.1 m)	CA21100007	CA21106007	CA21107007	CA21109007
	10 ft. (3.0 m)	CA21100010	CA21106010	CA21107010	CA21109010
	15 ft. (4.6 m)	CA21100015	CA21106015	CA21107015	CA21109015


Other lengths and colors available

### 10GX Category 6A Horizontal Cable

	Description	Belden Part Number				
		Bonded		Non-Bonded		
		Blue	White	Blue	White	Purple
	10GX Solution – CMR	10GX32 0061000	10GX32 0091000	10GX12 0061000	10GX12 0091000	10GX12 0071000
	10GX Solution – CMP	10GX33 D151000	10GX33 0091000	10GX13 D151000	10GX13 0091000	10GX13 0071000


Other Colors and Reel-in-Box Available

### 10GXS Small Diameter Category 6A Horizontal Cable

	Description	Belden Part Number				
		Bonded <small>(Available June 2015)</small>		Non-Bonded		
		Blue	White	Blue	White	Purple
	10GX Solution – CMR	10GX32 0061000	10GX32 0091000	10GX12 0061000	10GX12 0091000	10GX12 0071000
	10GX Solution – CMP	10GX33 D151000	10GX33 0091000	10GX13 D151000	10GX13 0091000	10GX13 0071000

Other Colors and Reel-in-Box Available

### 10GX Pre-Terminated System

	Cable Assembly*		KeyConnect Coupler Patch Panel (Preloaded)	Modular Coupler	
	CMR, Black	CA21100xxxA06	24-port, 1U, Titanium	AX104141	Black
CMP, Black	CA22100xxxA06	48-port, 2U, Titanium	AX104142		

\* Use xxx to specify length in feet—006-050 ft in increments of 1 ft—055-265 ft in increments of 5 ft


## Networking Solutions – CAT6+ (TIA/EIA Category 6 LAN)

### CAT6+ KeyConnect Modular Jacks

	Color	Belden Part Number
	White	AX101320
	Black	AX101321
	Red	AX104190
	Blue	AX104193
	Purple	AX104194


A broad range of dark and pastel colors are also available

### CAT6+ KeyConnect Patch Panels


	Description	Belden Part Number
	KeyConnect, 24-Port, 1U*	AX103253
	KeyConnect, 48-Port, 2U*	AX103255
	AngleFlex, 24-Port, 1U**	AX103248
	AngleFlex, 48-Port, 2U**	AX103249
	KeyConnect, 24-Port, 1U**	AX103114
	KeyConnect, 48-Port, 1U**	AX103121
	KeyConnect, 48-Port, 2U**	AX103115

\* Preloaded; \*\* Modular patch panels

### CAT6+ KeyConnect Patch Panels (featuring designation strips)

	Description	Belden Part Number
	CAT6+ KeyConnect Patch Panels featuring designation strips, 24-port, 1U, Black	AX105156
	CAT6+ KeyConnect Patch Panels featuring designation strips, 48-port, 2U, Black	AX105157

### CAT6+ Modular Cords (Bonded-Pairs CMR)

	Description	Belden Part Number			
		Black	Blue	Purple	White
	2 ft. (0.6 m)	C601100002	C601106002	C601107002	C601109002
	4 ft. (1.2 m)	C601100004	C601106004	C601107004	C601109004
	7 ft. (2.1 m)	C601100007	C601106007	C601107007	C601109007
	10 ft. (3.0 m)	C601100010	C601106010	C601107010	C601109010
	15 ft. (4.6 m)	C601100015	C601106015	C601107015	C601109015

Other lengths and colors available

## Networking Solutions – CAT6+ (TIA/EIA Category 6 LAN) (continued)

### CAT6+ Horizontal Cable

Description	Bonded			Non-Bonded			
	Blue	White	Black	Blue	White	Purple	Black
3600 Solution - CMR	3632 006A1000	3632 009A1000	3632 010A1000	3612 006A1000	3612 009A1000	3612 007A1000	3612 010A1000
3600 Solution - CMP	3633 D15A1000	3633 009A1000	3633 010A1000	3613 D15A1000	3613 009A1000	3613 007A1000	3613 010A1000
2400 Solution - CMR	1872A 006A1000	1872A 009A1000	1872A 010A1000	2412 006A1000	2412 009A1000	2412 007A1000	2412 010A1000
2400 Solution - CMP	1874A D15A1000	1874A 009A1000	1874A 010A1000	2413 D15A1000	2413 009A1000	2413 007A1000	2413 010A1000
Indoor/Outdoor Category 6 (CMR/CMX)	—	—	7940A	—	—	—	—
Indoor/Outdoor Category 6 Shielded (CMR/CMX)	—	—	7953A	—	—	—	—

Other colors available

### 3600 Pre-Terminated System

Cable Assembly*	KeyConnect Coupler Patch Panel (Preloaded)		Modular Coupler	
	Part Number	Description	Part Number	Description
CMR, Black	C601106xxxA06	24-port, 1U, Titanium	AX104227	Black
CMP, Black	C602106xxxA06	48-port, 2U, Titanium	AX104228	AX104215

\* Use xxx to specify length in feet—006-050 ft in increments of 1 ft—055-265 ft in increments of 5 ft

### CAT6+ Shielded Cabling System

Description	Belden Part Number				
	Blue	Gray	White	Black	Metallic
Belden DataTwist 2400, F/UTP, Non Plenum	1351A 0061000	1351A 0081000	1351A 0091000	—	—
Belden DataTwist 2400, F/UTP, Plenum	1352A 0061000	1352A 0081000	1352A 0091000	—	—
Shielded Modular Jack, Metallic	—	—	—	—	AX104596
Shielded Modular Patch Panel, 24-Port, 1U, Titanium (empty)	—	—	—	—	AX104563
Shielded Modular Patch Panel, 48-Port, 2U, Titanium (empty)	—	—	—	—	AX104564
2 ft (.6m), Shielded Patch Cord, 4-Pair, T568A/B-T568A/B, Non Plenum	C6F1106002	C6F1108002	C6F1109002	C6F1100002	—
4 ft (1.2m), Shielded Patch Cord, 4-Pair, T568A/B-T568A/B, Non Plenum	C6F1106004	C6F1108004	C6F1109004	C6F1100004	—
7 ft (2.1m), Shielded Patch Cord, 4-Pair, T568A/B-T568A/B, Non Plenum	C6F1106007	C6F1108007	C6F1109007	C6F1100007	—
15 ft (4.6m), Shielded Patch Cord, 4-Pair, T568A/B-T568A/B, Non Plenum	C6F1106015	C6F1108015	C6F1109015	C6F1100015	—
25 ft (7.6m), Shielded Patch Cord, 4-Pair, T568A/B-T568A/B, Non Plenum	C6F1106025	C6F1108025	C6F1109025	C6F1100025	—
15 ft (4.6m), Shielded Pigtailed, 4-Pair, T568B-Open, Non Plenum	C6F1306015	C6F1308015	—	—	—
25 ft (7.6m), Shielded Pigtailed, 4-Pair, T568B-Open, Non Plenum	C6F1306025	C6F1308025	—	—	—

### CAT6+ Accessories

Description	Belden Part Number
Connecting Tool	AX100749
Termination Station	AX101852
Release Tool	AX101185
Cable Preparation Tool	1797B
Patch Cord Tool	AX102775

Description	Belden Part Number
Velcro Cable Ties, 25 Per Roll, Black, 8 in	AX100783
Velcro Cable Ties, 25 Per Roll, Black, 12 in	AX100784
Wrap-Around Labels, Gray, 48 Labels/Sheet (25 sheets per pack)	AX101555

## Networking Solutions – CAT5E (TIA/EIA Category 5e LAN)

### CAT5E KeyConnect Modular Jacks

Color	Belden Part Number
White	AX101309
Black	AX101310
Red	AX104183
Blue	AX104186
Purple	AX104187

A broad range of dark and pastel colors are also available

### CAT5E KeyConnect Patch Panels

Description	Belden Part Number
HD-110, 24-Port, 1U*	AX103258
HD-110, 48-Port, 2U*	AX103259
AngleFlex, 24-Port, 1U**	AX103248
AngleFlex, 48-Port, 2U**	AX103249
KeyConnect, 24-Port, 1U**	AX103114
KeyConnect, 48-Port, 1U**	AX103121
KeyConnect, 48-Port, 2U**	AX103115

\*Preloaded; \*\*Modular patch panels

Be certain.



## Networking Solutions – CAT5E (TIA/EIA Category 5e LAN) (continued)

### CAT5E Modular Cords (Bonded-Pairs CMR)

Description	Belden Part Number			
	Black	Blue	Purple	White
2 ft. (0.6 m)	C501100002	C501106002	C501107002	C501109002
4 ft. (1.2 m)	C501100004	C501106004	C501107004	C501109004
7 ft. (2.1 m)	C501100007	C501106007	C501107007	C501109007
10 ft. (3.0 m)	C501100010	C501106010	C501107010	C501109010
15 ft. (4.6 m)	C501100015	C501106015	C501107015	C501109015

Other lengths and colors available

### CAT5E Horizontal Cable

Description	Bonded			Non-Bonded			
	Blue	White	Black	Blue	White	Purple	Black
1200 Solution - CMR	1700A 006U1000	1700A 009U1000	1700A 010U1000	1212 006U1000	1212 009U1000	1212 007U1000	1212 010U1000
1200 Solution - CMP	1701A D15U1000	1701A 009U1000	1701A 010U1000	1213 D15U1000	1213 009U1000	1213 007U1000	1213 010U1000
Indoor/Outdoor Category 5e (CMR/CMX)	—	—	7918A	—	1594A	—	7923A
Indoor/Outdoor Category 5e (Waterblocked)	—	—	—	—	—	—	7934A
Indoor/Outdoor Category 5e Shielded (CMR/CMX)	—	—	—	—	—	—	7919A
Indoor/Outdoor Category 5e Shielded (Waterblocked)	—	—	—	—	—	—	7937A
Indoor/Outdoor Tactical Category 5e (Heavy Duty Jacket)	—	—	1304A	—	—	—	—
4 Channel CatSnake Tactical Category 5e (16 pairs total)	—	—	1304A4	—	—	—	—
Indoor/Outdoor Tactical Category 5e (Upjacketed)	—	—	1305A	—	—	—	—
1 Pair Category 5e	1353A 006U1000	1353A 009U1000	1353A 010U1000	—	—	—	—

Other colors available

### CAT5E Shielded Cabling System

Description	Blue	Gray	White	Black	Metallic
	Belden DataTwist 1200, F/UTP, Non Plenum	1212F 0061000	1212F 0081000	1212F 0091000	1212F 0101000
Belden DataTwist 1200, F/UTP, Plenum	1213F 0061000	1213F 0081000	1213F 0091000	1213F 0101000	—
Shielded Modular Jack, Metallic	—	—	—	—	AX104595
Shielded Modular Patch Panel, 24-Port, 1U, Titanium (empty)	—	—	—	—	AX104563
Shielded Modular Patch Panel, 48-Port, 2U, Titanium (empty)	—	—	—	—	AX104564
2 ft (.6m), Shielded Patch Cord, 4-Pair, T568A/B-T568A/B, Non Plenum	C5F1106002	C5F1108002	C5F1109002	C5F1100002	—
4 ft (1.2m), Shielded Patch Cord, 4-Pair, T568A/B-T568A/B, Non Plenum	C5F1106004	C5F1108004	C5F1109004	C5F1100004	—
7 ft (2.1m), Shielded Patch Cord, 4-Pair, T568A/B-T568A/B, Non Plenum	C5F1106007	C5F1108007	C5F1109007	C5F1100007	—
15 ft (4.6m), Shielded Patch Cord, 4-Pair, T568A/B-T568A/B, Non Plenum	C5F1106015	C5F1108015	C5F1109015	C5F1100015	—
25 ft (7.6m), Shielded Patch Cord, 4-Pair, T568A/B-T568A/B, Non Plenum	C5F1106025	C5F1108025	C5F1109025	C5F1100025	—
15 ft (4.6m), Shielded Pigtailed, 4-Pair, T568B-Open, Non Plenum	C5F1306015	C5F1308015	—	—	—
25 ft (7.6m), Shielded Pigtailed, 4-Pair, T568B-Open, Non Plenum	C5F1306025	C5F1308025	—	—	—

### CAT5E Accessories

Description	Belden Part Number	Description	Belden Part Number
Connecting Tool	AX100749	Velcro Cable Ties, 25 Per Roll, Black, 8 in	AX100783
Termination Station	AX101852	Velcro Cable Ties, 25 Per Roll, Black, 12 in	AX100784
Release Tool	AX101185	Wrap-Around Labels, Gray, 48 Labels/Sheet (25 sheets per pack)	AX101555
Cable Preparation Tool	1797B		
Patch Cord Tool	AX102775		



## Networking Solutions – FiberExpress System

### FX Brilliance Universal Connectors

Description	Belden Part Number		
	Multimode, OM1	Multimode, OM3/OM4 - Aqua	Multimode, OM4 - Erika Violet
LC with 900 µm Boot, 25 per package	AX105200-B25	AX105202-B25	AX105252-B25
SC with 900 µm Boot, 25 per package	AX105205-B25	AX105207-B25	AX105253-B25
ST with 900 µm Boot, 25 per package	AX105210-B25	AX105212-B25	AX105254-B25

Description	Belden Part Number	
	Singlemode, OS2	Singlemode, OS2/APC
LC with 900 µm Boot	AX105203-B25	-
SC with 900 µm Boot	AX105208-B25	AX105209-B25
ST with 900 µm Boot	AX105213-B25	-

FX Brilliance Universal includes a boot for 900 µm Tight Buffered fiber. Boots for 2 mm/3 mm Jacketed fiber are sold separately. Replace -B25 with -S1 for sample 1 per package.

### FX Breakout Kits

Description	Belden Part Number
Breakout Kit for 2.0 mm Subunits, 6-fiber, 1-Pack	AX101100
Breakout Kit for 3.0 mm Subunits, 12-fiber, 1-Pack	AX101101
Breakout kit for 5.2 mm Subunits (Central Tube), 6-fiber, 1-Pack	AX104695
Breakout kit for 5.2 mm Subunits (Central Tube), 12-fiber, 1-Pack	AX104696

### FX Brilliance Installation Kit

Description	Belden Part Number
Precision Installation Kit (Basic Kit, Fiber Preparation Tools, Precision Cleaver and Visual Fault Locator)	AX104271

### FX UHD Housings

Description	Number of Module Bays	Total LC Duplex/ MPO Ports using FX Ultra Frames and Cassettes	Total LC Duplex/ MPO Ports using FX UHD Frames and Cassettes	Belden Part Number	
				Titanium	Black
1U Housing with Front and Rear Cable Tray	4	48	72	AX104681	AX105563
4U Housing with Front and Rear Cable Tray	16	192	288	AX104683	AX105565
4U 23" Housing with Front and Rear Cable Tray	20	240	360	AX105379	-
Optional 1U Splice Housing Kit, 144 splices (add up to 4 on the 4U Housing) <sup>1</sup>	N/A	N/A	N/A	AX104684	AX105678
Optional Patch Cord Tray Cover, 19in <sup>2</sup>	N/A	N/A	N/A	AX105162	-

### FX UHD Shelves

Description	Number of Module Bays	Total LC Duplex/ MPO Ports using FX Ultra Frames and Cassettes	Total LC Duplex/ MPO Ports using FX UHD Frames and Cassettes	Belden Part Number	
				Titanium	Black
1U Standard Fixed Shelf	4	48	72	AX105164	AX105673
1U Recessed Fixed Shelf	4	48	72	AX105165	AX105674
4U Standard Fixed Shelf	10	120	180	AX105166	AX105675
4U Recessed Fixed Shelf	10	120	180	AX105167	AX105676

See the FX UHD System Product Bulletin (PB500) for further options

### FX UHD and FX Ultra Type-A Cassettes

Description			Belden Part Number				
Patch Ports (fibers)	Trunk Ports	Family	OM1 Beige Adapters	OM3 Aqua Adapters	OM4 Erika Violet Adapters	OS2 Blue Adapters	SM/APC Green Adapters
<b>LC Duplex to MPO-12(f)</b>							
18 (36)	3	FX UHD*	-	FC3H18LDMF	FC4H18LDMF	FCSH18LDMF	FCSH18LAMF
12 (24)	2	FX Ultra	FC1U12LDMF	FC3U12LDMF	FC4U12LDMF	FCSU12LDMF	FCSU12LAMF
<b>SC Duplex to MPO-12(f)</b>							
6 (12)	1	FX Ultra	FC1U06SDMF	FC3U06SDMF	FC4U06SDMF	FCSU06SDMF	FCSU06SAMF
<b>SC Simplex to MPO-12(f)</b>							
12 (12)	1	FX Ultra	-	-	-	FCSU12SCMF	FCSU12SBMF

\*Optional HD Patch cord release tool AX104685

Be certain.



## Networking Solutions – FiberExpress System (continued)

### FX UHD and FX Ultra Type-A-Alternate Cassettes\*


Patch Ports (fibers)	Description		Belden Part Number				
	Trunk Ports	Family	OM1 Beige Adapters	OM3 Aqua Adapters	OM4 Erika Violet Adapters	OS2 Blue Adapters	SM/APC Green Adapters
<b>LC Duplex to MPO-12(f)</b>							
18 (36)	3	FX UHD*	–	FC3H18LDMF1A	FC4H18LDMF1E	FCSH18LDMF1B	FCSH18LAMF1G
12 (24)	2	FX Ultra	FC1U12LDMF1K	FC3U12LDMF1A	FC4U12LDMF1E	FCSU12LDMF1B	FCSU12LAMF1G
<b>SC Duplex to MPO-12(f)</b>							
6 (12)	1	FX Ultra	FC1U06SDMF1T	FC3U06SDMF1A	FC4U06SDMF1E	FCSU06SDMF1B	FCSU06SAMF1G
<b>SC Simplex to MPO-12(f)</b>							
12 (12)	1	FX Ultra	–	–	–	FCSU12SCMF1B	FCSU12SBMF1G

\* In order to maintain proper port numbering within a 10G installation AND chart your path to 40G and beyond, please refer to our Fiber Optic Catalog that outlines when and where to use Type-A-Alternate Cassettes, as well as the process for migrating to 40G.

### FX UHD and FX Ultra Frames

Patch Ports (fibers)	Description		Belden Part Number			
	Family	OM1 Beige Adapters	OM3 Aqua Adapters	OM4 Erika Violet Adapters	SM Blue Adapters	SM/APC Green Adapters
<b>MPO Type-A (Key-Up/Key-Down)</b>						
18	FX UHD	–	FF3H18MP	FF4H18MP	–	FFSH18MP
12	FX Ultra	–	FF3U12MP	FF4U12MP	–	FFSU12MP
<b>LC Duplex</b>						
18 (36)	FX UHD	–	FF3H18LD	FF4H18LD	FFSH18LD	FFSH18LA
12 (24)	FX Ultra	FF1U12LD	FF3U12LD	FF4U12LD	FFSU12LD	FFSU12LA
<b>SC Duplex</b>						
6 (12)	FX Ultra	FF1U06SD	FF3U06SD	FF4U06SD	FFSU06SD	FFSU06SA
<b>SC Simplex</b>						
12 (12)	FX Ultra	–	–	–	FFSU12SC	FFSU12SB
<b>ST</b>						
12 (12), Metal	FX Ultra	← FFSU12ST →				–

### FX MPO Trunk Assemblies



#### Building a SmartPart Number

Fixed Series	1. Choose Fiber Type	2. Choose Connectors	3. Choose Connector Gender	4. Choose Polarity (outside)	5. Choose Connector Count (per side)	6. Choose Length
FM	4	M	M	B	2	025M
<b>Fiber Type</b>	<b>Connectors</b>	<b>Connector Gender</b>	<b>Polarity (outside)</b>	<b>Connector Count</b>	<b>Length</b>	
3 OM3	M MPO-12	M Male to Male	A Type-A	1 12 Fiber	005M to 350M (use M as decimal)	
4 OM4		E Extension (M to F)	B Type-B	2 24 Fiber		
S OS2			C Type-C	D 144 Fiber		

#### Examples:

**FM4MMB2025M** : FX MPO TRUNK, OM4, MPO-12(MALE TO MALE), TYPE-B, 2 MPO (24 FIBERS), 25 M, OFNP, MINI-DISTRIBUTION (3.0MM SUB-UNITS), FAN-OUT: 0.5M x IN-LINE, ERIKA VIOLET JACKET

**FMSMEBD17M5**: FX MPO TRUNK, OS2, MPO-12(MALE TO FEMALE), TYPE-B, 12 MPO (144 FIBERS), 17.5 M, OFNP, MINI-DISTRIBUTION (3.0MM SUB-UNITS), FAN-OUT: 0.5M x IN-LINE, YELLOW JACKET

## Networking Solutions – FiberExpress System (continued)

### Standard FX Patch Cords

Length (m)	OM1	OM3	OM4	OS2	OS2/APC
	Beige	Aqua	Erika Violet	Blue	Green
<b>MPO-12(f) to MPO-12(f)</b>					
2	–	FP3MFMF002M	FP4MFMF002M	–	FPSMFMF002M
3	–	FP3MFMF003M	FP4MFMF003M	–	FPSMFMF003M
5	–	FP3MFMF005M	FP4MFMF005M	–	FPSMFMF005M
<b>LC Duplex to LC Duplex</b>					
2	–	FP3LDLD002M	FP4LDLD002M	FPSLDLD002M	FPSLALA002M
3	–	FP3LDLD003M	FP4LDLD003M	FPSLDLD003M	FPSLALA003M
5	–	FP3LDLD005M	FP4LDLD005M	FPSLDLD005M	FPSLALA005M
<b>SC Duplex to SC Duplex</b>					
2	FP1SDSD002M	FP3SDSD002M	FP4SDSD002M	FPSSDSD002M	FPSASA002M
3	FP1SDSD003M	FP3SDSD003M	FP4SDSD003M	FPSSDSD003M	FPSASA003M
5	FP1SDSD005M	FP3SDSD005M	FP4SDSD005M	FPSSDSD005M	FPSASA005M
<b>ST to ST (Duplex Cord)</b>					
2	FP1STST002M	FP3STST002M	FP4STST002M	FPSSTST002M	–
3	FP1STST003M	FP3STST003M	FP4STST003M	FPSSTST003M	–
5	FP1STST005M	FP3STST005M	FP4STST005M	FPSSTST005M	–
<b>Hybrid: LC Duplex to SC Duplex</b>					
3	FP1LSDSD003M	FP3LSDSD003M	FP4LSDSD003M	FPSLSDSD003M	FPSLASA003M
<b>Hybrid: SC Duplex to ST</b>					
3	FP1SDST003M	FP3SDST003M	–	FPSDST003M	–

### FX Color-coded Pigtail Kits (900 µm)

Description	Belden Part Number				
	OM1	OM3	OM4	OS2	SM/APC
LC	–	FT3LC900PR12	FT4LC900PR12	FTSLC900PR12	FTSLB900PR12
SC	FT1SC900PR12	FT3SC900PR12	FT4SC900PR12	FTSSC900PR12	FTSSB900PR12
ST	FT1ST900PR12	FT3ST900PR12	–	FTSST900PR12	–

Standard Color-coded Pigtail Kits contain 12 color-coded 900 µm fibers, 2 m in length.

### FX Cable

Description			Belden Part Number						
			2 fibers	6 fibers	12 fibers	24 fibers	48 fibers	96 fibers	144 fibers
Indoor	Interconnect	Riser	B96915	–	–	–	–	–	–
		Plenum	B96919	–	–	–	–	–	–
Indoor	Distribution Tight buffer	Riser	B9X037	B9X039	B9X042	B9X601	B9X606	B9X622	B9X619
		Plenum	B9X043	B9X045	B9X048	B9X611	B9X616	B9X623	B9X621
	Breakout 2.0mm units	Riser	B9X005	B9X007	B9X010	B9X012	–	–	–
		Plenum	B9X013	B9X015	B9X018	B9X020	–	–	–
Indoor / Outdoor	Interlocked Armor Dist.	Riser	–	B9X230	B9X231	B9X232	B9X235	B9X237	B9X238
		Plenum	–	B9X240	B9X241	B9X242	B9X245	B9X247	B9X248
Outdoor	Loose Tube	Riser	–	B9X510T	B9X511T	B9X500T	B9X505T	B9X513T	B9X509T
Indoor / Outdoor	Distribution Tight Buffer	Riser	B9X037T	B9X039T	B9X042T	B9X601T	B9X606T	–	–
		Plenum	B9X043T	B9X045T	B9X048T	B9X611T	B9X616T	–	–
	Loose Tube	Riser	–	B9X810	B9X811	B9X812	B9X814	B9X816	B9X817
Plenum		–	B9X202	B9X204	B9X205	B9X207	B9X211	B9X215	

Other Fiber Counts are available; See our full line up in our Belden Optical Fiber Catalog

Where X is replaced by:

OM1	OM2	OM3	OM4	Single-mode
B	A	C	E	W

Other connector and adapter types are available

Other patch cord combinations and lengths are available

Be certain.



## Broadcast Cable Assemblies

Belden is continuing to build on its reputation as the solutions provider for the Broadcast and Pro AV markets, with the addition of pre-terminated, custom made, cable assemblies to its solutions portfolio. Belden is now able to offer a wide range of cable assemblies in custom lengths using SMPTE, Tactical Fiber, Coax, Triax, and Audio cables and industry leading connector brands, in cable assemblies with the same superior quality that you have come to expect from Belden. All assemblies are manufactured to Belden's strict quality standards and undergo rigorous testing to ensure that your signal is transmitted flawlessly and safely.

Some of the cable and connector choices include, but are not limited to the list to the right.

Assembly configurators have been developed to help our customers navigate the breadth of cable and connector alternatives offered and to simplify the process of "building" assemblies that fit their particular installation requirements.



### Broadcast Coax/Triax Assembly Configurator

Assembly	Connector 1	Product Code	Connector 2	Length & Unit of Measure	Jacket Color
A	05	1855A	05	150	R

Please select options 1 to 9 (in order):

- Cable Type: Coax
- UL Type: CMR
- Cable Grade: RG-59
- Cable Construction: 1855A
- Connector 1 Make: Belden
- Connector 1: 1-Piece Compression-1855A
- Connector 2 Make: Belden
- Connector 2: 1-Piece Compression-1855A
- Type a Length (feet): 150
- Jacket Color: RED

**Cable Information**

AWG: 23

Plenum Rated: No

Riser Rated: Yes

Belden Color Code: 002

**Connector Information**

Connector 1 Product Code: 1855ABHD1

Connector 1 Finish/Band Color: Polished Nickel/Purple

Connector 2 Product Code: 1855ABHD1

Connector 2 Finish/Band Color: Polished Nickel/Purple

Special Labeling Instructions:

Part Number:

Description:

Lead Time:






Minimum Order Qty:

Version 1.2

Once configured, each assembly will have a "smart part" number assigned to it that will allow the user to easily determine the construction of the assembly and can be used for repeat ordering. To facilitate the quoting process, the configurators have built-in functionality that allows the user to build a BOM of different assemblies that can then be sent in for quoting purposes.

Assembly	Connector 1	Product Code	Connector 2	Length & Unit of Measure	Jacket Color
A	05	1855A	05	150	R

For more information or to access the configurators, please visit our website; <http://www.belden.com/broadcast-assemblies.cfm>, or call 1-800-422-9961.

Coax	
	<p><b>Cables:</b> 1694A, 1694WB, 1855A, 1505A, 1505F, 1694F, 1855P, 7731A, 7732A, 1506A, 179DT, 1695A</p> <p><b>Connectors:</b> Belden Brilliance HD-BNC, King's BNC &amp; Mini DIN's, Amphenol BNC &amp; Mini DIN's</p>
Triax	
	<p><b>Cables:</b> RG-11 - 8233, 8233A, 8233P, 1859A RG-59 - 1856A, 1857A, 1856B, 88232</p> <p><b>Connectors:</b> King's Lemo</p>
Tactical Fiber	
	<p><b>Cables:</b> Single Mode and Multi Mode 2 - 12 channels</p> <p><b>Connectors:</b> LC, SC &amp; ST Tyco, Amphenol, QPC, Neutrik OpticalCON</p>
SMPTE	
	<p><b>Cables:</b> 7804R - Industry Standard 7804P - Industry Standard Plenum 7804LW - Light Duty 7804WB - Industry Standard Waterblocked 7804C - Heavy Gauge Standard 7817A - Double Jacket 7818A - Harsh Environment</p> <p><b>Connectors:</b> Lemo King's Amphenol</p>
Audio Cable	
	<p><b>Cables:</b> 9451, 9451P, 1800B, 1815R, 1816R, 1513C</p> <p><b>Connectors:</b> Neutrik XLR Amphenol XLR DT-12</p>

## Part Number Index

Part No.	Page	Part No.	Page	Part No.	Page	Part No.	Page	Part No.	Page	Part No.	Page	Part No.	Page
5T00UP	4	1313A	4	1801BS4	3	3613 010A1000	7, 12	6302UE	4	8810WB	4	AX102655	10
6T00UP	4	1325A	4	1801BS6	3	3613 D15A1000	7, 12	6302UH	4	8812	4	AX102657	10
10GX12 0061000	7, 11	1325R	4	1802B	3	3632 006A1000	7, 12	6400FE	4	8814	4	AX102660	10
10GX12 0071000	7, 11	1326A	4	1802F	3	3632 009A1000	7, 12	6400FH	4	9116	8	AX102671	10
10GX12 0091000	7, 11	1326R	4	1803F	3	3632 010A1000	7, 12	6500FE	4	9116P	8	AX102775	12, 13
10GX13 0071000	7, 11	1347A	6	1805F	3	3633 009A1000	7, 12	6500FH	4	9451	4	AX102903	10
10GX13 0091000	7, 11	1351A 0061000	12	1806F	3	3633 010A1000	7, 12	6502FE	4	9451D	3, 4	AX102904	10
10GX13 D151000	7, 11	1351A 0081000	12	1807A	6	3633 D15A1000	7, 12	6502GE	4	9451DP	3, 4	AX102905	10
10GX32 0061000	7, 11	1351A 0091000	12	1808A	6	5000FE	4	6541PA	3	9451P	4	AX102906	10
10GX32 0091000	7, 11	1352A 0061000	12	1814R	3	5000FH	4	6542PA	3	9451PS4	3	AX102907	10
10GX33 0091000	7, 11	1352A 0081000	12	1814WB	3	5000UE	4	6543PA	3	9451PS6	3	AX102908	10
10GX33 D151000	7, 11	1352A 0091000	12	1815P	3	5000UH	4	6545PA	3	9451WB	4	AX103114	10, 11, 12
10GXS12 0061000	11	1353A	4	1815R	3	5100FE	4	6546PA	3	9841	9	AX103115	10, 11, 12
10GXS12 0071000	11	1353A 006U1000	13	1815WB	3	5100FH	4	6548PA	3	9842	9	AX103121	10, 11, 12
10GXS12 0091000	11	1353A 009U1000	13	1816P	3	5100UE	4	6549PA	3	82723	4	AX103248	10, 11, 12
10GXS13 0071000	11	1353A 010U1000	13	1816R	3	5102U1	4	7700A	6	82841	9	AX103249	10, 11, 12
10GXS13 0091000	11	1392A	9	1816WB	3	5102UE	4	7712A	5	82842	9	AX103253	11
10GXS13 D151000	11	1392P	9	1817P	3	5102UH	4	7731A	5	88232	6	AX103254	10
10GXS32 0061000	11	1502P	9	1817R	3	5140F1	4	7731WB	5	533945	8	AX103255	11
10GXS32 0091000	11	1502R	9	1817WB	3	5140U1	4	7732A	5	539945	8	AX103256	10
10GXS33 0091000	11	1505A	5	1818P	3	5200FE	4	7789A	5	543945	8	AX103258	12
10GXS33 D151000	11	1505ABHD1	5, 6	1818R	3	5200FH	4	7796A	5	549945	8	AX103259	12
179DT	5	1505ABHD3	5	1818WB	3	5200UE	4	7804C	6	633948	8	AX104024	11
179DTBHD1	5	1505ABHDL	5	1819R	3	5202U1	4	7804LW	6	639948	8	AX104131	10
179DTBHD3	5	1505F	5	1820R	3	5202UE	4	7804P	6	643948	8	AX104141	11
716SNS1P11H	8	1505S5	5	1821R	3	5202UH	4	7804R	6	649948	8	AX104142	11
716SNS1P11HPLA	5, 8	1506A	5	1822R	3	5240F1	4	7804WB	6	AC303569	7	AX104153	10
716SNS1P11HQ	5	1506ABHD1	5	1823R	3	5240U1	4	7817A	6	AC303570	7	AX104156	10
1172A	3	1506ABHD3	5	1829AC	8	5300F1	4	7818A	6	AC303571	7	AX104157	10
1189A	8	1506ABHDL	5	1850F	3	5300FE	4	7824P	6	AC303572	7	AX104183	12
1189AP	8	1510C	3	1852F	3	5300FH	4	7824R	6	AC303573	7	AX104186	12
1192A	3	1511C	3	1854F	3	5300U1	4	7824WB	6	AC303574	7	AX104187	12
1212 006U1000	7, 13	1512C	3	1855A	5	5300UE	4	7825P	6	AC303575	7	AX104190	11
1212 007U1000	7, 13	1513C	3	1855ABHD1	5	5300UH	4	7825R	6	AC303576	7	AX104193	11
1212 009U1000	7, 13	1514C	3	1855ABHD3	5	5302FE	4	7880A	3	AC303579	7	AX104194	11
1212 010U1000	7, 13	1523A	8	1855ABHDL	5	5302GE	4	7890A	3	AC303580	7	AX104215	12
1212F 0061000	13	1523AP	8	1855P	5	5302U1	4	7892A	3	AC303581	7	AX104227	12
1212F 0081000	13	1594A	13	1855S5	5	5302UE	4	7893A	3	AC303582	7	AX104228	12
1212F 0091000	13	1694A	5	1856A	6	5302UH	4	7918A	13	AC303583	7	AX104231	10
1212F 0101000	13	1694ABHD1	5	1857A	6	5400FE	4	7919A	13	AC303584	7	AX104232	10
1213 007U1000	7, 13	1694ABHD3	5	1858A	6	5400FH	4	7923A	13	AC303585	7	AX104233	10
1213 009U1000	7, 13	1694ABHDL	5	1859A	6	5500F1	4	7934A	13	AC303586	7	AX104271	14
1213 010U1000	7, 13	1694ABHDLW*	5	1872A 006A1000	7, 12	5500FE	4	7937A	13	AX100749	12, 13	AX104479	10
1213 D15U1000	7, 13	1694D	5	1872A 009A1000	7, 12	5500FH	4	7940A	12	AX100783	12, 13	AX104480	10
1213F 0061000	13	1694F	5	1872A 010A1000	7, 12	5502FE	4	7953A	12	AX100784	12, 13	AX104563	12, 13
1213F 0081000	13	1694S5	5	1874A 009A1000	7, 12	5502GE	4	7987P	7	AX101100	14	AX104564	12, 13
1213F 0091000	13	1694WB	5	1874A 010A1000	7, 12	6000FE	4	7987R	7	AX101101	14	AX104573	10
1213F 0101000	13	1695A	5	1874A D15A1000	7, 12	6000FH	4	7988P	7	AX101185	12, 13	AX104574	10
1277P	6	1695ABHD1	5	2221	3	6000UE	4	7988R	7	AX101309	12	AX104575	10
1277R	6	1695ABHDL	5	2412 006A1000	7, 12	6000UH	4	7999A	8	AX101310	12	AX104595	13
1279P	6	1695S5	5	2412 007A1000	7, 12	6100FE	4	7999AP	8	AX101320	11	AX104596	12
1279R	6	1700A 006U1000	7, 13	2412 009A1000	7, 12	6100FH	4	8232	6	AX101321	11	AX104681	14
1281P	6	1700A 009U1000	7, 13	2412 010A1000	7, 12	6100UE	4	8232A	6	AX101555	12, 13	AX104683	14
1281R	6	1700A 010U1000	7, 13	2413 007A1000	7, 12	6102UE	4	8233A	6	AX101852	12, 13	AX104684	14
1281S5	6	1701A 009U1000	7, 13	2413 009A1000	7, 12	6102UH	4	8233P	6	AX102005	10	AX104695	14
1282S5	6	1701A 010U1000	7, 13	2413 010A1000	7, 12	6200FE	4	8233WB	6	AX102006	10	AX104696	14
1304A	4, 13	1701A D15U1000	7, 13	2413 D15A1000	7, 12	6200FH	4	8240	8	AX102007	10	AX105152	10
1304A4	4, 13	1776	3	3105A	9	6200UE	4	8412	3	AX102009	10	AX105153	10
1305A	4, 13	1794A	5	3107A	9	6202UE	4	8451	4	AX102010	10	AX105156	11
1307A	4	1794ABHD1	5	3612 006A1000	7, 12	6202UH	4	8723	4	AX102011	10	AX105157	11
1308A	4	1797B	12, 13	3612 007A1000	7, 12	6300FE	4	8808	4	AX102012	10	AX105162	14
1309A	4	1800B	3	3612 009A1000	7, 12	6300FH	4	8808H	4	AX102249	10	AX105164	14
1310A	4	1800F	3	3612 010A1000	7, 12	6300UE	4	8808WB	4	AX102251	10	AX105165	14
1311A	4	1801B	3	3613 007A1000	7, 12	6300UH	4	8810	4	AX102282	10	AX105166	14
1312A	4	1801BD	3	3613 009A1000	7, 12	6302FE	4	8810H	4	AX102283	10	AX105167	14



Be certain.



## Part Number Index

Part No.	Page	Part No.	Page	Part No.	Page	Part No.	Page	Part No.	Page	Part No.	Page	Part No.	Page
AX105200-B25	14	B9X018	16	B96574	6	C501100004	13	CPLCRBC-BR	5, 6	FP3LDDL002M	16	FSNSHBCNPLA	8
AX105202-B25	14	B9X020	16	B96575	6	C501100007	13	CPSNSCT-596	8	FP3LDDL003M	16	FT1SC900PR12	16
AX105203-B25	14	B9X037	16	B96639	6	C501100010	13	FC1U06SDMF	14	FP3LDDL005M	16	FT1ST900PR12	16
AX105205-B25	14	B9X037T	16	B96915	16	C501100015	13	FC1U06SDMFT	14	FP3LDSDD003M	16	FT3LC900PR12	16
AX105207-B25	14	B9X039	16	B96919	16	C501106002	13	FC1U12LDMF	15	FP3MFMF002M	16	FT3SC900PR12	16
AX105207-S1	8	B9X039T	16	BB3PHCT	5	C501106004	13	FC1U12LDMFTK	15	FP3MFMF003M	16	FT3ST900PR12	16
AX105208-B25	14	B9X042	16	BB3PST	5	C501106007	13	FC3H18LDMF	14	FP3MFMF005M	16	FT4LC900PR12	16
AX105209-B25	14	B9X042T	16	BHRR194	9	C501106010	13	FC3H18LDMF1A	15	FP3SDSD002M	16	FT4SC900PR12	16
AX105210-B25	14	B9X043	16	BHRR234	9	C501106015	13	FC3U06SDMF	14	FP3SDSD003M	16	FTSLB900PR12	16
AX105212-B25	14	B9X043T	16	BHRR6194	9	C501107002	13	FC3U06SDMF1A	15	FP3SDSD005M	16	FTSLC900PR12	16
AX105213-B25	14	B9X045	16	BHVH0XX	9	C501107004	13	FC3U12LDMF	14	FP3SDST003M	16	FTSSB900PR12	16
AX105252-B25	14	B9X045T	16	BHVHXX	9	C501107007	13	FC3U12LDMF1A	15	FP3STST002M	16	FTSSC900PR12	16
AX105253-B25	14	B9X048	16	BHVHXX	9	C501107010	13	FC4H18LDMF	14	FP3STST003M	16	FTSST900PR12	16
AX105254-B25	14	B9X048T	16	BHVLOXX	9	C501107015	13	FC4H18LDMF1E	15	FP3STST005M	16	HD-700-2	7
AX105334-AL	10	B9X202	16	C5F1100002	13	C501109002	13	FC4U06SDMF	14	FP4LDDL002M	16	HD-700-4	7
AX105334-BK	10	B9X204	16	C5F1100004	13	C501109004	13	FC4U06SDMF1E	15	FP4LDDL003M	16	HD-700-8	7
AX105334-EW	10	B9X205	16	C5F1100007	13	C501109007	13	FC4U12LDMF	14	FP4LDDL005M	16	HD-700-16	7
AX105335-AL	10	B9X207	16	C5F1100015	13	C501109010	13	FC4U12LDMF1E	15	FP4LDSDD003M	16	HD-700-25	7
AX105335-BK	10	B9X211	16	C5F1100025	13	C501109015	13	FCSH18LDMF	14	FP4MFMF002M	16	HD-700-35	7
AX105335-EW	10	B9X215	16	C5F1106002	13	C601100002	11	FCSH18LDMF1G	15	FP4MFMF003M	16	HD-700-50	7
AX105336-AL	10	B9X230	16	C5F1106004	13	C601100004	11	FCSH18LDMF	14	FP4MFMF005M	16	HD2001	7
AX105336-BK	10	B9X231	16	C5F1106007	13	C601100007	11	FCSH18LDMF1B	15	FP4SDSD002M	16	HD2002	7
AX105336-EW	10	B9X232	16	C5F1106015	13	C601100010	11	FCSU06SAMD	14	FP4SDSD003M	16	HD2003	7
AX105337-AL	10	B9X235	16	C5F1106025	13	C601100015	11	FCSU06SAMD1G	15	FP4SDSD005M	16	HD2004	7
AX105337-BK	10	B9X237	16	C5F1108002	13	C601106002	11	FCSU06SDMF	14	FP4STST002M	16	HD2007	7
AX105337-EW	10	B9X238	16	C5F1108004	13	C601106004	11	FCSU06SDMF1B	15	FP4STST003M	16	L3011B	5
AX105338-AL	10	B9X240	16	C5F1108007	13	C601106007	11	FCSU12LDMF	14	FP4STST005M	16	PS-11	5, 8
AX105338-BK	10	B9X241	16	C5F1108015	13	C601106010	11	FCSU12LDMF1G	15	FPSLALA002M	16	PS59/6/RGB	5, 6
AX105338-EW	10	B9X242	16	C5F1108025	13	C601106015	11	FCSU12LDMF	14	FPSLALA003M	16	PSA59/6	5, 6, 8
AX105339-AL	10	B9X245	16	C5F1109002	13	C601107002	11	FCSU12LDMF1B	15	FPSLALA005M	16	R301601	7, 10
AX105339-BK	10	B9X247	16	C5F1109004	13	C601107004	11	FCSU12SBMF	14	FPSLASA003M	16	R301602	7, 10
AX105339-EW	10	B9X248	16	C5F1109007	13	C601107007	11	FCSU12SBMF1G	15	FPSLDL002M	16	SLS-59/6	5, 6, 8
AX105340-AL	10	B9X500T	16	C5F1109015	13	C601107010	11	FCSU12SCMF	14	FPSLDL003M	16	SLS-RGB	8
AX105340-BK	10	B9X505T	16	C5F1109025	13	C601107015	11	FCSU12SCMF1B	15	FPSLDL005M	16	SLS-RGB-*	5
AX105340-EW	10	B9X509T	16	C5F1306015	13	C601109002	11	FF1U06SD	15	FPSLDSDD003M	16	SNSUNI	5, 8
AX105341-AL	10	B9X510T	16	C5F1306025	13	C601109004	11	FF1U12LD	15	FPSMFMF002M	16	X105344-BK	10
AX105341-BK	10	B9X511T	16	C5F1308015	13	C601109007	11	FF3H18LD	15	FPSMFMF003M	16	XDP84-3-154420	9
AX105341-EW	10	B9X513T	16	C5F1308025	13	C601109010	11	FF3H18MP	15	FPSMFMF005M	16	XDR8419-3#XXX	9
AX105342-AL	10	B9X601	16	C6F1100002	12	C601109015	11	FF3U06SD	15	FPSSASA002M	16	XDR8419-310	9
AX105342-BK	10	B9X601T	16	C6F1100004	12	CA21100XXXA06	11	FF3U12LD	15	FPSSASA003M	16	XDR8419-310W	9
AX105342-EW	10	B9X606	16	C6F1100007	12	CA22100XXXA06	11	FF3U12MP	15	FPSSASA005M	16	XDR8419-312	9
AX105344-AL	10	B9X606T	16	C6F1100015	12	CA21100002	11	FF4H18LD	15	FPSSSD002M	16	XDR8423-31XW	9
AX105344-EW	10	B9X611	16	C6F1100025	12	CA21100004	11	FF4H18MP	15	FPSSSD003M	16	XDR8423-31#XX	9
AX105345-AL	10	B9X611T	16	C6F1106002	12	CA21100007	11	FF4U06SD	15	FPSSSD005M	16	XDRS8419-610	9
AX105345-BK	10	B9X616	16	C6F1106004	12	CA21100010	11	FF4U12LD	15	FPSSDST003M	16	XME442620210	9
AX105345-EW	10	B9X616T	16	C6F1106007	12	CA21100015	11	FF4U12MP	15	FPSSSTST002M	16	XMER4436233200	9
AX105346-AL	10	B9X619	16	C6F1106015	12	CA21106002	11	FFSH18LA	15	FPSSSTST003M	16	XMF45241222200	9
AX105346-BK	10	B9X621	16	C6F1106025	12	CA21106004	11	FFSH18LD	15	FPSSSTST005M	16	XSF47-24-100000	9
AX105346-EW	10	B9X622	16	C6F1108002	12	CA21106007	11	FFSH18MP	15	FS1BNC	6	XST84-3-154420	9
AX105379	14	B9X623	16	C6F1108004	12	CA21106010	11	FFSU06SA	15	FSNS6BNCPL	8	XWM-24XX-GD-3	9
AX105563	14	B9X810	16	C6F1108007	12	CA21106015	11	FFSU06SD	15	FSNS6BNCPLQ	8	XWM-24XX-SD-3	9
AX105565	14	B9X811	16	C6F1108015	12	CA21107002	11	FFSU12LA	15	FSNS6BNCU	8	XWM-36XX-GD-3	9
AX105673	14	B9X812	16	C6F1108025	12	CA21107004	11	FFSU12LD	15	FSNS6PL	8	XWM-36XX-SD-3	9
AX105674	14	B9X814	16	C6F1109002	12	CA21107007	11	FFSU12MP	15	FSNS6PLQ	8	XWM-48XX-GD-3	9
AX105675	14	B9X816	16	C6F1109004	12	CA21107010	11	FFSU12SB	15	FSNS6RCAPL	8	XWM-48XX-SD-3	9
AX105676	14	B9X817	16	C6F1109007	12	CA21107015	11	FFSU12SC	15	FSNS6RCAPLQ	8		
AX105678	14	B96551	6	C6F1109015	12	CA21109002	11	FFSU12ST	15	FSNS6RCAU	8		
B9E006	8	B96556	6	C6F1109025	12	CA21109004	11	FP1LSD003M	16	FSNS6U	8		
B9E014	8	B96567	6	C6F1306015	12	CA21109007	11	FP1SDSD002M	16	FSNS11HBCN	8		
B9X005	16	B96568	6	C6F1306025	12	CA21109010	11	FP1SDSD003M	16	FSNS11HBCNPLA	5		
B9X007	16	B96569	6	C6F1308015	12	CA21109015	11	FP1SDSD005M	16	FSNS11QHBCN	5		
B9X010	16	B96570	6	C6F1308025	12	CPLCCT-11BNC	5, 8	FP1SDST003M	16	FSNS59BNCPL	8		
B9X012	16	B96571	6	C601106XXXA06	12	CPLCCT-SLM	6, 8	FP1STST002M	16	FSNS59BNCPL	8		
B9X013	16	B96572	6	C602106XXXA06	12	CPLCCT-SS59/11	5	FP1STST003M	16	FSNS59BNCPL	8		
B9X015	16	B96573	6	C501100002	13	CPLCRBC1794	5	FP1STST005M	16	FSNS59U	8		

## Recommended Transmission Distance at Serial Digital Data Rates


Data Rate:	143 Mb/s		177 Mb/s		270 Mb/s		360 Mb/s		1.5 Gb/s		3.0 Gb/s	
	SMPTE 259M		ITU-R BT. 601		SMPTE 259M		SMPTE 259M		SMPTE 292M		SMPTE 424M	
	Composite SD-SDI (NTSC)		Composite SD-SDI (PAL)		Component SD-SDI		Widescreen SD-SDI		HD-SDI		1080p/50-60 3G-SDI	
Cable Part Number	Ft.	m	Ft.	m	Ft.	m	Ft.	m	Ft.	m	Ft.	m
179DT	542	165	498	152	416	127	362	110	115	35	81	25
1865A*	686	209	627	191	517	158	446	136	134	41	90	27
1855P	986	301	904	276	746	227	640	195	190	58	125	38
1855A	1022	312	932	284	781	238	680	207	215	66	149	45
1505F	1173	358	1060	323	858	262	732	223	220	67	147	45
1506A***	1354	413	1243	379	1030	314	887	270	265	81	177	54
1694F	1460	445	1312	400	1066	325	916	279	280	85	189	58
1505A**	1440	439	1317	401	1105	337	958	292	304	93	210	64
1695A	1706	520	1566	477	1276	389	1104	337	322	98	211	64
1694WB****	1733	528	1597	487	1333	406	1161	354	363	111	249	76
1694A****	1791	546	1650	503	1371	418	1188	362	371	113	256	78
1694D	1791	546	1650	503	1371	418	1188	362	371	113	256	78
7732A	2575	785	2335	712	1929	588	1638	499	451	137	283	86
1794A	2276	694	2078	633	1746	532	1510	460	469	143	320	98
7731A	2791	851	2613	796	2146	654	1871	570	580	177	393	120

The serial digital interconnect standards are designed to operate where the signal loss at 1/2 the clock frequency does not exceed the approximate loss values listed below. The recommended length values shown are based on typical attenuation values for the cables listed and the following criteria: **Maximum length = 30 dB loss at 1/2 the clock frequency: SMPTE 259M, PAL, Widescreen. Maximum length = 20 dB loss at 1/2 the clock frequency: SMPTE 292M and SMPTE 424M.**

The bit error rate (BER) can vary dramatically as the calculated distances are approached. BER is dependent on receiver design and the losses of the actual coax used. Distribution and routing equipment manufacturers should be contacted to verify their maximum recommended transmission.

- \* Includes cables that use 1855A as a constituent, such as 7787A, 7788A, 7789A, 7790A, 7791A, 7792A, 1855S3, 1855S5, 1855S6
- \*\* Includes cables that use 1505A as a constituent, such as 7794A, 7795A, 7796A, 7798A, 1505S3, 1505S5, 1505S6
- \*\*\* Includes cables that use 1506A as a constituent, such as 1283S3, 1283S5, 1283S6
- \*\*\*\* Includes cables that use 1694A as a constituent, such as 7710A, 7711A, 7712A, 7713A, 1694S3, 1694S5, 1694S6, 1694WB, 1694D

### Return Loss Headroom (1694A)



### Maximum Recommended Transmission Distance at Digital Audio Data Rates\* (AES3-2003)\*\*

Part Number	6 MHz		12 MHz		25 MHz	
	Ft.	m	Ft.	m	Ft.	m
1353A	1112	339	772	235	525	160
9180, 7880A Series	813	248	633	193	474	144
1800F	664	203	424	129	279	85
1800B, 1801B, 1802B, 1803F Series	1105	337	877	267	649	198
1696A	1538	469	1250	381	1015	309
179DT (AES3)†♦	1005	306	722	220	522	159
(AES-3id)††	402	123	289	88	209	64
1855A (AES3)†♦	1992	607	1538	469	1111	339
(AES-3id)††	796	242	615	188	444	135
1505A (AES3)†♦	2911	887	2222	677	1538	469
(AES-3id)††	1164	355	888	270	615	188
1505F (AES3)†♦	2985	910	2041	622	1389	423
(AES-3id)††	1194	364	816	249	556	169
1694A (AES3)†♦	3407	1039	2500	762	2000	610
(AES-3id)††	1363	416	1000	305	800	244
1694F (AES3)†♦	3660	1116	2411	735	1701	518
(AES-3id)††	1811	552	1193	364	841	256