

# 114FX6 Industrial Ethernet Switch

N-Tron Networking Series



## ▶▶▶ Unmanaged Industrial Ethernet Switch

### PRODUCT FEATURES

- Compact, Space Saving Package
- Full IEEE 802.3 Compliance
- Eight 10/100BaseTX RJ-45 Ports
- Six 100BaseFX Ports, ST or SC Style
- Unmanaged Operation
- Extended Environmental Specifications
- -40°C to 80°C Operating Temperature
- >2 Million Hours MTBF
- Supports Full/Half Duplex Operation
- Auto Sensing 10/100BaseTX, Duplex, MDIX
- Full Wire Speed Communication
- Store-and-Forward Technology
- Redundant Power Inputs (10-49 VDC)
- ESD Protection Diodes on all RJ-45 Ports
- Surge Protection Diodes on Power Inputs
- LED Link/Activity Status Indication
- Hardened Metal DIN-Rail Enclosure



### PRODUCT OVERVIEW

The N-TRON® 114FX6 unmanaged industrial network switch is designed to meet the most demanding communications requirements while providing high throughput and minimum downtime. The 14-port Ethernet switch is the perfect low-cost solution for mission critical data acquisition, control, and Ethernet I/O applications.

#### Exceptional Quality

The ultra-compact 114FX6 provides exceptional performance and reliability under harsh conditions. Enclosed in a high-grade metal case, the switch offers a robust feature set that includes an extended temperature range, superior shock and vibration resistance, redundant power inputs, surge and ESD protection, and an exceptional MTBF—greater than two million hours. The space-saving design includes an attached DIN-rail bracket for quick installation.

#### Versatile Connectivity

The 114FX6 includes eight RJ-45 auto-sensing 10/100BaseTX ports. All ports support full/half duplex transmission and use N-Tron's proven Ethernet switching technology. Setup is easy. The unit automatically configures itself on the network and auto-negotiates both speed and flow control for all copper ports.

For fiber optic networks, the 114FX6 supplies six 100BaseFX ports. These connections provide vital support for applications where EMI immunity or communication over long distances (up to 80 km) is required. N-Tron offers singlemode and multimode options, as well as SC- or ST-style connectivity.

#### Excellent Network Support

The 114FX6 is a brilliant plug-and-play solution for unmanaged operations, eliminating virtually all network collisions. Designed with advanced communication processing, store-and-forward programming and memory for up to 8,000 MAC-addresses, this powerful unit handles the demands of even the most complex networks. Intelligent auto-sensing ports instantly recognize and resolve 10/100BaseTX, MDIX and duplex conflicts. For added convenience, LEDs are provided to display link status and activity for each port.

# ▶▶▶ 114FX6 Specifications

## Specifications

### Switch Properties

Number of MAC Addresses: 8000  
 Latency Typical: 2.6  $\mu$ s  
 Switching Method: Store-and-Forward

### Case Dimensions

Height: 4.3" (10.8 cm)  
 Width: 3.1" (7.9 cm)  
 Depth: 4.6" (11.5 cm)  
 Weight (max): 1.7 lbs (0.77 kg)  
 DIN-Rail Mount: 35mm

### Electrical

Redundant Input Voltage: 10-49 VDC (Regulated)  
 Input Current (max): 545mA max. @24 VDC  
 BTU/hr: 44.7@24 VDC  
 N-Tron Power Supply: NTPS-24-1.3 (1.3A@24V)

### Environmental

Operating Temperature: -40°C to 80°C  
 Storage Temperature: -40°C to 85°C  
 Operating Humidity: 5% to 95% (Non Condensing)  
 Operating Altitude: 0 to 10,000 ft.

### Shock and Vibration (bulkhead mounted)

Shock: 200g @ 10ms  
 Vibration/Seismic: 50g, 5-200Hz, Triaxial

### Reliability

MTBF: >2 Million Hours

### Network Media

10BaseT:  $\geq$ Cat3 Cable  
 100BaseTX:  $\geq$ Cat5 Cable

### Connectors

10/100BaseTX: Eight (8) RJ-45 Copper Ports  
 100BaseFX: Six (6) SC or ST Fiber Duplex Ports

### Recommended Wiring Clearance

Front: 4" (10.16 cm)  
 Side: 1" (2.54 cm)

## Fiber Transceiver Characteristics


Fiber Length	2km*	15km**	40km**	80km**
TX Power Min	-19dBm	-15dBm	-5dBm	-5dBm
RX Sensitivity Max	-31dBm	-31dBm	-34dBm	-34dBm
Wavelength	1310nm	1310nm	1310nm	1550nm

\* Multimode Fiber Optic Cable  
 \*\* Singlemode Fiber Optic Cable

## Regulatory Approvals

- FCC: Title 47, Part 15, Subpart B, Class A; ANSI C63.4; ICES-003
- UL /cUL: Class I, Div 2, Groups A, B, C, D and T4
- CE: IEC 61000-4-2/3/4/5/6/8/11, EN 61000-6-2/4
- Other: ABS Type Approval for Shipboard Applications; GOST-R certified; RoHS compliant

Further information regarding this product's regulatory conformity can be found on the N-Tron website at [www.n-tron.com/regulator](http://www.n-tron.com/regulator)




OPTIONAL COMPACT PANEL MOUNT ASSY.  
 ( P/N: CPMA-2 )

# ▶▶▶ 114FX6 Specifications

## ORDERING INFORMATION

PART NUMBER	DESCRIPTION
114FX6-XX	14-port (8 10/100BaseTX, 6 100BaseFX Fiber Ports, multimode) Industrial Ethernet Switch, DIN-Rail
114FXE6-XX-YY	14-port (8 10/100BaseTX, 6 100BaseFX Fiber Ports, singlemode) Industrial Ethernet Switch, DIN-Rail
NTPS-24-1.3	N-Tron Power Supply - (1.3 Amp @ 24 VDC)
CPMA-2	Compact panel mount (factory installed option only)
URMK	Universal Rack Mount Kit

Where: E = Singlemode  
 XX = ST for ST style fiber connector, SC for SC style fiber connector  
 YY = Segment length:  
 15 for 15km max. fiber segment length  
 40 for 40km max. fiber segment length  
 80 for 80km max. fiber segment length  
*Mixed fiber configurations available.*



**RL**  
**RED LION**  
 a spectris company  
**EXCELLENCE. REDEFINED.**  
[www.redlion.net](http://www.redlion.net)  
 +1 (717) 767-6511

As global experts in communication, monitoring and control for industrial automation and networking, Red Lion has been delivering innovative solutions for over forty years. Our automation, Ethernet and cellular M2M technology enables companies worldwide to gain real-time data visibility that drives productivity. Product brands include Red Lion, N-Tron and Sixnet. With headquarters in York, Pennsylvania, the company has offices across the Americas, Asia-Pacific and Europe. Red Lion is part of Spectris plc, the productivity-enhancing instrumentation and controls company. For more information, please visit [www.redlion.net](http://www.redlion.net). ADLD0311 031120 © 2020 Red Lion Controls, Inc. All rights reserved. Red Lion, the Red Lion logo, N-Tron and Sixnet are registered trademarks of Red Lion Controls, Inc. All other company and product names are trademarks of their respective owners.

**AMERICAS**  
 SALES@REDLION.NET

**ASIA-PACIFIC**  
 ASIA@REDLION.NET

**EUROPE, MIDDLE EAST, AFRICA**  
 EUROPE@REDLION.NET