

2J6A83B-RB-SP

5GNR Screw Mount

Key Features

5GNR

- 617-960 MHz
- 1427-2690 MHz
- 3300-5000 MHz
- 5150-5925 MHz

Screw Mount

Anti-Rotation

Ground Plane Dependent

Customizable Cable and Connector

Dimensions \varnothing 69 × 65.5 mm

Certificates: IP67, IK09, IP69K



1. Antenna and electrical specifications

| Parameters | 5G NR Antenna | | | |
|-----------------------------|---|---|---------------------------------|----------------------|
| Technologies | 5G, 4G, 3G and 2G | | | |
| Standards | 5G NR/4G LTE/FirstNet/CBRS/LPWA/CAT-X/CAT-Mx/CAT-NBx/NB-IoT/3G/2G | | | |
| Frequency (MHz) | 617-960 | 1427-2690 | 3300-5000 | 5150-5925 |
| Band (MHz) | 600, 700, 850, 900 | 1500, 1600, 1700, 1800, 1900, 2000, 2100, 2300, 2500, 2600 | 3300, 3500, 3600, 3700, 4500 | 5200, 5500, 5800 |
| 5G NR Bands | n5, n8, 12, n20, n28, n71, n81, n82, n83, | n1, n2, n3, n7, n25, n34, n38, n39, n40, n41, n50, n51, n66, n70, n74, n75, n76, n80, n84, n86 | n77, n78, n79 | |
| 4G LTE Bands | B5, B6, B8, B12, B13, B14, B17, B18, B19, B20, B26, B27, B28, B29, B44, B67, B68, B71, B85 | B1, B2, B3, B4, B7, B9, B10, B11, B21, B23, B24, B25, B30, B32, B33, B34, B35, B36, B37, B38, B39, B40, B41, B45, B50, B51, B65, B66, B69, B70, B74, B75, B76 | B22, B42, B43, B48, B49, B52 | B46, B47, B252, B255 |
| 3G CELL Bands | B5, B6, B8, B12, B13, B14, B19, B20, B26 | B1, B2, B3, B4, B7, B9, B10, B11, B21, B25, B32, B33, B34, B35, B36, B37, B38, B39, B40 | B22 | |
| 2G CELL Bands | 710, 750, 810T, 850, 900P, 900E, 900R | 1800DCS, 1900PCS | | |
| CDMA CELL Bands | BC0, BC2, BC3, BC7, BC9, BC10, BC12, BC18, BC19 | BC1, BC4, BC6, BC8, BC13, BC14, BC15, BC16, BC20, BC21 | | |
| Return Loss (dB) | ~-5.3 | ~-15.0 | ~-12.3 | ~-5.8 |
| VSWR | ~4.0:1 | ~1.7:1 | ~1.8:1 | ~3.1:1 |
| Efficiency (%) | ~41.0 | ~55.7 | ~43.5 | ~25.4 |
| Peak Gain (dBi) | ~-0.9 | ~3.0 | ~3.7 | ~-0.2 |
| Average Gain (dB) | ~-4.2 | ~-2.7 | ~-3.6 | ~-6.3 |
| Impedance (Ohm) | 50 | | | |
| Polarisation | Linear | | | |
| Radiation Pattern | Omni-Directional | | | |
| Max. Input Power (W) | 35 | | | |
| Connector Type | SMA-Male Standard (Other Connectors Available) | | | |
| Cable Length | 300 cm Standard (Any Cable Length Available) | | | |
| Cable Type | LL100 Standard (Other Cables Available) | | | |

Antenna Measurement Conditions:

Mounted on 30 x 30 cm Metal Plate



100 cm of LL100 Cable



Measured in Certified CTIA 3D Anechoic Chamber



2. Mechanical and environmental specifications

| Specifications | 2J6A83B-RB-SP |
|----------------------------------|-------------------|
| Mounting Type | Screw Mount |
| Dimensions (mm) | Ø 69 x 65.5 |
| Rec. Tighten Torque (Nm) | 6 Nm |
| Radome | ASA |
| Radome color | Black |
| Antenna Base | Zamak |
| Operating Temperature (C) | -40 to +85 |
| Storage Temperature (C) | -40 to +85 |
| Substance Compliance | RoHS |
| Certificates | IP67, IK09, IP69K |


3. Antenna parameters








Radiation pattern reference






740 and 2500 MHz Radiation pattern



4500 and 5500 MHz Radiation pattern

4. Antenna drawings



Note: Dimensions are in millimeters
***Dimensions are after mounting**
****Mounting Torque= 6 Nm**

5. Antenna Images

